




REVISIONS		DOC. NO. SPC-F003	Effective 7/8/02	DCP No. 1308				
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1969	A	RELEASED	JWM	9/12/02	JN	03/18/08	JN	03/18/08



RECOMMENDED MOUNTING CONFIGURATION

SPECIFICATIONS:  
 IMPEDANCE: 50 Ohms  
 FREQUENCY RANGE: 0-6 GHz  
 WORKING VOLTAGE: 170 V rms @ sea level  
 TEMPERATURE RANGE: -65°C TO 165°C  
 INSULATION RESISTANCE: 1,000 Megohms min.

#	DESCRIPTION	MATERIAL	FINISH
1	BODY	BRASS	GOLD, 3 μ"
2	INSULATOR	PTFE	-
3	CONTACT	Be.Cu.	GOLD, 30 μ"
		MATERIAL	FINISH

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DISCLAIMER:  
 ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

DRAWN BY:	DATE:
Jeff McVicker	9/12/02
CHECKED BY:	DATE:
Jason Nash	03/18/08
APPROVED BY:	DATE:
Jason Nash	03/18/08

DRAWING TITLE:		MMCX Jack, PCB Mount	
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	SPC10016	18C1889.dwg	A
SCALE:	NTS	U.O.M.: INCHES [mm]	SHEET: 1 OF 1