

Crystal Clock Oscillator

2725 Series

Power-saving Type

■ Application

- For compact mobile information equipment, such as DVC, DSC, notebook PC, and PDA

■ Features

- A power saving-type crystal oscillator, capable of being driven by a 2.5 V. power supply.
- Automatic mounting by taping and IR reflow (lead-free) are possible.
- Lead-free.
- Compact and light. Dimensions : 5.0 x 3.2 x 1.0 mm, weight : 0.06 g.

Pb
Free

RoHS Compliant
Directive 2011/65/EU


Absolute maximum rating
Supply Voltage (V_{CC}) -0.5 to +7.0 V
Storage Temperature Range -55 to +125 °C




■ Specifications

Item			Model	2725Q						
Output Level				CMOS						
Nominal Frequency Range			(MHz)	$2.5 \leq F < 5$	$5 \leq F < 10$	$10 \leq F < 20$	$20 \leq F < 40$	$40 \leq F < 75$	$75 \leq F \leq 125$	
Operating Temperature Range			(°C)	-10 to +70						
Overall Frequency Tolerance			($\times 10^{-6}$)	± 50						
Supply Voltage [V_{CC}]			(V)	$+2.5 \pm 0.1$						
Current Consumption Max.	During Operation	+25 °C	(mA)	2	3	4	6	16	24	
	During Standby	+25 °C	(μ A)	10						
V_{OL} max/ V_{OH} min			(V)	$0.1 V_{CC}/0.9 V_{CC}$						$0.2 V_{CC}/0.8 V_{CC}$
Tr Max. / Tf Max.			(ns)	5/5 ($0.1 V_{CC}$ to $0.9 V_{CC}$)						4/4 ($0.2 V_{CC}$ to $0.8 V_{CC}$)
Symmetry Min. to Max.			(%)	40 to 60 (at $1/2 V_{CC}$)						
Load (C_L) Max.			(pF)	15						
Start-up time Max.			(ms)	4						10
Standby function				Available (Three-state)						
Specification Number				NSA6296B						

■ Dimensions



■ Output Waveform <CMOS>



■ Standby Function

#1 Input	#3 Output
Level H ($0.7 V_{CC} \leq V_{IH} \leq V_{CC}$) or OPEN is selected.	Oscillation output ON
Level L ($V_{IL} \leq 0.3 V_{CC}$) is selected.	High impedance

Please specify the model name, frequency, and specification number when you order products.
For further questions regarding specifications, please feel free to contact us.