

## Important notice

Dear Customer,

On 7 February 2017 the former NXP Standard Product business became a new company with the tradename **Nexperia**. Nexperia is an industry leading supplier of Discrete, Logic and PowerMOS semiconductors with its focus on the automotive, industrial, computing, consumer and wearable application markets

In data sheets and application notes which still contain NXP or Philips Semiconductors references, use the references to Nexperia, as shown below.

Instead of <http://www.nxp.com>, <http://www.philips.com/> or <http://www.semiconductors.philips.com/>, use **<http://www.nexperia.com>**

Instead of [sales.addresses@www.nxp.com](mailto:sales.addresses@www.nxp.com) or [sales.addresses@www.semiconductors.philips.com](mailto:sales.addresses@www.semiconductors.philips.com), use **[salesaddresses@nexperia.com](mailto:salesaddresses@nexperia.com)** (email)

Replace the copyright notice at the bottom of each page or elsewhere in the document, depending on the version, as shown below:

- © NXP N.V. (year). All rights reserved or © Koninklijke Philips Electronics N.V. (year). All rights reserved

Should be replaced with:

- © **Nexperia B.V. (year). All rights reserved.**

If you have any questions related to the data sheet, please contact our nearest sales office via e-mail or telephone (details via **[salesaddresses@nexperia.com](mailto:salesaddresses@nexperia.com)**). Thank you for your cooperation and understanding,

Kind regards,

Team Nexperia

# DATA SHEET

**74LVT02**

**3.3V Quad 2-input NOR gate**

Product specification

1996 Aug 15

IC24 Data Handbook

3.3V Quad 2-input NOR gate

74LVT02


QUICK REFERENCE DATA

| SYMBOL                 | PARAMETER                                       | CONDITIONS<br>$T_{amb} = 25^{\circ}\text{C}$ ;<br>$GND = 0V$ | TYPICAL    | UNIT |
|------------------------|-------------------------------------------------|--------------------------------------------------------------|------------|------|
| $t_{PLH}$<br>$t_{PHL}$ | Propagation delay<br>An or Bn<br>to $\bar{Y}_n$ | $C_L = 50\text{pF}$ ;<br>$V_{CC} = 3.3V$                     | 2.8<br>2.6 | ns   |
| $C_{IN}$               | Input capacitance                               | $V_I = 0V$ or $3.0V$                                         | 3          | pF   |
| $I_{CCL}$              | Total supply current                            | Outputs Low; $V_{CC} = 3.6V$                                 | 1          | mA   |


ORDERING INFORMATION

| PACKAGES             | TEMPERATURE RANGE                              | OUTSIDE NORTH AMERICA | NORTH AMERICA | DWG NUMBER |
|----------------------|------------------------------------------------|-----------------------|---------------|------------|
| 14-Pin Plastic SO    | $-40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$ | 74LVT02 D             | 74LVT02 D     | SOT108-1   |
| 14-Pin Plastic SSOP  | $-40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$ | 74LVT02 DB            | 74LVT02 DB    | SOT337-1   |
| 14-Pin Plastic TSSOP | $-40^{\circ}\text{C}$ to $+85^{\circ}\text{C}$ | 74LVT02 PW            | 74LVT02PW DH  | SOT402-1   |


LOGIC SYMBOL



PIN CONFIGURATION



LOGIC SYMBOL (IEEE/IEC)




PIN DESCRIPTION

| PIN NUMBER               | SYMBOL      | NAME AND FUNCTION       |
|--------------------------|-------------|-------------------------|
| 2, 3, 5, 6, 8, 9, 11, 12 | An-Bn       | Data inputs             |
| 1, 4, 10, 13             | $\bar{Y}_n$ | Data outputs            |
| 7                        | GND         | Ground (0V)             |
| 14                       | $V_{CC}$    | Positive supply voltage |

## 3.3V Quad 2-input NOR gate

74LVT02

## LOGIC DIAGRAM



## FUNCTION TABLE

| INPUTS |     | OUTPUT     |
|--------|-----|------------|
| Dna    | Dnb | $\bar{Q}n$ |
| L      | L   | H          |
| L      | H   | L          |
| H      | L   | L          |
| H      | H   | L          |

## NOTES:

H = High voltage level

L = Low voltage level

ABSOLUTE MAXIMUM RATINGS<sup>1, 2</sup>

| SYMBOL    | PARAMETER                      | CONDITIONS                  | RATING       | UNIT |
|-----------|--------------------------------|-----------------------------|--------------|------|
| $V_{CC}$  | DC supply voltage              |                             | -0.5 to +4.6 | V    |
| $I_{IK}$  | DC input diode current         | $V_I < 0$                   | -50          | mA   |
| $V_I$     | DC input voltage <sup>3</sup>  |                             | -0.5 to +7.0 | V    |
| $I_{OK}$  | DC output diode current        | $V_O < 0$                   | -50          | mA   |
| $V_{OUT}$ | DC output voltage <sup>3</sup> | Output in Off or High state | -0.5 to +7.0 | V    |
| $I_{OUT}$ | DC output current              | Output in High state        | -32          | mA   |
|           |                                | Output in Low state         | 64           |      |
| $T_{stg}$ | Storage temperature range      |                             | -65 to 150   | °C   |

## NOTES:

1. Stresses beyond those listed may cause permanent damage to the device. These are stress ratings only and functional operation of the device at these or any other conditions beyond those indicated under "recommended operating conditions" is not implied. Exposure to absolute-maximum-rated conditions for extended periods may affect device reliability.
2. The performance capability of a high-performance integrated circuit in conjunction with its thermal environment can create junction temperatures which are detrimental to reliability. The maximum junction temperature of this integrated circuit should not exceed 150°C.
3. The input and output negative voltage ratings may be exceeded if the input and output clamp current ratings are observed.

## RECOMMENDED OPERATING CONDITIONS

| SYMBOL              | PARAMETER                                           | LIMITS |     | UNIT |
|---------------------|-----------------------------------------------------|--------|-----|------|
|                     |                                                     | MIN    | MAX |      |
| $V_{CC}$            | DC supply voltage                                   | 2.7    | 3.6 | V    |
| $V_I$               | Input voltage                                       | 0      | 5.5 | V    |
| $V_{IH}$            | High-level input voltage                            | 2.0    |     | V    |
| $V_{IL}$            | Low-level Input voltage                             |        | 0.8 | V    |
| $I_{OH}$            | High-level output current                           |        | -20 | mA   |
| $I_{OL}$            | Low-level output current                            |        | 32  | mA   |
| $\Delta t/\Delta v$ | Input transition rise or fall rate; Outputs enabled |        | 10  | ns/V |
| $T_{amb}$           | Operating free-air temperature range                | -40    | +85 | °C   |

## 3.3V Quad 2-input NOR gate

74LVT02

## DC ELECTRICAL CHARACTERISTICS

Over recommended operating conditions

Voltages are referenced to GND (ground = 0V)

| SYMBOL           | PARAMETER                                            | TEST CONDITIONS                                                                                          | LIMITS                |                  |      | UNIT |
|------------------|------------------------------------------------------|----------------------------------------------------------------------------------------------------------|-----------------------|------------------|------|------|
|                  |                                                      |                                                                                                          | Temp = -40°C to +85°C |                  |      |      |
|                  |                                                      |                                                                                                          | MIN                   | TYP <sup>1</sup> | MAX  |      |
| V <sub>IK</sub>  | Input clamp voltage                                  | V <sub>CC</sub> = 2.7V; I <sub>IK</sub> = −18mA                                                          |                       |                  | −1.2 | V    |
| V <sub>OH</sub>  | High-level output voltage                            | V <sub>CC</sub> = 2.7 to 3.6V; I <sub>OH</sub> = −100μA                                                  | V <sub>CC</sub> −0.2  |                  |      | V    |
|                  |                                                      | V <sub>CC</sub> = 2.7V; I <sub>OH</sub> = −6mA                                                           | 2.4                   |                  |      |      |
|                  |                                                      | V <sub>CC</sub> = 3.0V; I <sub>OH</sub> = −20mA                                                          | 2.0                   |                  |      |      |
| V <sub>OL</sub>  | Low-level output voltage                             | V <sub>CC</sub> = 2.7V; I <sub>OL</sub> = 100μA                                                          |                       |                  | 0.2  | V    |
|                  |                                                      | V <sub>CC</sub> = 2.7V; I <sub>OL</sub> = 24mA                                                           |                       |                  | 0.5  |      |
|                  |                                                      | V <sub>CC</sub> = 3.0V; I <sub>OL</sub> = 32mA                                                           |                       |                  | 0.5  |      |
| I <sub>I</sub>   | Input leakage current                                | V <sub>CC</sub> = 0 or 3.6V; V <sub>I</sub> = 5.5V                                                       |                       |                  | 10   | μA   |
|                  |                                                      | V <sub>CC</sub> = 3.6V; V <sub>I</sub> = V <sub>CC</sub> or GND                                          |                       |                  | ±1   |      |
| I <sub>OFF</sub> | Output off current                                   | V <sub>CC</sub> = 0V; V <sub>I</sub> or V <sub>O</sub> = 0 to 4.5V                                       |                       |                  | ±100 | μA   |
| I <sub>CCH</sub> | Quiescent supply current                             | V <sub>CC</sub> = 3.6V; Outputs High, V <sub>I</sub> = GND or V <sub>CC</sub> , I <sub>O</sub> = 0       |                       |                  | 0.02 | mA   |
| I <sub>CCL</sub> |                                                      | V <sub>CC</sub> = 3.6V; Outputs Low, V <sub>I</sub> = GND or V <sub>CC</sub> , I <sub>O</sub> = 0        |                       | 1                | 2    |      |
| ΔI <sub>CC</sub> | Additional supply current per input pin <sup>2</sup> | V <sub>CC</sub> = 3V to 3.6V; One input at V <sub>CC</sub> −0.6V, Other inputs at V <sub>CC</sub> or GND |                       |                  | 0.2  | μA   |
| C <sub>I</sub>   | Input capacitance                                    | V <sub>I</sub> = 3V or 0                                                                                 |                       | 3                |      | pF   |

## NOTES:

1. All typical values are at  $V_{CC} = 3.3V$  and  $T_{amb} = 25^\circ C$ .
2. This is the increase in supply current for each input at the specified voltage level other than  $V_{CC}$  or GND.

## AC CHARACTERISTICS


GND = 0V;  $t_R = t_F = 2.5ns$ ;  $C_L = 50pF$ ,  $R_L = 500\Omega$ ;  $T_{amb} = -40^\circ C$  to  $+85^\circ C$ .

| SYMBOL                 | PARAMETER                                    | WAVEFORM | LIMITS                   |                  |            |                 | UNIT |
|------------------------|----------------------------------------------|----------|--------------------------|------------------|------------|-----------------|------|
|                        |                                              |          | $V_{CC} = 3.3V \pm 0.3V$ |                  |            | $V_{CC} = 2.7V$ |      |
|                        |                                              |          | MIN                      | TYP <sup>1</sup> | MAX        | MAX             |      |
| $t_{PLH}$<br>$t_{PHL}$ | Propagation delay<br>An or Bn to $\bar{Y}_n$ | 1        | 1.0<br>1.0               | 2.8<br>2.6       | 4.4<br>3.6 | 5.2<br>3.4      | ns   |

## NOTE:

1. All typical values are at  $V_{CC} = 3.3V$  and  $T_{amb} = 25^\circ C$ .

## AC WAVEFORMS


 $V_M = 1.5V$ ,  $V_{IN} = GND$  to  $2.7V$ 

Waveform 1. Propagation delay for inverting outputs

3.3V Quad 2-input NOR gate

74LVT02

TEST CIRCUIT AND WAVEFORMS




3.3V Quad 2-input NOR gate

74LVT02

SO14: plastic small outline package; 14 leads; body width 3.9 mm

SOT108-1



DIMENSIONS (inch dimensions are derived from the original mm dimensions)

| UNIT   | A<br>max. | A <sub>1</sub>   | A <sub>2</sub> | A <sub>3</sub> | b <sub>p</sub> | c                | D <sup>(1)</sup> | E <sup>(1)</sup> | e     | H <sub>E</sub> | L     | L <sub>p</sub> | Q              | v    | w    | y     | Z <sup>(1)</sup> | θ        |
|--------|-----------|------------------|----------------|----------------|----------------|------------------|------------------|------------------|-------|----------------|-------|----------------|----------------|------|------|-------|------------------|----------|
| mm     | 1.75      | 0.25<br>0.10     | 1.45<br>1.25   | 0.25           | 0.49<br>0.36   | 0.25<br>0.19     | 8.75<br>8.55     | 4.0<br>3.8       | 1.27  | 6.2<br>5.8     | 1.05  | 1.0<br>0.4     | 0.7<br>0.6     | 0.25 | 0.25 | 0.1   | 0.7<br>0.3       | 8°<br>0° |
| inches | 0.069     | 0.0098<br>0.0039 | 0.057<br>0.049 | 0.01           | 0.019<br>0.014 | 0.0098<br>0.0075 | 0.35<br>0.34     | 0.16<br>0.15     | 0.050 | 0.24<br>0.23   | 0.041 | 0.039<br>0.016 | 0.028<br>0.024 | 0.01 | 0.01 | 0.004 | 0.028<br>0.012   |          |

Note

1. Plastic or metal protrusions of 0.15 mm maximum per side are not included.


| OUTLINE<br>VERSION | REFERENCES |          |      |  | EUROPEAN<br>PROJECTION                                                                | ISSUE DATE           |
|--------------------|------------|----------|------|--|---------------------------------------------------------------------------------------|----------------------|
|                    | IEC        | JEDEC    | EIAJ |  |                                                                                       |                      |
| SOT108-1           | 076E06S    | MS-012AB |      |  |  | 91-08-13<br>95-01-23 |

3.3V Quad 2-input NOR gate

74LVT02

SSOP14: plastic shrink small outline package; 14 leads; body width 5.3 mm

SOT337-1




3.3V Quad 2-input NOR gate

74LVT02

TSSOP14: plastic thin shrink small outline package; 14 leads; body width 4.4 mm

SOT402-1



---

3.3V Quad 2-input NOR gate74LVT02

---

**NOTES**

3.3V Quad 2-input NOR gate

74LVT02

| DEFINITIONS               |                        |                                                                                                                                                                                                                                                            |
|---------------------------|------------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Data Sheet Identification | Product Status         | Definition                                                                                                                                                                                                                                                 |
| Objective Specification   | Formative or in Design | This data sheet contains the design target or goal specifications for product development. Specifications may change in any manner without notice.                                                                                                         |
| Preliminary Specification | Preproduction Product  | This data sheet contains preliminary data, and supplementary data will be published at a later date. Philips Semiconductors reserves the right to make changes at any time without notice in order to improve design and supply the best possible product. |
| Product Specification     | Full Production        | This data sheet contains Final Specifications. Philips Semiconductors reserves the right to make changes at any time without notice, in order to improve design and supply the best possible product.                                                      |

Philips Semiconductors and Philips Electronics North America Corporation reserve the right to make changes, without notice, in the products, including circuits, standard cells, and/or software, described or contained herein in order to improve design and/or performance. Philips Semiconductors assumes no responsibility or liability for the use of any of these products, conveys no license or title under any patent, copyright, or mask work right to these products, and makes no representations or warranties that these products are free from patent, copyright, or mask work right infringement, unless otherwise specified. Applications that are described herein for any of these products are for illustrative purposes only. Philips Semiconductors makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

LIFE SUPPORT APPLICATIONS  
Philips Semiconductors and Philips Electronics North America Corporation Products are not designed for use in life support appliances, devices, or systems where malfunction of a Philips Semiconductors and Philips Electronics North America Corporation Product can reasonably be expected to result in a personal injury. Philips Semiconductors and Philips Electronics North America Corporation customers using or selling Philips Semiconductors and Philips Electronics North America Corporation Products for use in such applications do so at their own risk and agree to fully indemnify Philips Semiconductors and Philips Electronics North America Corporation for any damages resulting from such improper use or sale.