

# PESDxL4UF; PESDxL4UG; PESDxL4UW

Low capacitance unidirectional quadruple ESD protection diode arrays

Rev. 04 — 28 February 2008

Product data sheet

## 1. Product profile

### 1.1 General description

Low capacitance unidirectional quadruple ElectroStatic Discharge (ESD) protection diode arrays in small Surface-Mounted Device (SMD) plastic packages designed to protect up to four signal lines from the damage caused by ESD and other transients.

Table 1. Product overview

| Type number | Package  |        |        | Package configuration     |
|-------------|----------|--------|--------|---------------------------|
|             | Nexperia | JEITA  | JEDEC  |                           |
| PESD3V3L4UF | SOT886   | -      | MO-252 | leadless ultra small      |
| PESD5V0L4UF | SOT886   | -      | MO-252 | leadless ultra small      |
| PESD3V3L4UG | SOT353   | SC-88A | -      | very small                |
| PESD5V0L4UG | SOT353   | SC-88A | -      | very small                |
| PESD3V3L4UW | SOT665   | -      | -      | ultra small and flat lead |
| PESD5V0L4UW | SOT665   | -      | -      | ultra small and flat lead |

### 1.2 Features

- ESD protection of up to four lines
- Low diode capacitance
- Max. peak pulse power:  $P_{PP} = 30 \text{ W}$
- Low clamping voltage:  $V_{CL} = 12 \text{ V}$
- Ultra low leakage current:  $I_{RM} = 5 \text{ nA}$
- ESD protection up to 20 kV
- IEC 61000-4-2; level 4 (ESD)
- IEC 61000-4-5 (surge);  $I_{PP} = 2.5 \text{ A}$

### 1.3 Applications

- Computers and peripherals
- Audio and video equipment
- Cellular handsets and accessories
- Communication systems
- Portable electronics
- Subscriber Identity Module (SIM) card protection







1.4 Quick reference data

Table 2. Quick reference data  
*T<sub>amb</sub> = 25 °C unless otherwise specified.*

| Symbol           | Parameter                                 | Conditions                      | Min | Typ | Max | Unit |
|------------------|-------------------------------------------|---------------------------------|-----|-----|-----|------|
| Per diode        |                                           |                                 |     |     |     |      |
| V <sub>RWM</sub> | reverse standoff voltage                  |                                 |     |     |     |      |
|                  | PESD3V3L4UF<br>PESD3V3L4UG<br>PESD3V3L4UW |                                 | -   | -   | 3.3 | V    |
|                  | PESD5V0L4UF<br>PESD5V0L4UG<br>PESD5V0L4UW |                                 | -   | -   | 5.0 | V    |
| C <sub>d</sub>   | diode capacitance                         | f = 1 MHz; V <sub>R</sub> = 0 V |     |     |     |      |
|                  | PESD3V3L4UF<br>PESD3V3L4UG<br>PESD3V3L4UW |                                 | -   | 22  | 28  | pF   |
|                  | PESD5V0L4UF<br>PESD5V0L4UG<br>PESD5V0L4UW |                                 | -   | 16  | 19  | pF   |

2. Pinning information

Table 3. Pinning

| Pin                      | Description       | Simplified outline                                                                   | Symbol                                                                                             |
|--------------------------|-------------------|--------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------|
| PESD3V3L4UF; PESD5V0L4UF |                   |                                                                                      |                                                                                                    |
| 1                        | cathode (diode 1) |  | <br>006aaa156 |
| 2                        | common anode      |                                                                                      |                                                                                                    |
| 3                        | cathode (diode 2) |                                                                                      |                                                                                                    |
| 4                        | cathode (diode 3) |                                                                                      |                                                                                                    |
| 5                        | common anode      |                                                                                      |                                                                                                    |
| 6                        | cathode (diode 4) |                                                                                      |                                                                                                    |
| PESD3V3L4UG; PESD5V0L4UG |                   |                                                                                      |                                                                                                    |
| 1                        | cathode (diode 1) |  | <br>006aaa157 |
| 2                        | common anode      |                                                                                      |                                                                                                    |
| 3                        | cathode (diode 2) |                                                                                      |                                                                                                    |
| 4                        | cathode (diode 3) |                                                                                      |                                                                                                    |
| 5                        | cathode (diode 4) |                                                                                      |                                                                                                    |
| PESD3V3L4UW; PESD5V0L4UW |                   |                                                                                      |                                                                                                    |
| 1                        | cathode (diode 1) |  | <br>006aaa157 |
| 2                        | common anode      |                                                                                      |                                                                                                    |
| 3                        | cathode (diode 2) |                                                                                      |                                                                                                    |
| 4                        | cathode (diode 3) |                                                                                      |                                                                                                    |
| 5                        | cathode (diode 4) |                                                                                      |                                                                                                    |

### 3. Ordering information

Table 4. Ordering information

| Type number | Package |                                                                                                            |         |
|-------------|---------|------------------------------------------------------------------------------------------------------------|---------|
|             | Name    | Description                                                                                                | Version |
| PESD3V3L4UF | XSON6   | plastic extremely thin small outline package;<br>no leads; 6 terminals; body $1 \times 1.45 \times 0.5$ mm | SOT886  |
| PESD5V0L4UF |         |                                                                                                            |         |
| PESD3V3L4UG | SC-88A  | plastic surface-mounted package; 5 leads                                                                   | SOT353  |
| PESD5V0L4UG |         |                                                                                                            |         |
| PESD3V3L4UW | -       | plastic surface-mounted package; 5 leads                                                                   | SOT665  |
| PESD5V0L4UW |         |                                                                                                            |         |

### 4. Marking

Table 5. Marking codes

| Type number | Marking code <sup>[1]</sup> |
|-------------|-----------------------------|
| PESD3V3L4UF | A5                          |
| PESD5V0L4UF | A6                          |
| PESD3V3L4UG | L1*                         |
| PESD5V0L4UG | L2*                         |
| PESD3V3L4UW | A2                          |
| PESD5V0L4UW | A1                          |

[1] \* = -: made in Hong Kong

\* = p: made in Hong Kong

\* = t: made in Malaysia

\* = W: made in China

### 5. Limiting values

Table 6. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

| Symbol           | Parameter                                 | Conditions                   | Min                                                           | Max | Unit |
|------------------|-------------------------------------------|------------------------------|---------------------------------------------------------------|-----|------|
| <b>Per diode</b> |                                           |                              |                                                               |     |      |
| $P_{PP}$         | peak pulse power                          | $t_p = 8/20 \mu s$           | <a href="#">[1]</a> <a href="#">[2]</a> <a href="#">[3]</a> - | 30  | W    |
| $I_{PP}$         | peak pulse current                        | $t_p = 8/20 \mu s$           | <a href="#">[1]</a> <a href="#">[2]</a> <a href="#">[3]</a>   |     |      |
|                  | PESD3V3L4UF<br>PESD3V3L4UG<br>PESD3V3L4UW |                              | -                                                             | 3.0 | A    |
|                  | PESD5V0L4UF<br>PESD5V0L4UG<br>PESD5V0L4UW |                              | -                                                             | 2.5 | A    |
| $I_{FSM}$        | non-repetitive peak forward current       | square wave;<br>$t_p = 1$ ms | -                                                             | 3.5 | A    |

**Table 6.** Limiting values ...continued

In accordance with the Absolute Maximum Rating System (IEC 60134).

| Symbol            | Parameter                                     | Conditions                           | Min | Max  | Unit |
|-------------------|-----------------------------------------------|--------------------------------------|-----|------|------|
| $I_{ZSM}$         | non-repetitive peak reverse current           | square wave;<br>$t_p = 1 \text{ ms}$ |     |      |      |
|                   | PESD3V3L4UF<br>PESD3V3L4UG<br>PESD3V3L4UW     |                                      | -   | 0.9  | A    |
|                   | PESD5V0L4UF<br>PESD5V0L4UG<br>PESD5V0L4UW     |                                      | -   | 0.8  | A    |
| $P_{ZSM}$         | non-repetitive peak reverse power dissipation | square wave;<br>$t_p = 1 \text{ ms}$ | -   | 6    | W    |
| <b>Per device</b> |                                               |                                      |     |      |      |
| $T_j$             | junction temperature                          |                                      | -   | 150  | °C   |
| $T_{amb}$         | ambient temperature                           |                                      | -65 | +150 | °C   |
| $T_{stg}$         | storage temperature                           |                                      | -65 | +150 | °C   |

[1] Non-repetitive current pulse 8/20  $\mu\text{s}$  exponential decay waveform according to IEC 61000-4-5.

[2] For PESDxL4UF measured from pin 1, 3, 4 or 6 to pin 2 or 5.

[3] For PESDxL4UG and PESDxL4UW measured from pin 1, 3, 4 or 5 to pin 2.

**Table 7.** ESD maximum ratings $T_{amb} = 25^\circ\text{C}$  unless otherwise specified.

| Symbol           | Parameter                       | Conditions                           | Min         | Max | Unit |
|------------------|---------------------------------|--------------------------------------|-------------|-----|------|
| <b>Per diode</b> |                                 |                                      |             |     |      |
| $V_{ESD}$        | electrostatic discharge voltage | IEC 61000-4-2<br>(contact discharge) | [1][2][3] - | 20  | kV   |
|                  |                                 | MIL-STD-883 (human body model)       | -           | 10  | kV   |

[1] Device stressed with ten non-repetitive ESD pulses.

[2] For PESDxL4UF measured from pin 1, 3, 4 or 6 to pin 2 or 5.

[3] For PESDxL4UG and PESDxL4UW measured from pin 1, 3, 4 or 5 to pin 2.

**Table 8.** ESD standards compliance

| Standard                                | Conditions                      |
|-----------------------------------------|---------------------------------|
| <b>Per diode</b>                        |                                 |
| IEC 61000-4-2; level 4 (ESD)            | > 15 kV (air); > 8 kV (contact) |
| MIL-STD-883; class 3 (human body model) | > 4 kV                          |




Fig 1. 8/20  $\mu$ s pulse waveform according to IEC 61000-4-5




Fig 2. ESD pulse waveform according to IEC 61000-4-2

6. Characteristics

Table 9. Characteristics  
 $T_{amb} = 25\text{ }^{\circ}\text{C}$  unless otherwise specified.

| Symbol    | Parameter                                 | Conditions               | Min  | Typ | Max  | Unit |
|-----------|-------------------------------------------|--------------------------|------|-----|------|------|
| Per diode |                                           |                          |      |     |      |      |
| $V_{RWM}$ | reverse standoff voltage                  |                          |      |     |      |      |
|           | PESD3V3L4UF<br>PESD3V3L4UG<br>PESD3V3L4UW |                          | -    | -   | 3.3  | V    |
|           | PESD5V0L4UF<br>PESD5V0L4UG<br>PESD5V0L4UW |                          | -    | -   | 5.0  | V    |
| $I_{RM}$  | reverse leakage current                   |                          |      |     |      |      |
|           | PESD3V3L4UF<br>PESD3V3L4UG<br>PESD3V3L4UW | $V_{RWM} = 3.3\text{ V}$ | -    | 75  | 300  | nA   |
|           | PESD5V0L4UF<br>PESD5V0L4UG<br>PESD5V0L4UW | $V_{RWM} = 5.0\text{ V}$ | -    | 5   | 25   | nA   |
| $V_{BR}$  | breakdown voltage                         | $I_R = 1\text{ mA}$      |      |     |      |      |
|           | PESD3V3L4UF<br>PESD3V3L4UG<br>PESD3V3L4UW |                          | 5.32 | 5.6 | 5.88 | V    |
|           | PESD5V0L4UF<br>PESD5V0L4UG<br>PESD5V0L4UW |                          | 6.46 | 6.8 | 7.14 | V    |


**Table 9. Characteristics ...continued**  
 $T_{amb} = 25^{\circ}\text{C}$  unless otherwise specified.

| Symbol   | Parameter                                 | Conditions                                | Min                                                         | Typ | Max | Unit     |
|----------|-------------------------------------------|-------------------------------------------|-------------------------------------------------------------|-----|-----|----------|
| $C_d$    | diode capacitance                         | $f = 1\text{ MHz};$<br>$V_R = 0\text{ V}$ |                                                             |     |     |          |
|          | PESD3V3L4UF<br>PESD3V3L4UG<br>PESD3V3L4UW |                                           | -                                                           | 22  | 28  | pF       |
|          | PESD5V0L4UF<br>PESD5V0L4UG<br>PESD5V0L4UW |                                           | -                                                           | 16  | 19  | pF       |
|          | clamping voltage                          |                                           | <a href="#">[1]</a> <a href="#">[2]</a> <a href="#">[3]</a> |     |     |          |
|          | PESD3V3L4UF<br>PESD3V3L4UG<br>PESD3V3L4UW | $I_{PP} = 1\text{ A}$                     | -                                                           | -   | 8   | V        |
|          | PESD3V3L4UF<br>PESD3V3L4UG<br>PESD3V3L4UW | $I_{PP} = 3\text{ A}$                     | -                                                           | -   | 12  | V        |
| $V_{CL}$ | PESD5V0L4UF<br>PESD5V0L4UG<br>PESD5V0L4UW | $I_{PP} = 1\text{ A}$                     | -                                                           | -   | 10  | V        |
|          | PESD5V0L4UF<br>PESD5V0L4UG<br>PESD5V0L4UW | $I_{PP} = 2.5\text{ A}$                   | -                                                           | -   | 13  | V        |
|          | differential resistance                   | $I_R = 1\text{ mA}$                       |                                                             |     |     |          |
|          | PESD3V3L4UF<br>PESD3V3L4UG<br>PESD3V3L4UW |                                           | -                                                           | -   | 200 | $\Omega$ |
|          | PESD5V0L4UF<br>PESD5V0L4UG<br>PESD5V0L4UW |                                           | -                                                           | -   | 100 | $\Omega$ |
|          |                                           |                                           |                                                             |     |     |          |

[1] Non-repetitive current pulse 8/20  $\mu\text{s}$  exponential decay waveform according to IEC 61000-4-5.


[2] For PESDxL4UF measured from pin 1, 3, 4 or 6 to pin 2 or 5.

[3] For PESDxL4UG and PESDxL4UW measured from pin 1, 3, 4 or 5 to pin 2.




$T_{amb} = 25\text{ }^{\circ}\text{C}$   
(1) PESD3V3L4UF; PESD3V3L4UG; PESD3V3L4UW  
(2) PESD5V0L4UF; PESD5V0L4UG; PESD5V0L4UW

Fig 3. Non-repetitive peak reverse current as a function of pulse duration; maximum values



$T_{amb} = 25\text{ }^{\circ}\text{C}$   
(1) PESD3V3L4UF; PESD3V3L4UG; PESD3V3L4UW  
(2) PESD5V0L4UF; PESD5V0L4UG; PESD5V0L4UW

Fig 4. Non-repetitive peak reverse power dissipation as a function of pulse duration; maximum values



$f = 1\text{ MHz}; T_{amb} = 25\text{ }^{\circ}\text{C}$   
(1) PESD3V3L4UF; PESD3V3L4UG; PESD3V3L4UW  
(2) PESD5V0L4UF; PESD5V0L4UG; PESD5V0L4UW

Fig 5. Diode capacitance as a function of reverse voltage; typical values






Fig 6. Relative variation of reverse current as a function of junction temperature; typical values





**Fig 8. ESD clamping test setup and waveforms**

## 7. Application information

The devices are designed for the protection of up to four unidirectional data or signal lines from the damage caused by ESD and surge pulses. The devices may be used on lines where the signal polarities are both, positive and negative with respect to ground. The devices provide a surge capability of 30 W per line for an 8/20  $\mu$ s waveform each.





Fig 9. Application diagram

### Circuit board layout and protection device placement

Circuit board layout is critical for the suppression of ESD, Electrical Fast Transient (EFT) and surge transients. The following guidelines are recommended:

1. Place the device as close to the input terminal or connector as possible.
2. The path length between the device and the protected line should be minimized.
3. Keep parallel signal paths to a minimum.
4. Avoid running protected conductors in parallel with unprotected conductors.
5. Minimize all Printed-Circuit Board (PCB) conductive loops including power and ground loops.
6. Minimize the length of the transient return path to ground.
7. Avoid using shared transient return paths to a common ground point.
8. Ground planes should be used whenever possible. For multilayer PCBs, use ground vias.

8. Package outline




9. Packing information

Table 10. Packing methods  
The indicated -xxx are the last three digits of the 12NC ordering code.<sup>[1]</sup>

| Type number | Package | Description                        | Packing quantity    |      |      |      |       |
|-------------|---------|------------------------------------|---------------------|------|------|------|-------|
|             |         |                                    | 3000                | 4000 | 5000 | 8000 | 10000 |
| PESD3V3L4UF | SOT886  | 4 mm pitch, 8 mm tape and reel; T1 | <sup>[2]</sup> -    | -    | -115 | -    | -     |
|             |         | 4 mm pitch, 8 mm tape and reel; T4 | <sup>[3]</sup> -    | -    | -132 | -    | -     |
| PESD5V0L4UF | SOT886  | 4 mm pitch, 8 mm tape and reel; T1 | <sup>[2]</sup> -    | -    | -115 | -    | -     |
|             |         | 4 mm pitch, 8 mm tape and reel; T4 | <sup>[3]</sup> -    | -    | -132 | -    | -     |
| PESD3V3L4UG | SOT353  | 4 mm pitch, 8 mm tape and reel; T1 | <sup>[2]</sup> -115 | -    | -    | -    | -135  |
|             |         | 4 mm pitch, 8 mm tape and reel; T2 | <sup>[4]</sup> -125 | -    | -    | -    | -165  |
| PESD5V0L4UG | SOT353  | 4 mm pitch, 8 mm tape and reel; T1 | <sup>[2]</sup> -115 | -    | -    | -    | -135  |
|             |         | 4 mm pitch, 8 mm tape and reel; T2 | <sup>[4]</sup> -125 | -    | -    | -    | -165  |
| PESD3V3L4UW | SOT665  | 2 mm pitch, 8 mm tape and reel     | -                   | -    | -    | -315 | -     |
|             |         | 4 mm pitch, 8 mm tape and reel     | -                   | -115 | -    | -    | -     |
| PESD5V0L4UW | SOT665  | 2 mm pitch, 8 mm tape and reel     | -                   | -    | -    | -315 | -     |
|             |         | 4 mm pitch, 8 mm tape and reel     | -                   | -115 | -    | -    | -     |

- [1] For further information and the availability of packing methods, see [Section 13](#).  
[2] T1: normal taping  
[3] T4: 90° rotated reverse taping  
[4] T2: reverse taping

10. Soldering






Fig 14. Reflow soldering footprint PESDxL4UG (SOT353/SC-88A)





Fig 15. Wave soldering footprint PESDxL4UG (SOT353/SC-88A)



## 11. Revision history

Table 11. Revision history

| Document ID        | Release date                                                                 | Data sheet status     | Change notice | Supersedes                            |
|--------------------|------------------------------------------------------------------------------|-----------------------|---------------|---------------------------------------|
| PESDXL4UF_G_W_4    | 20080228                                                                     | Product data sheet    | -             | PESDXL4UF_G_W_3                       |
| Modifications:     | • <a href="#">Figure 8 “ESD clamping test setup and waveforms”</a> : amended |                       |               |                                       |
| PESDXL4UF_G_W_3    | 20080114                                                                     | Product data sheet    | -             | PESDXL4UW_SER_2<br>PESDXL4UG_SERIES_1 |
| PESDXL4UW_SER_2    | 20040406                                                                     | Product specification | -             | PESDXL4UW_SERIES_1                    |
| PESDXL4UG_SERIES_1 | 20040323                                                                     | Product specification | -             | -                                     |

## 12. Legal information

### 12.1 Data sheet status

| Document status <sup>[1][2]</sup> | Product status <sup>[3]</sup> | Definition                                                                            |
|-----------------------------------|-------------------------------|---------------------------------------------------------------------------------------|
| Objective [short] data sheet      | Development                   | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet    | Qualification                 | This document contains data from the preliminary specification.                       |
| Product [short] data sheet        | Production                    | This document contains the product specification.                                     |

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nexperia.com>.

### 12.2 Definitions

**Draft** — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

**Short data sheet** — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

### 12.3 Disclaimers

**General** — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

**Right to make changes** — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

**Suitability for use** — Nexperia products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or

malfunction of a Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia accepts no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

**Applications** — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

**Limiting values** — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

**Terms and conditions of sale** — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nexperia.com/profile/terms>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by Nexperia. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

**No offer to sell or license** — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

### 12.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

## 13. Contact information

For additional information, please visit: <http://www.nexperia.com>

For sales office addresses, send an email to: [salesaddresses@nexperia.com](mailto:salesaddresses@nexperia.com)

## 14. Contents

---

|           |                                          |           |
|-----------|------------------------------------------|-----------|
| <b>1</b>  | <b>Product profile</b> . . . . .         | <b>1</b>  |
| 1.1       | General description. . . . .             | 1         |
| 1.2       | Features . . . . .                       | 1         |
| 1.3       | Applications . . . . .                   | 1         |
| 1.4       | Quick reference data. . . . .            | 2         |
| <b>2</b>  | <b>Pinning information</b> . . . . .     | <b>2</b>  |
| <b>3</b>  | <b>Ordering information</b> . . . . .    | <b>3</b>  |
| <b>4</b>  | <b>Marking</b> . . . . .                 | <b>3</b>  |
| <b>5</b>  | <b>Limiting values</b> . . . . .         | <b>3</b>  |
| <b>6</b>  | <b>Characteristics</b> . . . . .         | <b>5</b>  |
| <b>7</b>  | <b>Application information</b> . . . . . | <b>10</b> |
| <b>8</b>  | <b>Package outline</b> . . . . .         | <b>11</b> |
| <b>9</b>  | <b>Packing information</b> . . . . .     | <b>12</b> |
| <b>10</b> | <b>Soldering</b> . . . . .               | <b>12</b> |
| <b>11</b> | <b>Revision history</b> . . . . .        | <b>15</b> |
| <b>12</b> | <b>Legal information</b> . . . . .       | <b>16</b> |
| 12.1      | Data sheet status . . . . .              | 16        |
| 12.2      | Definitions . . . . .                    | 16        |
| 12.3      | Disclaimers . . . . .                    | 16        |
| 12.4      | Trademarks. . . . .                      | 16        |
| <b>13</b> | <b>Contact information</b> . . . . .     | <b>16</b> |
| <b>14</b> | <b>Contents</b> . . . . .                | <b>17</b> |