

UPWMiniature Sized, Low Impedance,
High Reliability For
Switching Power Supplies

Smaller





Low Impedance



Long Life

Anti-Solvent
Feature
(Through
100V only)



- Smaller case size and lower impedance than UPM.
- Low impedance and high reliability withstanding 2000 hours to 8000 hours.
- Capacitance ranges available based on the numerical values in E12 series under JIS.
- Compliant to the RoHS directive (2011/65/EU).



Specifications

Item	Performance Characteristics																						
Category Temperature Range	−55 to +105°C (6.3 to 100V), −40 to + 105°C (160 to 400V), −25 to +105°C (450V)																						
Rated Voltage Range	6.3 to 450V																						
Rated Capacitance Range	0.47 to 15000μF																						
Capacitance Tolerance	±20% at 120Hz, 20°C																						
Leakage Current	Rated voltage (V)	6.3 to 100						160 to 450															
	Leakage current	After 1 minute's application of rated voltage at 20°C, leakage current is not more than 0.03CV or 4 (μA), whichever is greater.						CV ≤ 1000: I = 0.1CV+40 (μA) max. CV > 1000: I = 0.04CV+100 (μA) max.															
Tangent of loss angle (tan δ)	For capacitance of more than 1000μF, add 0.02 for every increase of 1000μF. Measurement frequency : 120Hz at 20°C																						
	Rated voltage (V)	6.3	10	16	25	35	50	63	100	160 to 250	315 · 350	400 · 450											
	tan δ (MAX.)	0.22	0.19	0.16	0.14	0.12	0.10	0.09	0.08	0.15	0.20	0.25											
Stability at Low Temperature	120Hz																						
	Rated voltage (V)			6.3 · 10	16 · 25	35 · 50	63 · 100	160 · 200	250	315 · 350	400	450											
	Impedance ratio (MAX.)	Z−25°C / Z+20°C			—	—	—	—	3	3	4	6	15										
		Z−40°C / Z+20°C			—	—	—	—	4	6	8	10	—										
			Z−55°C / Z+20°C			3	3	3	3	—	—	—	—										
Endurance	The specifications listed at right shall be met when the capacitors are restored to 20°C after D.C. bias plus rated ripple current is applied for 8000 hours (2000 hours for φD=4, 5 and 6.3, 3000 hours for φD=8, 5000 hours for φD=10, 7000 hours for φD=12.5) at 105°C, the peak voltage shall not exceed the rated voltage.																						
													Capacitance change	Within ±20% of the initial capacitance value									
													tan δ	200% or less than the initial specified value									
Shelf Life	After storing the capacitors under no load at 105°C for 1000 hours and then performing voltage treatment based on JIS C 5101-4 clause 4.1 at 20°C, they shall meet the specified values for the endurance characteristics listed above.																						
													Leakage current	Less than or equal to the initial specified value									
Marking	Printed with white color letter on dark brown sleeve.																						


Radial Lead Type



α		(mm)													
		ϕD	4	5	6.3	8	10	12.5	16	18	20	22	25		
		P	1.5	2.0	2.5	3.5	5.0	5.0	7.5	7.5	10.0	10.0	12.5		
β		ϕd	0.45	0.5 (0.45)	0.5 (0.45)	0.6	0.6	0.6 ※0.8	0.8	0.8	1.0	1.0	1.0		
		β	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	1.0	1.0		

※: Applied to L>25 products
(): Applied to 7mmL products

Type numbering system (Example : 10V 680µF)



※ Configuration

φ D	Pb-free leadwire Pb-free PET sleeve
4 · 5	DD
6.3	ED (7mm L : DD)
8 · 10	PD
12.5 to 18	HD
20 to 25	RD

• Please refer to page 20 about the end seal configuration.

Frequency coefficient of rated ripple current

V	Cap. (µF)	Frequency	50Hz	120Hz	300Hz	1kHz	10kHz or more
6.3 to 100	2.2 to 56		0.20	0.30	0.50	0.80	1.00
	68 to 330		0.55	0.65	0.75	0.85	1.00
	390 to 1000		0.70	0.75	0.80	0.90	1.00
	1200 to 15000		0.80	0.85	0.90	0.95	1.00
160 to 450	0.47 to 220		0.80	1.00	1.25	1.40	1.60
	330 to 470		0.90	1.00	1.10	1.13	1.15

Please refer to page 20, 21, 22 about the formed or taped product spec.
Please refer to page 4 for the minimum order quantity.

● Dimension table in next page.

UPW

■ Standard Ratings

V (Code) Cap.(μF) Code		Item	6.3 (0J)				10 (1A)			
			Case size φD × L (mm)	Impedance (Ω) MAX.		Rated ripple (mA rms) 105°C / 100kHz	Case size φD × L (mm)	Impedance (Ω) MAX.		Rated ripple (mA rms) 105°C / 100kHz
				20°C / 100kHz	−10°C / 100kHz			20°C / 100kHz	−10°C / 100kHz	
22	220	5 × 11	0.60	1.20	180	5 × 11 ▲ 4 × 7	0.60 2.00	1.20 5.00	180 65	
27	270	4 × 7	2.00	5.00	65					
33	330	5 × 11	0.60	1.20	180	5 × 11	0.60	1.20	180	
		▲ 5 × 7	0.95	2.40	120	▲ 5 × 7	0.95	2.40	120	
39	390					5 × 7	0.95	2.40	120	
47	470	5 × 11	0.60	1.20	180	5 × 11	0.60	1.20	180	
		▲ 5 × 7	0.95	2.40	120	▲ 4 × 11	1.30	2.60	120	
56	560	5 × 7	0.95	2.40	120					
68	680	4 × 11	1.30	2.60	120					
82	820					5 × 11 ▲ 6.3 × 7	0.60 0.45	1.20 1.20	180 200	
						5 × 11 ▲ 5 × 15	0.60 0.50	1.20 1.00	180 235	
120	121	6.3 × 7	0.45	1.20	200					
150	151	6.3 × 11	0.25	0.50	290					
		▲ 5 × 15	0.50	1.00	235	6.3 × 11	0.25	0.50	290	
180	181					6.3 × 11	0.25	0.50	290	
220	221	6.3 × 11	0.25	0.50	290	6.3 × 11	0.25	0.50	290	
						▲ 6.3 × 15	0.23	0.46	430	
330	331	6.3 × 11	0.25	0.50	290					
		▲ 6.3 × 15	0.23	0.46	430	8 × 11.5	0.117	0.234	555	
470	471	8 × 11.5	0.117	0.234	555	8 × 11.5	0.117	0.234	555	
560	561	8 × 11.5	0.117	0.234	555					
680	681	10 × 12.5	0.090	0.180	755	10 × 12.5	0.090	0.180	760	
						▲ 8 × 15	0.085	0.170	730	
820	821	8 × 15	0.085	0.170	730					
		▲ 10 × 12.5	0.090	0.180	755					
1000	102	10 × 12.5	0.090	0.180	755	10 × 16	0.068	0.136	1050	
						▲ 8 × 20	0.065	0.130	995	
1200	122	8 × 20	0.065	0.130	995	10 × 20	0.052	0.104	1220	
		▲ 10 × 16	0.068	0.136	1050					
1500	152	10 × 20	0.052	0.104	1220	10 × 20	0.052	0.104	1220	
						▲ 10 × 25	0.045	0.090	1440	
2200	222	12.5 × 20	0.038	0.076	1655	12.5 × 20	0.038	0.076	1655	
		▲ 10 × 25	0.045	0.090	1440	▲ 10 × 31.5	0.035	0.070	1815	
2700	272	10 × 31.5	0.035	0.070	1815	12.5 × 25	0.030	0.060	1945	
3300	332	12.5 × 20	0.038	0.076	1655	12.5 × 25	0.030	0.060	1950	
						▲ 12.5 × 31.5	0.025	0.050	2310	
3900	392	12.5 × 25	0.030	0.060	1945	12.5 × 35.5	0.022	0.044	2510	
						▲ 16 × 20	0.029	0.058	2210	
4700	472	16 × 25	0.022	0.044	2555	16 × 25	0.022	0.044	2555	
		▲ 12.5 × 31.5	0.025	0.050	2310					
5600	562	12.5 × 35.5	0.022	0.044	2510	16 × 25	0.022	0.044	2560	
		▲ 16 × 20	0.029	0.058	2210	▲ 18 × 20	0.028	0.056	2490	
6800	682	16 × 25	0.022	0.044	2560	16 × 31.5	0.018	0.036	3010	
		▲ 18 × 20	0.028	0.056	2490	▲ 18 × 25	0.020	0.040	2740	
8200	822	16 × 31.5	0.018	0.036	3010	16 × 35.5	0.016	0.032	3150	
						▲ 18 × 31.5	0.016	0.032	3635	
10000	103	16 × 31.5	0.016	0.032	3150	18 × 35.5	0.015	0.030	3680	
		▲ 18 × 25	0.020	0.040	2740					
12000	123	18 × 31.5	0.016	0.032	3635					
15000	153	18 × 35.5	0.015	0.030	3680	18 × 40	0.014	0.028	3800	

▲ : In this case, [6] will be put at 12th digit of type numbering system.

UPW

■ Standard Ratings

Cap. (μF)	V(Code)	Item Code	16 (1C)			25 (1E)			
			Case size φD × L (mm)	Impedance (Ω) MAX.		Case size φD × L (mm)	Impedance (Ω) MAX.		Rated ripple (mArms) 105°C / 100kHz
				20°C / 100kHz	-10°C / 100kHz		20°C / 100kHz	-10°C / 100kHz	
4.7	4R7					5 × 11	0.60	1.20	180
10	100		5 × 11	0.60	1.20	5 × 11	0.60	1.20	180
						▲4 × 7	2.00	5.00	65
15	150		4 × 7	2.00	5.00				
22	220		5 × 11	0.60	1.20	5 × 11	0.60	1.20	180
			▲5 × 7	0.95	2.40	▲5 × 7	0.95	2.40	120
27	270		5 × 7	0.95	2.40	4 × 11	1.30	2.60	120
33	330		5 × 11	0.60	1.20				
			▲6.3 × 7	0.45	1.20	5 × 11	0.60	1.20	180
39	390		4 × 11	1.30	2.60	5 × 11	0.60	1.20	180
						▲6.3 × 7	0.45	1.20	200
47	470		5 × 11	0.60	1.20	5 × 11	0.60	1.20	180
56	560		5 × 11	0.60	1.20				
			▲6.3 × 7	0.45	1.20	5 × 15	0.50	1.00	235
82	820		5 × 15	0.50	1.00	6.3 × 11	0.25	0.50	290
100	101		6.3 × 11	0.25	0.50	6.3 × 11	0.25	0.50	290
120	121		6.3 × 11	0.25	0.50	6.3 × 15	0.23	0.46	430
150	151		6.3 × 11	0.25	0.50	8 × 11.5	0.117	0.234	555
180	181		6.3 × 15	0.23	0.46				
220	221		8 × 11.5	0.117	0.234	8 × 11.5	0.117	0.234	555
330	331		8 × 11.5	0.117	0.234	10 × 12.5	0.090	0.180	760
						▲8 × 15	0.085	0.170	730
470	471		10 × 12.5	0.090	0.180	10 × 16	0.068	0.136	1050
			▲8 × 15	0.085	0.170	▲8 × 20	0.065	0.130	995
560	561					10 × 20	0.052	0.104	1220
680	681		10 × 16	0.068	0.136	10 × 20	0.052	0.104	1220
			▲8 × 20	0.065	0.130				
820	821		10 × 20	0.052	0.104	10 × 25	0.045	0.090	1440
1000	102		10 × 20	0.052	0.104	12.5 × 20	0.038	0.076	1660
						▲10 × 31.5	0.035	0.070	1815
1200	122		10 × 25	0.045	0.090				
1500	152		12.5 × 20	0.038	0.076	16 × 25	0.022	0.044	2555
			▲10 × 31.5	0.035	0.070	▲12.5 × 25	0.030	0.060	1950
1800	182					12.5 × 31.5	0.025	0.050	2310
						▲16 × 20	0.029	0.058	2210
2200	222		12.5 × 25	0.030	0.060	16 × 25	0.022	0.044	2555
						▲18 × 20	0.028	0.056	2490
						※12.5 × 35.5	0.022	0.044	2510
2700	272		12.5 × 31.5	0.025	0.050	16 × 25	0.022	0.044	2555
			▲16 × 20	0.029	0.058				
3300	332		16 × 25	0.022	0.044	16 × 31.5	0.018	0.036	3010
			▲12.5 × 35.5	0.022	0.044	▲18 × 25	0.020	0.040	2740
3900	392		16 × 25	0.022	0.044	16 × 35.5	0.016	0.032	3150
			▲18 × 20	0.028	0.056	▲18 × 31.5	0.016	0.032	3635
4700	472		16 × 31.5	0.018	0.036	18 × 35.5	0.015	0.030	3680
			▲18 × 25	0.020	0.040				
5600	562		16 × 35.5	0.016	0.032				
			▲18 × 31.5	0.016	0.032				
6800	682		18 × 35.5	0.015	0.030	18 × 40	0.014	0.028	3800
8200	822		18 × 35.5	0.015	0.030				
10000	103		18 × 40	0.014	0.028				

▲ : In this case, [6] will be put at 12th digit of type numbering system.

※ : In this case, [3] will be put at 12th digit of type numbering system.

UPW

■ Standard Ratings

V(Code)		Item Code	35 (1V)				50 (1H)			
Cap. (μF)	Case size φD × L (mm)		Impedance (Ω) MAX.		Rated ripple (mA _{rms}) 105°C / 100kHz	Case size φD × L (mm)	Impedance (Ω) MAX.		Rated ripple (mA _{rms}) 105°C / 100kHz	
			20°C / 100kHz	−10°C / 100kHz			20°C / 100kHz	−10°C / 100kHz		
2.2	2R2					5 × 11	3.00	6.00	55	
3.3	3R3					5 × 11	2.60	5.20	65	
4.7	4R7		5 × 11	0.60	1.20	180	5 × 11	2.30	4.60	
6.8	6R8		4 × 7	2.00	5.00	65			90	
10	100	5 × 11	0.60	1.20	180	5 × 11	1.40	2.80	120	
		▲ 5 × 7	0.95	2.40	120	▲ 4 × 11	2.50	5.00	90	
12	120	5 × 7	0.95	2.40	120					
18	180	4 × 11	1.30	2.60	120	5 × 11	1.30	2.60	155	
22	220	5 × 11	0.60	1.20	180	5 × 11	1.20	2.40	170	
27	270	5 × 11	0.60	1.20	180					
		▲ 6.3 × 7	0.45	1.20	200	5 × 15	0.90	1.80	215	
33	330	5 × 11	0.60	1.20	180	6.3 × 11	0.43	0.86	300	
39	390	5 × 15	0.50	1.00	235					
47	470	6.3 × 11	0.25	0.50	290	6.3 × 11	0.43	0.86	300	
56	560	6.3 × 11	0.25	0.50	290	6.3 × 15	0.40	0.80	360	
82	820	6.3 × 15	0.23	0.46	430	8 × 11.5	0.234	0.468	485	
100	101	8 × 11.5	0.117	0.234	555	8 × 11.5	0.234	0.468	485	
120	121					8 × 15	0.155	0.310	635	
						▲ 10 × 12.5	0.162	0.324	620	
150	151	8 × 11.5	0.117	0.234	555	10 × 12.5	0.162	0.324	615	
180	181					8 × 20	0.120	0.240	860	
						▲ 10 × 16	0.119	0.238	850	
220	221	10 × 12.5	0.090	0.180	760	10 × 16	0.119	0.238	850	
		▲ 8 × 15	0.085	0.170	730	▲ 10 × 20	0.090	0.180	1030	
270	271					10 × 25	0.082	0.164	1200	
330	331	10 × 16	0.068	0.136	1050	10 × 20	0.090	0.180	1030	
		▲ 8 × 20	0.065	0.130	995	▲ 10 × 31.5	0.060	0.120	1610	
390	391	10 × 20	0.052	0.104	1220	12.5 × 20	0.063	0.126	1480	
470	471	10 × 20	0.052	0.104	1220	12.5 × 20	0.060	0.120	1500	
560	561	10 × 25	0.045	0.090	1440	12.5 × 25	0.050	0.100	1832	
680	681	12.5 × 20	0.038	0.076	1660	12.5 × 25	0.050	0.100	1840	
		▲ 10 × 31.5	0.035	0.070	1815	▲ 16 × 20	0.048	0.096	1840	
820	821					12.5 × 35.5	0.034	0.068	2290	
						▲ 18 × 20	0.042	0.084	2420	
1000	102	12.5 × 25	0.030	0.060	1950	16 × 25	0.034	0.068	2235	
1200	122	12.5 × 31.5	0.025	0.050	2310	16 × 31.5	0.028	0.056	2700	
		▲ 16 × 20	0.029	0.058	2210	▲ 18 × 25	0.029	0.058	2610	
1500	152	16 × 25	0.022	0.044	2555	16 × 31.5	0.028	0.056	2700	
		▲ 12.5 × 35.5	0.022	0.044	2510	▲ 16 × 35.5	0.025	0.050	2790	
1800	182	16 × 25	0.022	0.044	2555					
		▲ 18 × 20	0.028	0.056	2490	18 × 31.5	0.025	0.050	3000	
2200	222	16 × 31.5	0.018	0.036	3010					
		▲ 18 × 25	0.020	0.040	2740	18 × 35.5	0.023	0.046	3100	
2700	272	16 × 35.5	0.016	0.032	3150					
		▲ 18 × 31.5	0.016	0.032	3635					
3300	332	18 × 35.5	0.015	0.030	3680					
4700	472	18 × 40	0.014	0.028	3800					

▲ : In this case, [6] will be put at 12th digit of type numbering system.

UPW

■ Standard Ratings

Cap.(μF)	V(Code) Item Code	63 (1J)				100 (2A)			
		Case size φD × L (mm)	Impedance (Ω) MAX.		Rated ripple (mArms) 105°C / 100kHz	Case size φD × L (mm)	Impedance (Ω) MAX.		Rated ripple (mArms) 105°C / 100kHz
			20°C / 100kHz	-10°C / 100kHz			20°C / 100kHz	-10°C / 100kHz	
2.2	2R2					5 × 11	9.80	19.6	44
3.3	3R3					5 × 11	6.60	13.2	58
4.7	4R7	5 × 11	4.70	9.40	68	5 × 11	4.60	9.20	74
6.8	6R8	5 × 11	2.50	5.00	95	5 × 11	3.50	7.00	95
		▲ 4 × 11	3.50	7.00	80				
10	100	5 × 11	2.10	4.20	110	6.3 × 11	1.80	3.60	130
12	120	5 × 11	2.00	4.00	145				
15	150	6.3 × 11	1.20	2.40	160	8 × 11.5	0.83	1.66	180
18	180	5 × 15	1.30	2.60	200	6.3 × 15	0.80	1.60	200
22	220	6.3 × 11	0.71	1.42	250	8 × 11.5	0.68	1.36	230
33	330	6.3 × 11	0.71	1.42	250	10 × 12.5	0.46	0.92	320
		▲ 8 × 15				▲ 8 × 15	0.45	0.90	360
39	390	6.3 × 15	0.70	1.40	330				
47	470	8 × 11.5	0.342	0.684	405	10 × 16	0.37	0.74	420
						▲ 8 × 20	0.37	0.74	420
68	680	8 × 11.5	0.342	0.684	405	10 × 20	0.30	0.60	490
82	820					10 × 25	0.25	0.50	540
100	101	10 × 12.5	0.256	0.512	540	12.5 × 20	0.18	0.36	580
		▲ 8 × 15	0.230	0.460	535				
120	121	10 × 16	0.194	0.388	600				
150	151	10 × 16	0.194	0.388	660	12.5 × 25	0.13	0.26	710
180	181	10 × 20	0.147	0.294	890	12.5 × 31.5	0.12	0.24	790
		▲ 12.5 × 15	0.150	0.300	1020	▲ 16 × 20	0.13	0.26	750
220	221	10 × 20	0.147	0.294	885	16 × 25	0.10	0.20	890
		▲ 10 × 25	0.130	0.260	1050	▲ 18 × 20	0.11	0.22	850
270	271	16 × 15	0.090	0.180	1410				
330	331	12.5 × 20	0.085	0.170	1290	16 × 25	0.090	0.18	1080
390	391	12.5 × 25	0.070	0.140	1720	18 × 25	0.083	0.166	1260
		▲ 18 × 15	0.086	0.172	1690				
470	471	12.5 × 25	0.070	0.140	1720	16 × 31.5	0.076	0.152	1310
		▲ 12.5 × 31.5	0.055	0.110	2090				
		※ 16 × 20	0.059	0.118	1770				
560	561					18 × 31.5	0.068	0.136	1370
680	681	16 × 25	0.050	0.100	2160	16 × 35.5	0.064	0.128	1410
		▲ 12.5 × 35.5	0.047	0.094	2270				
		※ 18 × 20	0.055	0.110	2290				
820	821	16 × 31.5	0.043	0.086	2670				
		▲ 18 × 25	0.043	0.086	2590				
1000	102	16 × 31.5	0.043	0.086	2770	18 × 40	0.047	0.094	1520
		▲ 16 × 35.5	0.036	0.072	2770				
1200	122	18 × 31.5	0.032	0.064	2950				
1500	152	18 × 35.5	0.030	0.060	3100				
2200	222	18 × 40	0.028	0.056	3200				

▲ : In this case, [6] will be put at 12th digit of type numbering system.

※ : In this case, [3] will be put at 12th digit of type numbering system.

Cap. (μF)	V(Code) Code	160		200		250		315		350		400		450	
		2C		2D		2E		2F		2V		2G		2W	
0.47	R47	6.3 × 11	12	6.3 × 11	12	6.3 × 11	12	8 × 11.5	11	8 × 11.5	11				
1	010	6.3 × 11	17	6.3 × 11	17	6.3 × 11	17	8 × 11.5	16	10 × 12.5	17	10 × 12.5	16	10 × 12.5	18
2.2	2R2	6.3 × 11	25	6.3 × 11	25	8 × 11.5	29	10 × 12.5	28	10 × 16	31	10 × 16	27	10 × 20	29
3.3	3R3	8 × 11.5	36	8 × 11.5	36	10 × 12.5	42	10 × 12.5	34	10 × 16	38	10 × 20	36	12.5 × 20	41
4.7	4R7	8 × 11.5	43	10 × 12.5	50	10 × 12.5	50	10 × 16	45	10 × 20	49	10 × 20	43	12.5 × 20	49
10	100	10 × 12.5	70	10 × 16	80	10 × 20	88	10 × 20	72	12.5 × 20	82	12.5 × 25	72	16 × 25	75
22	220	10 × 20	130	10 × 20	140	12.5 × 25	155	12.5 × 25	120	16 × 25	130	16 × 25	110	16 × 31.5	115
33	330	12.5 × 20	180	12.5 × 25	190	12.5 × 25	190	16 × 25	155	16 × 31.5	160	16 × 31.5	140	● 18 × 35.5	145
47	470	12.5 × 25	220	12.5 × 25	220	16 × 25	230	16 × 35.5	190	● 18 × 35.5	200	● 18 × 35.5	170	20 × 40	175
100	101	16 × 25	330	16 × 31.5	335	● 18 × 35.5	340	▲ 18 × 40	285	20 × 40	290	22 × 50	350	25 × 50	350
220	221	● 18 × 35.5	500	▲ 18 × 40	515	20 × 40	525	22 × 50	540	25 × 50	550				
330	331	20 × 40	900	22 × 40	1100	22 × 50	1150								
470	471	22 × 50	1200	22 × 50	1310	25 × 50	1350								

※1 Rated ripple current (mArms) at 105°C 120Hz

Size φ20 × 31 is available for capacitors marked "●"

Size φ20 × 35 is available for capacitors marked "▲"

In this case, [6] will be put at 12th digit of type numbering system.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Nichicon:

[UPW2D470MHD1TO](#) [UPW2D330MHD1TO](#) [UPW2D2R2MED1TD](#) [UPW2D220MPD1TD](#) [UPW2D100MPD1TD](#)
[UPW2DR47MED1TD](#) [UPW2D3R3MPD1TD](#) [UPW2CR47MED](#) [UPW1A101MDD](#) [UPW1C221MPD1TA](#)
[UPW1V471MPD1TD](#) [UPW1C471MPD](#) [UPW1J681MHD3](#) [UPW1J821MHD6](#) [UPW1E560MDD1TD](#)
[UPW1C102MPD1TD](#) [UPW1J4R7MDD](#) [UPW1H181MPD1TD](#) [UPW1E272MHD1DU](#) [UPW1C332MHD](#)
[UPW1C100MDD1TD](#) [UPW1E182MHD6TN](#) [UPW0J270MDD](#) [UPW1J391MHD6](#) [UPW1H821MHD6](#)
[UPW2G100MHD1TO](#) [UPW1J120MDD](#) [UPW2W2R2MPD1TD](#) [UPW0J472MHD](#) [UPW1H101MPD1TA](#)
[UPW2A470MPD](#) [UPW1C682MHD](#) [UPW1V122MHD6](#) [UPW2E220MHD](#) [UPW2V3R3MPD](#) [UPW2A010MDD1TD](#)
[UPW2C101MHD](#) [UPW1H2R2MDD](#) [UPW1H270MDD](#) [UPW0J682MHD6](#) [UPW2F4R7MPD](#) [UPW2C3R3MPD](#)
[UPW2F010MPD1TD](#) [UPW1H820MPD1TD](#) [UPW2F2R2MPD](#) [UPW1E152MHD6](#) [UPW1H010MDD](#) [UPW1V272MHD6](#)
[UPW1J121MPD](#) [UPW2A100MED](#) [UPW2A181MHD6](#) [UPW1H220MDD1TA](#) [UPW1V332MHD](#) [UPW1C181MED1TD](#)
[UPW0J470MDD6TP](#) [UPW1A122MPD](#) [UPW2V330MHD](#) [UPW1A472MHD](#) [UPW1C220MDD6TP](#) [UPW1C332MHD6](#)
[UPW1V390MDD](#) [UPW1A220MDD](#) [UPW2C3R3MPD1TD](#) [UPW0J682MHD](#) [UPW2A4R7MDD](#) [UPW2F4R7MPD1TD](#)
[UPW2C010MED](#) [UPW1V560MED1TD](#) [UPW1E560MDD](#) [UPW1A471MPD](#) [UPW2C101MHD1TN](#) [UPW2C2R2MED](#)
[UPW1V221MPD](#) [UPW1V122MHD](#) [UPW1H560MED1TD](#) [UPW2A100MED1TD](#) [UPW1V390MDD1TD](#) [UPW2C470MHD](#)
[UPW0J471MPD1TD](#) [UPW2F470MHD](#) [UPW2G220MHD](#) [UPW0J682MHD6TN](#) [UPW1J181MPD](#) [UPW1V182MHD6](#)
[UPW1C331MPD1TD](#) [UPW1H221MPD1TD](#) [UPW1A222MHD1TO](#) [UPW1A471MPD1TD](#) [UPW1J4R7MDD1TD](#)
[UPW1J470MPD](#) [UPW1V331MPD](#) [UPW1V6R8MDD1TP](#) [UPW2E471MRD](#) [UPW1C471MPD6TD](#) [UPW1V182MHD](#)
[UPW2V2R2MPD](#) [UPW1V102MHD](#) [UPW2D331MRD](#) [UPW2E3R3MPD1TD](#) [UPW1J180MDD](#)