

General Specifications

Electrical Capacity (Resistive Load)

Logic Level: 0.4VA maximum @ 28V AC/DC maximum
(Applicable Range 0.1mA ~ 0.1A @ 20mV ~ 28V)
Note: Find additional explanation of operating range in Supplement section.

Other Ratings

Contact Resistance: 80 milliohms maximum
Insulation Resistance: 500 megohms minimum @ 500V DC
Dielectric Strength: 500V AC minimum for 1 minute minimum
Mechanical Life: 100,000 operations minimum
Electrical Life: 100,000 operations minimum
10,000 operations minimum @ 0.1A @ 28V AC/DC
Nominal Operating Force: 1.30N
Angle of Throw: 28°

Materials & Finishes

Actuator: Polyamide
Case: Glass fiber reinforced polyamide
Sealing Rings: Nitrile butadiene rubber
Movable Contacts: Phosphor bronze with gold plating
Stationary Contacts: Phosphor bronze with gold plating
Base: Glass fiber reinforced polyamide
Power Terminals: Phosphor bronze with gold plating
Lamp Terminals: Phosphor bronze with gold plating

Environmental Data

Operating Temperature Range: -25°C through +55°C (-13°F through +131°F)
Humidity: 90 ~ 95% humidity for 240 hours @ 40°C (104°F)
Vibration: 10 ~ 500Hz with peak-to-peak amplitude of 1.5mm traversing the frequency range & returning in 1 minute; 3 right angled directions for 2 hours
Shock: 50G (490m/s²) acceleration (tested in 6 right angled directions, with 5 shocks in each direction)

PCB Processing

Soldering: Wave Soldering recommended. See Profile A in Supplement section.
Manual Soldering: See Profile A in Supplement section.
Cleaning: Automated cleaning. See Cleaning specifications in Supplement section.

Standards & Certifications

The G Series toggles have not been tested for UL recognition or CSA certification.
These switches are designed for use in a low-voltage, low-current, logic-level circuit.
When used as intended in a logic-level circuit, the results do not produce hazardous energy.

Distinctive Characteristics

Fully illuminated toggle for highly visible status indication with LED in red, green, or amber for single color and red/green for bicolor.


Ultra-miniature size allows high density mounting, and extremely light weight makes these switches ideal for handheld equipment.

Totally sealed body construction prevents contact contamination and allows time- and money-saving automated soldering and cleaning.


Molded-in, epoxy sealed terminals lock out flux, solvents, and other contaminants.

Award-winning STC contact mechanism with benefits unavailable in conventional mechanisms: smooth, positive detent actuation, increased contact stability, and unparalleled logic-level reliability. (Additional STC details in Terms & Acronyms; see Supplement section.)

.100" x .100" (2.54mm x 2.54mm) terminal spacing conforms to standard PC board grid spacing. Round terminals facilitate easier through-hole mounting on PC boards.



Actual Size



A	Toggles
	Rockers
	Pushbuttons
	Illuminated PB
	Programmable
	Keylocks
	Rotaries
	Slides
	Tactiles
	Tilt
	Touch
	Indicators
	Accessories
	Supplement

TYPICAL SWITCH ORDERING EXAMPLE

G

Pole	
1	SPDT

1

Circuits			
2	ON	NONE	ON
Combines with single color or bicolor LEDs			
3	ON	OFF	ON
Combines with bicolor LED only			

2

J

Actuator	
J	Clear

H

PC Terminals	
P	Straight
H	Right Angle
V	Vertical

C

LEDs	
Single Color	
C	Red
D	Amber
F	Green
ON-NONE-ON only	
Bicolor	
CF	Red/Green
ON-NONE-ON & ON-OFF-ON	

DESCRIPTION FOR TYPICAL ORDERING EXAMPLE

G12JHC

ON-NONE-ON Circuit

Clear Toggle,

Red LED

Right Angle


PC Terminals

POLES & CIRCUITS

		Toggle Position			Connected Terminals			Schematics
Pole Throw	Model	Up	Center	Down	Up	Center	Down	
								Note: Terminal numbers are not actually on the switch. LED circuit is isolated and requires an external power source. Single Color Bicolor
SPDT	G12 G13	ON ON	NONE OFF	ON ON	2-3 2-3	NONE OPEN	2-1 2-1	

ACTUATOR

J Clear Toggle




LED COLORS & SPECIFICATIONS

		Single Color			Bicolor
		C Red	D Amber	F Green	CF Red/Green
LEDs are an integral part of the switch and not available separately. The electrical specifications shown are determined at a basic temperature of 25°C.	Colors				
	Maximum Forward Current I_{FM}	30mA	30mA	25mA	30mA/25mA
	Typical Forward Current I_F	20mA	20mA	20mA	20mA/20mA
	Forward Voltage V_F	2.0V	2.0V	2.1V	2.0V/2.1V
	Maximum Reverse Voltage V_{RM}	5V	5V	5V	5V/5V
	Current Reduction Rate Above 25°C ΔI_F	0 - No current Reduction Rate within Ambient Temperature Range			
	Ambient Temperature Range	-25° ~ +55°C			

PC TERMINALS


P

Straight




H

Right Angle







V

Vertical



TYPICAL SWITCH DIMENSIONS








Straight PC



5 & 6 are LED terminals; 4 is a support pin on single color models & an LED terminal on bicolor models.

G12JPC






Right Angle PC



5 & 6 are LED terminals; 4 is a support pin on single color models & an LED terminal on bicolor models.

G12JHD

Vertical PC



5 & 6 are LED terminals; 4 is a support pin on single color models & an LED terminal on bicolor models.

G12JVCf