



Passive-Input Digital Isolators – CMOS Outputs


Functional Diagrams




IL610




IL611



IL612



IL613



IL614

Features

- Up to 100 Mbps data rate
- Flexible inputs with wide input voltage range
- 5 mA input current
- Deterministic default LOW and default HIGH versions
- No carriers or clocks for low EMI emissions and susceptibility
- 3 V to 5 V power supplies
- 44000 year barrier life
- -40°C to 85°C temperature range
- 2.5 kV isolation
- IEC 60747-17 (VDE 0884-17):2021-10; UL 1577
- 8-pin MSOP, SOIC, and PDIP packages
- 0.15", 0.3", or True 8™ mm SOIC packages

Applications

- Optocoupler replacements
- Logic to control interfaces
- Differential line receivers
- Space-critical applications

Description

The IL600 Series are passive input digital signal isolators with CMOS outputs. They have a similar interface but better performance and higher package density than optocouplers.

The devices are manufactured with NVE's patented* IsoLoop® spintronic Giant Magnetoresistive (GMR) technology for small size, high speed, and low power.

A unique ceramic/polymer composite barrier provides excellent isolation and virtually unlimited barrier life.

A resistor sets the input current; a capacitor in parallel with the current-limit resistor provides improved dynamic performance. Parts are available in both default HIGH output and default LOW versions.

These versatile components simplify inventory requirements by replacing a variety of optocouplers, functioning over a wide range of data rates, edge speeds, and power supply levels. The devices are available in various packages, as well as bare die.

Absolute Maximum Ratings⁽¹⁾

Parameters	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Storage Temperature	T _S	-55 ⁽²⁾		150	°C	
Junction Temperature	T _J	-55		150	°C	
Ambient Operating Temperature	T _A	-40 ⁽³⁾		85	°C	
Supply Voltage	V _{DD}	-0.5		7	V	
DC Input Current	I _{IN}	-25		25	mA	
AC Input Current (Single-Ended Input)	I _{IN}	-35		35	mA	
AC Input Current (Differential Input)	I _{IN}	-75		75	mA	
Output Voltage	V _O	-0.5		V _{DD} +1.5	V	
Maximum Output Current	I _O	-10		10	mA	
ESD (output enable CMOS inputs)			2		kV	HBM

Recommended Operating Conditions

Parameters	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Ambient Operating Temperature	T _A	-40 ⁽³⁾		85	°C	
Junction Temperature	T _J	-40		100	°C	
Supply Voltage	V _{DD}	3.0		5.5	V	
Output Current	I _{OUT}	-4		4	mA	
Common Mode Input Voltage	V _{CM}			400	V _{RMS}	

Note 1: Operating at absolute maximum ratings will not damage the device. Parametric performance is not guaranteed at absolute maximum ratings.

Note 2: -55°C applies to all except IL611-1E. -20°C applies to IL611-1E

Note 3: -40°C applies to all except IL611-1E. -20°C applies to IL611-1E

Safety and Approvals

IEC 60747-17 (VDE 0884-17):2021-10 (Basic Isolation; VDE File Number 5016933-4880-0001):

- Isolation voltage (V_{ISO}): 2500 V_{RMS}
- Transient overvoltage (V_{IOTM}): 4000 V_{PK}
- Surge rating 4000 V
- Each part tested at 1590 V_{PK} for 1 second, 5 pC partial discharge limit
- Samples tested at 4000 V_{PK} for 60 sec.; then 1358 V_{PK} for 10 sec. with 5 pC partial discharge limit
- Working Voltage (V_{IORM} ; pollution degree 2):

Package	Part No. Suffix	Working Voltage
MSOP8	-1	800 V_{RMS}
SOIC8	-3	700 V_{RMS}
PDIP8	-2	900 V_{RMS}
Narrow-body SOIC16	-3	700 V_{RMS}
Wide-body SOIC16/True 8™	None	600 V_{RMS}

Safety-Limiting Values	Symbol	Value	Units
Safety rating ambient temperature	T_S	180	°C
Safety rating power (180°C)	P_S	270	mW
Supply current safety rating (total of supplies)	I_S	54	mA

UL 1577 (Component Recognition Program File Number E207481)

- 2500 V rating for all types other than MSOP.
- Each part other than MSOP tested at 3000 V_{RMS} (4240 V_{PK}) for 1 second; each lot sample tested at 2500 V_{RMS} (3530 V_{PK}) for 1 minute.
- MSOP rating 1000 V; tested at 1200 V_{RMS} (1768 V_{PK}) for 1 second; each lot sample tested at 1500 V_{RMS} (2121 V_{PK}) for 1 minute.

Soldering Profile


Per JEDEC J-STD-020C; MSL 1

Electrostatic Discharge Sensitivity

This product has been tested for electrostatic sensitivity to the limits stated in the specifications. However, NVE recommends that all integrated circuits be handled with appropriate care to avoid damage. Damage caused by inappropriate handling or storage could range from performance degradation to complete failure.


IL610/IL610F Pin Connections

1	NC	No internal connection
2	IN-	Coil connection
3	IN+	Coil connection
4	NC	No internal connection
5	GND	Ground return for V_{DD}
6	OUT	Data out
7	V_{OE}	Output enable (internally held low with approx. 100 k Ω)
8	V_{DD}	Supply Voltage




IL611 Pin Connections

1	IN ₁ -	Channel 1 coil connection
2	IN ₁ +	Channel 1 coil connection
3	IN ₂ -	Channel 2 coil connection
4	IN ₂ +	Channel 2 coil connection
5	GND	Ground return for V_{DD}
6	OUT ₂	Data out, channel 2
7	OUT ₁	Data out, channel 1
8	V_{DD}	Supply Voltage




IL612 Pin Connections

1	IN ₁ -	Channel 1 coil connection
2	V_{DD1}	Supply Voltage 1
3	OUT ₂	Data out, channel 2
4	GND ₁	Ground return for V_{DD1}
5	GND ₂	Ground return for V_{DD2}
6	IN ₂ -	Channel 2 coil connection
7	V_{DD2}	Supply Voltage 2
8	OUT ₁	Data out, channel 1



IL613 Pin Connections


1	IN ₁ -	Channel 1 coil connection
2	NC	No connection (internally connected to pin 8)
3	IN ₁ +	Channel 1 coil connection
4	IN ₂ -	Channel 2 coil connection
5	IN ₂ +	Channel 2 coil connection
6	IN ₃ -	Channel 3 coil connection
7	IN ₃ +	Channel 3 coil connection
8	NC	No connection (internally connected to pin 2)
9	GND	Ground return for V_{DD} (internally connected to pin 15)
10	OUT ₃	Data out, channel 3
11	NC	No connection
12	V_{DD}	Supply Voltage. Pin 12 and pin 16 must be connected externally
13	OUT ₂	Data out, channel 2
14	OUT ₁	Data out, channel 1
15	GND	Ground return for V_{DD} (internally connected to pin 9)
16	V_{DD}	Supply Voltage. Pin 12 and pin 16 must be connected externally



Note: Pins 12 and 16 must be connected externally.

IL614 Pin Connections

1	V _{DD1}	Supply Voltage 1
2	GND ₁	Ground return for V _{DD1} (internally connected to pin 8)
3	OUT ₁	Data out, channel 1
4	V _{OE}	Channel 1 data output enable. Internally held low with 100 k Ω
5	IN ₂₋	Data in, channel 2
6	V _{coil}	Supply connection for channel 2 and channel 3 coils
7	IN ₃₋	Data in, channel 3
8	GND ₁	Ground return for V _{DD1} (internally connected to pin 2)
9	GND ₂	Ground return for V _{DD2} (internally connected to pin 15)
10	NC	No Connection
11	OUT ₃	Data out, channel 3
12	V _{DD2}	Supply Voltage 2
13	OUT ₂	Data out, channel 2
14	IN ₁₋	Channel 1 coil connection
15	GND ₂	Ground return for V _{DD2} (internally connected to pin 9)
16	IN ₁₊	Channel 1 coil connection



Operating Specifications

Input Specifications ($V_{DD} = 3\text{ V} - 5.5\text{ V}$; $T = -40^{\circ}\text{C} - 85^{\circ}\text{C}$ unless otherwise stated)						
Parameters	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Coil Input Resistance	R_{COIL}	47	85	112	Ω	$T = 25^{\circ}\text{C}$
		31	85	128	Ω	$T = -40^{\circ}\text{C} - 85^{\circ}\text{C}$
Coil Resistance Temperature Coefficient	$TC\ R_{COIL}$		0.2	0.25	$\Omega/^{\circ}\text{C}$	
Coil Inductance	L_{COIL}		9		nH	
DC Input Threshold (5 V)	I_{INH-DC}	0.5	3		mA	$V_{DD} = 4.5\text{ V} - 5.5\text{ V}$
	I_{INL-DC}		3.5	5	mA	
DC Input Threshold (3 V)	I_{INH-DC}	0.3	0.5		mA	$V_{DD} = 3\text{ V} - 3.6\text{ V}$; no boost capacitor
	I_{INL-DC}		5	8	mA	
Dynamic Input Threshold (3 V)	$I_{INH-BOOST}$	0.5	3		mA	$V_{DD} = 3\text{ V} - 3.6\text{ V}$; $t_{IR} = t_{IF} = 3\text{ ns}$; $C_{BOOST} = 16\text{ pF}$
	$I_{INL-BOOST}$		3.5	5	mA	
Differential Input Threshold	$I_{INH-DIFF}$	0.5	3		mA	$V_{DD} = 3\text{ V} - 5.5\text{ V}$; input current reverses; boost cap not required
	$I_{INL-DIFF}$		3.5	5	mA	
Input Threshold Hysteresis	$I_{INH} - I_{INL}$		1		mA	
Failsafe Input Current ⁽¹⁾ (5 V)	I_{INL-FS}	-25		0.5	mA	$V_{DD} = 4.5\text{ V} - 5.5\text{ V}$
Failsafe Input Current ⁽¹⁾ (3 V)	I_{INH-FS}	-25		0.3	mA	$V_{DD} = 3\text{ V} - 3.6\text{ V}$
	I_{INL-FS}	8		25	mA	
V_{OE} Logic High Input Voltage	V_{IH}	2.4		V_{DD}	V	
V_{OE} Logic Low Input Voltage	V_{IL}	0		0.8	V	
Input Signal Rise and Fall Times	t_{IR}, t_{IF}			1	μs	
Common Mode Transient Immunity	$ CM_{HL} , CM_{L} $		100		kV/ μs	

Notes:

- “Failsafe Operation” is defined as the input current required to guarantee an output state on power-up.

To guarantee failsafe input energization, the DC current supplied to the coil must be at least 8 mA using 3.3 V supplies versus 5 mA for 4.5 V or higher supplies.




Figure 1. Test circuit.

5 V Electrical Specifications ($V_{DD} = 4.5\text{ V} - 5.5\text{ V}$; $T = -40^{\circ}\text{C}^{(5)} - 85^{\circ}\text{C}$ unless otherwise stated)						
Parameters	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Quiescent Supply Current						
IL610	I_{DD}		2	3	mA	$V_{DD} = 5\text{ V}$, $I_{IN} = 0$
IL611	I_{DD}		4	6		
IL612	I_{DD1}		2	3		
IL612	I_{DD2}		2	3		
IL613	I_{DD}		6	9		
IL614	I_{DD1}		2	3		
IL614	I_{DD2}		4	6		
Logic High Output Voltage	V_{OH}	4.9	5		V	$V_{DD} = 5\text{ V}$, $I_O = 20\text{ }\mu\text{A}$
		4.0	4.8		V	$V_{DD} = 5\text{ V}$, $I_O = 4\text{ mA}$
Logic Low Output Voltage	V_{OL}		0	0.1	V	$V_{DD} = 5\text{ V}$, $I_O = -20\text{ }\mu\text{A}$
			0.2	0.8	V	$V_{DD} = 5\text{ V}$, $I_O = -4\text{ mA}$
Logic Output Drive Current	$ I_O $	7	10		mA	

5 V Switching Specifications ($V_{DD} = 4.5\text{ V} - 5.5\text{ V}$; $T = -40^{\circ}\text{C}^{(5)} - 85^{\circ}\text{C}$ unless otherwise stated)						
Parameters	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Data Rate		100			Mbps	$t_{IR} = t_{IF} = 3\text{ ns}$; $C_{BOOST} = 16\text{ pF}$
Minimum Pulse Width ⁽¹⁾	PW	10			ns	
Propagation Delay	t_{PHL} ; t_{PLH}		8	15	ns	
Average Propagation Delay Drift	t_{PLH}		10		ps/ $^{\circ}\text{C}$	
Pulse Width Distortion $ t_{PHL} - t_{PLH} ^{(2)}$	PWD		3	5	ns	
Pulse Jitter ⁽³⁾	t_J			100	ps	
Propagation Delay Skew ⁽⁴⁾	t_{PSK}	-2		2	ns	
Output Rise / Fall Time (10–90%)	t_R ; t_F		2	4	ns	

Notes:

1. Minimum Pulse Width is the shortest pulse width at which the specified PWD is guaranteed.
2. PWD is defined as $|t_{PHL} - t_{PLH}|$.
3. 66,535-bit pseudo-random binary signal (PRBS) NRZ bit pattern with no more than five consecutive 1s or 0s; 800 ps transition time.
4. t_{PSK} is equal to the magnitude of the worst case difference in t_{PHL} and/or t_{PLH} that will be seen between units at 25°C .
5. -20°C for IL611-1E.

3.3 V Electrical Specifications ($V_{DD} = 3\text{ V} - 3.6\text{ V}$; $T = -40^{\circ}\text{C}^{(4)} - 85^{\circ}\text{C}$ unless otherwise stated)						
Parameters	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Quiescent Supply Current						
IL610	I_{DD}		1.3	2	mA	$V_{DD} = 3.3\text{ V}$, $I_{IN} = 0$
IL611	I_{DD}		2.6	4		
IL612	I_{DD1}		1.3	2		
IL612	I_{DD2}		1.3	2		
IL613	I_{DD}		4	6		
IL614	I_{DD1}		1.3	2		
IL614	I_{DD2}		2.6	4		
Logic High Output Voltage	V_{OH}	3.2	3.3		V	$V_{DD} = 3.3\text{ V}$, $I_O = 20\text{ }\mu\text{A}$
		3.0	3.1		V	$V_{DD} = 3.3\text{ V}$, $I_O = 4\text{ mA}$
Logic Low Output Voltage	V_{OL}		0	0.1	V	$V_{DD} = 3.3\text{ V}$, $I_O = -20\text{ }\mu\text{A}$
			0.2	0.8	V	$V_{DD} = 3.3\text{ V}$, $I_O = -4\text{ mA}$
Logic Output Drive Current	$ I_O $	7	10		mA	

3.3 V Switching Specifications ($V_{DD} = 3\text{ V} - 3.6\text{ V}$; $T = -40^{\circ}\text{C}^{(4)} - 85^{\circ}\text{C}$ unless otherwise stated)						
Data Rate		100			Mbps	$t_{IR} = t_{IF} = 3\text{ ns}$; $C_{BOOST} = 16\text{ pF}$
Minimum Pulse Width ⁽¹⁾	PW	10			ns	
Propagation Delay Input to Output (High to Low)	t_{PHL}		12	18	ns	
Propagation Delay Input to Output (Low to High)	t_{PLH}		12	18	ns	
Average Propagation Delay Drift	t_{PLH}		10		ps/ $^{\circ}\text{C}$	
Pulse Width Distortion $ t_{PHL} - t_{PLH} $ ⁽²⁾	PWD		3	5	ns	
Propagation Delay Skew ⁽³⁾	t_{PSK}	-2		2	ns	
Output Rise Time (10–90%)	t_R		3	5	ns	
Output Fall Time (10–90%)	t_F		3	5	ns	

Notes:

1. The Minimum Pulse Width is the shortest pulse width at which the specified PWD is guaranteed.
2. PWD is defined as $|t_{PHL} - t_{PLH}|$.
3. t_{PSK} is equal to the magnitude of the worst-case difference in t_{PHL} and/or t_{PLH} that will be seen between units at 25°C .
4. -20°C for IL611-1E

Insulation Specifications

Parameters	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Creepage Distance (external)						
MSOP		3.01			mm	
0.15" SOIC		4.03			mm	
0.3" SOIC		8.03	8.3		mm	Per IEC 60601
PDIP		7.08			mm	
Total Barrier Thickness (internal)		0.012	0.013		mm	
Leakage Current			0.2		μA	240 V _{RMS} , 60 Hz
Barrier Resistance	R _{IO}		>10 ¹⁴			500 V
Barrier Capacitance	C _{IO}		7		Ω pF	f = 1 MHz
Comparative Tracking Index	CTI	≥175			V	Per IEC 60112
High Voltage Endurance (Maximum Barrier Voltage for Indefinite Life)	AC	V _{IO}	1000		V _{RMS}	At maximum operating temperature
	DC		1500		V _{DC}	
Barrier Life			44000		Years	100°C, 1000 V _{RMS} , 60% CL activation energy

Thermal Characteristics

Parameter	Symbol	Min.	Typ.	Max.	Units	Test Conditions
Junction–Ambient Thermal Resistance	θ _{JA}		184 134 82 67 114			Double-sided PCB in free air
Junction–Case (Top) Thermal Resistance	θ _{JC}		15 10 8 12 36		°C/W	
Junction–Ambient Thermal Resistance	θ _{JA}		46			
Junction–Case (Top) Thermal Resistance	θ _{JC}		9			
Power Dissipation	P _D			500 675 675 1500 800	mW	2s2p PCB in free air per JESD51

Typical Performance Graphs




Figure 2. Typical high output voltage vs. load.




Figure 3. Typical low output voltage vs. load




Figure 4. Typical input threshold current hysteresis.




Figure 5. Typical output rise time vs. load capacitance

Applications Information

Overview

Figure 7 shows the IL600-Series block diagram. The coil, GMR, and support integrated circuitry are integrated on a single chip:




Figure 6. IL61x block diagram (each channel).

Input Coil

IL600-Series Isolators' current-mode architecture avoids semiconductor structures on the inputs and input-side power supplies, providing unique flexibility. Changes in current flow into the input coil result in logic state changes at the output. Input-stage hysteresis improves noise immunity.




Figure 7. Typical IL61x and IL61xF transfer functions.

GMR Wheatstone Bridge

The heart of the Isolators is a Wheatstone bridge constructed of GMR resistor elements. The current in the coil driven from the input side of the isolator creates a magnetic field that switches the GMR in the bridge. Thus the signal is transmitted by magnetic field.

Schmitt Trigger and Output Stage

The change in the bridge is detected by a Schmitt trigger comparator. This drives a push-pull MOSFET output stage. The outputs have deterministic defaults when the input coil is unenergized (LOW for the IL61xF and HIGH for the IL61x).

Coil Polarity

Current from (In+) to (In-) energizes the coil and switches the output from its default state. Zero or negative current will cause the output to switch to the default state. The coil input is analogous to the LED in an optocoupler, with (In+) analogous to the LED anode, and (In-) analogous to the cathode.

Input Resistor Selection

A resistor sets the coil input current:




Figure 8. Input resistor.

The input resistor can be on either side of the coil, although it is shown on the (+) input in most of our circuits. There is no limit to input voltages because there are no semiconductor input structures.

Worst-case logic low threshold current is 8 mA, which is for single-ended operation with a 3 V supply. In differential mode, where the input current reverses, the logic low threshold current is 5 mA for the range of supplies. A “boost capacitor” creates current reversals at edge transitions, reducing the input logic low threshold current to the differential level of 5 mA.

Typical Resistor Values

The following table shows typical values for the external resistor for 5 mA coil current. The values are approximate and should be adjusted for temperature or other application specifics:

V_{COIL}	Coil Resistor
3.3 V	510 Ω
5 V	820 Ω

Maximum Coil Current

Absolute Maximum unipolar coil current is 25 mA, while bipolar drive allows up to ± 75 mA. The difference in specifications is due to the risk of electromigration of coil metals under constant current flow. Long-term unipolar DC current flow above 25 mA can cause erosion of the coil metal. In differential mode, erosion takes place in both directions as each current cycle reverses and has no net effect up to the absolute maximum current.

An advantage over optocouplers and other high-speed couplers in differential mode is that no reverse bias protection for the input structure is required for a differential signal.

Boost Capacitor

A “boost capacitor” in parallel with the current-limiting resistor boosts the instantaneous coil current at the signal transition. This ensures switching and reduces propagation delay and reduces pulse-width distortion. The optimal value of the boost capacitor is based on the rise and fall times of the signal driving the inputs. The instantaneous boost capacitor current is proportional to input edge speeds ($C \frac{dV}{dt}$). Select a capacitor value based on the rise and fall times of the input signal to be isolated that provides approximately 20 mA of additional “boost” current. Figure 12 is a guide to boost capacitor selection. For high-speed logic signals ($t_r, t_f < 10$ ns), a 16 pF capacitor is recommended. The capacitor value is generally not critical; if in doubt, choose a higher value:




Figure 9. C_boost selection.

Drive Configurations

As the figures below show, IL600-Series Isolators can be configured with the input referenced to ground, referenced to a logic supply, or in a bipolar configuration.




Figure 10. Input referenced to ground.




Figure 11. Input referenced to logic supply.




Figure 12. Bipolar drive.

Single-Ended or Differential Input

The IL610, IL611, IL613, and channel 1 of the IL614 can be run with single-ended or differential inputs. In the differential mode, current will naturally flow through the coil in both directions without a boost capacitor, although the capacitor can still be used for increased external field immunity or improved pulse-width distortion. Bipolar drive increases the absolute maximum coil current, minimizes the required input current with a 3.3-volt supply, and maximizes immunity to external magnetic fields. No reverse bias protection for the input structure is required for a bipolar signal.

Power Supply Decoupling

0.1 μ F decoupling capacitors are recommended for the power supplies (V_{DD} , V_{DD1} , and V_{DD2}). The capacitors should be as close as possible to the V_{DD} pins.

Maintaining Creepage

Standard pad libraries often extend under the package, compromising creepage and clearance. Similarly, ground planes, if used, should be spaced to avoid compromising clearance. Package drawings and recommended pad layouts are included in this datasheet.

Electromagnetic Compatibility and Magnetic Field Immunity

IL600-Series isolators are ideal for harsh industrial environments with low emitted fields and very high external magnetic field immunity. Because IL600-Series Isolators are completely static, they do not emit any EMI.

Internal Shielding and Inherent Common-Mode Field Immunity

IsoLoop Isolators operate by imposing a magnetic field on a GMR sensor, which translates the change in field into a change in logic state. A magnetic shield and a Wheatstone Bridge configuration provide superb immunity to external magnetic fields.

Inherent AC magnetic field immunity

Unlike inductive or capacitive which transmit and detect high-frequency carriers, IsoLoop Isolators do not rely on AC signals, and are inherently insensitive to AC magnetic fields. It is harder to disrupt an isolated AC signal with an external magnetic field than a DC signal. This enhances the magnetic immunity in switch-mode power control applications. Immunity to external magnetic fields can be enhanced by (1) optimal orientation of the device with respect to the field direction and (2) the use of bipolar coil inputs.

1. Orientation of the device with respect to the external field

An applied field in the “H1” direction is the worst case for magnetic immunity. In this case, the external field is in the same direction as fields generated on-chip. An applied field in direction “H2” has considerably less effect and results in higher magnetic immunity.




Figure 13. Orientation with respect to the external field.

2. Bipolar coil input

Regardless of orientation, a bipolar input on the coil improves magnetic immunity. The higher the coil current, the higher the on-chip fields, and the higher the immunity to external fields.

Method	Approx. Immunity	Immunity Description
Field applied in H1 direction	±2 mT	A DC current of 100 A flowing in a conductor 1 cm from the device could cause disturbance.
Field applied in H2 direction	±7 mT	A DC current of 140 A flowing in a conductor 1 cm from the device could cause disturbance.
Field applied in any direction but with a bipolar input to the coil	±25 mT	A DC current of 1250 A flowing in a conductor 1 cm from the device could cause disturbance.

Illustrative Applications




Figure 14. Wide input voltage range using a current regulator.

A self-biasing transistor current regulator can be used instead of an input resistor in series with the coil to provide a wide range of input voltages without overdriving or under driving the coil.






Figure 15. Isolated RS-485 and RS-422 Receivers Using IL610s.

IL610 components can be used as simple isolated RS-485 or RS-422 receivers, terminating signals at the IL610 for a fraction of the cost of an isolated node. Cabling is simplified by eliminating the need to power the input side of the receiving board. No current-limiting resistor is needed for a single receiver because it will draw less current than the driver maximum. Current limiting resistors allow at least eight nodes without exceeding the maximum load of the transceiver. Placement of the current-limiting resistors on both lines provides better dynamic signal balance. There is generally no need for line termination resistors below data rates of approximately 10 Mbps because the IL610 coil resistance of approximately 85 Ω is close to the characteristic impedance of most cables. The circuit is intrinsically open-circuit failsafe because the IL610 is guaranteed to switch to the high state when the coil input current is less than 0.5 mA.

Number of Nodes	Current Limit Resistors (Ω)
1	None
2	17
3	22
4	27
5	27
6	27
7	30
8	33



The unique IL614 three-channel isolator can be used as part of a multi-chip design with a variety of non-isolated transceivers. The IL614 provides 2.5 kV_{RMS} isolation (1 minute) and 100 kV/μs transient immunity. The IL614-3 is in a narrow-body (0.15 inch-wide) package when board space is critical.




NVE Corporation 11409 Valley View Road, Eden Prairie, MN 55344-3617 (952) 829-9217 www.nve.com [YouTube.com/NveCorporation](https://www.youtube.com/NveCorporation) iso-apps@nve.com

Package Drawings


8-pin MSOP (-1 suffix)

Dimensions in inches (mm); scale = approx. 5X




8-pin SOIC Package (-3 suffix)

Dimensions in inches (mm); scale = approx. 5X




8-pin PDIP (-2 suffix)

Dimensions in inches (mm); scale = approx. 2.5X




0.15" 16-pin SOIC Package (-3 suffix)

Dimensions in inches (mm); scale = approx. 5X



0.3" 16-pin SOIC Package (no suffix)

Dimensions in inches (mm); scale = approx. 5X



*Specified for True 8™ package to guarantee 8 mm creepage per IEC 60601.

Ordering Information and Valid Part Numbers

IL 6xx F - 1 E TR13

→ **Bulk Packaging**

Blank = Tube
TR7 = 7" Tape and Reel
TR13 = 13" Tape and Reel

→ **Package**

E = RoHS Compliant

→ **Package Type**

Blank = 0.3" SOIC
-1 = MSOP
-2 = PDIP
-3 = 0.15" SOIC
-5 = Bare die

→ **Default Output**

Blank = HIGH
F = LOW

→ **Base Part Number**

610 = Single Channel
611 = 2 Drive Channels
612 = 1 Drive Channel,
1 Receive Channel
613 = 3 Drive Channels
614 = 2 Drive Channels,
1 Receive Channel

→ **Product Family**

IL = Isolators

**IL610 Valid
Part Numbers**

IL610-1E
IL610F-1E
IL610-2E
IL610-3E
IL610-5

**IL611 Valid
Part Numbers**

IL611-1E
IL611F-1E
IL611-2E
IL611-3E

**IL612 Valid
Part Numbers**

IL612-2E
IL612-3E

**IL613 Valid
Part Numbers**

IL613E
IL613-3E

**IL614 Valid
Part Numbers**

IL614E
IL614-3E

**RoHS
COMPLIANT**

Revision History

ISB-DS-001-IL600-AE
October 2025

Changes

- Added IL610F-1E and IL611F-1E default-LOW versions.
- Reversed coil polarity labeling for applicability to default-HIGH and default-LOW versions.
- Increased Common Mode Transient Immunity specification from 20 to 100 kV/μs (p. 6).
- Added Typical Performance Graphs (p. 10).
- Changed magnetic immunity units from G to mT (SI units); clarified “Immunity Descriptions” (p. 13).
- Added SBT current-limiter application diagram (p. 17).
- Changed channel-direction terminology from “Drive” to “Transmit” (p. 21).
- Misc. cosmetic changes.

ISB-DS-001-IL600-AD
October 2022

Changes

- Upgrade to VDE 0884-17 (p. 3).
- Increased Working Voltage ratings based on latest VDE testing (p. 3).
- Added V_{OE} logic high and low input voltage specifications (p. 6).
- Added thermal characteristics (p. 9).

ISB-DS-001-IL600-AC

Changes

- Corrected 8-pin SOIC package outline dimensions.
- Changed low temperature specification for IL611-1E to -20°C .

ISB-DS-001-IL600-AB

Changes

- IEC 60747-5-5 (VDE 0884) certification.
- Upgraded from MSL 2 to MSL 1.
- Rearranged input threshold specifications so maximum is more than minimum.

ISB-DS-001-IL600-AA

Changes

- Added VDE 0884 pending.
- Updated package drawings.
- Added recommended solder pad layouts.
- Clarified circuit polarities.

ISB-DS-001-IL600-Z

Changes

- Detailed isolation and barrier specifications.
- Cosmetic changes.

ISB-DS-001-IL600-Y

Changes

- Clarified Test Circuit 2 differential operation diagram (p.5).

ISB-DS-001-IL600-X

Changes

- Separated and clarified Input Specifications.
- Added minimum/maximum coil resistance specifications.
- Merged and simplified “Operation” and “Applications” sections.

ISB-DS-001-IL600-W

Changes

- Update terms and conditions.

ISB-DS-001-IL600-V

Changes

- Additional changes to pin spacing specification on MSOP drawing.

ISB-DS-001-IL600-U

Changes

- Changed pin spacing specification on MSOP drawing.

Datasheet Limitations

The information and data provided in datasheets shall define the specification of the product as agreed between NVE and its customer, unless NVE and customer have explicitly agreed otherwise in writing. All specifications are based on NVE test protocols. In no event however, shall an agreement be valid in which the NVE product is deemed to offer functions and qualities beyond those described in the datasheet.

Limited Warranty and Liability

Information in this document is believed to be accurate and reliable. However, NVE does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

In no event shall NVE be liable for any indirect, incidental, punitive, special or consequential damages (including, without limitation, lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Right to Make Changes

NVE reserves the right to make changes to information published in this document including, without limitation, specifications and product descriptions at any time and without notice. This document supersedes and replaces all information supplied prior to its publication.

Use in Life-Critical or Safety-Critical Applications

Unless NVE and a customer explicitly agree otherwise in writing, NVE products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical devices or equipment. NVE accepts no liability for inclusion or use of NVE products in such applications and such inclusion or use is at the customer's own risk. Should the customer use NVE products for such application whether authorized by NVE or not, the customer shall indemnify and hold NVE harmless against all claims and damages.

Applications

Applications described in this datasheet are illustrative only. NVE makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using NVE products, and NVE accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the NVE product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customers. Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

NVE does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customers. The customer is responsible for all necessary testing for the customer's applications and products using NVE products in order to avoid a default of the applications and the products or of the application or use by customer's third party customers. NVE accepts no liability in this respect.

Limiting Values

Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the recommended operating conditions of the datasheet is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and Conditions of Sale

In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. NVE hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of NVE products by customer.

No Offer to Sell or License

Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export Control

This document as well as the items described herein may be subject to export control regulations. Export might require a prior authorization from national authorities.

Automotive Qualified Products

Unless the datasheet expressly states that a specific NVE product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. NVE accepts no liability for inclusion or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without NVE's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond NVE's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies NVE for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond NVE's standard warranty and NVE's product specifications.

An ISO 9001 Certified Company

NVE Corporation
11409 Valley View Road
Eden Prairie, MN 55344-3617 USA
Telephone: (952) 829-9217

www.nve.com
e-mail: iso-info@nve.com

©NVE Corporation
All rights are reserved. Reproduction in whole or in part is prohibited without the prior written consent of the copyright owner.

ISB-DS-001-IL600-AE

October 2025