

MOS FET Relays

G3VM-81LR

World's Smallest SSOP Package MOS FET Relay* with Low Output Capacitance and ON Resistance ($C \times R = 37.5\text{pF} \cdot \Omega$) in a 80-V Load Voltage Model.

- Turn-on time = 0.1 ms (typ.), Turn-off time = 0.15 ms (typ.)
- RoHS compliant

*Information correct as of May 2007, according to data obtained by OMRON.

Application Examples

- Semiconductor inspection tools
- Measurement devices
- Broadband systems
- Data loggers



Note: The actual product is marked differently from the image shown here.



List of Models

Contact form	Terminals	Load voltage (peak value)	Model	Number per tape
SPST-NO	Surface-mounting terminals	80 VAC	G3VM-81LR	---
			G3VM-81LR(TR05)	500
			G3VM-81LR(TR)	1,500

Dimensions

Note: All units are in millimeters unless otherwise indicated.

G3VM-81LR




Note: The actual product is marked differently from the image shown here.

Note: A tolerance of ± 0.1 mm applies to all dimensions unless otherwise specified.

Weight: 0.03 g


Terminal Arrangement/Internal Connections (Top View)

G3VM-81LR



Actual Mounting Pad Dimensions (Recommended Value, Top View)

G3VM-81LR



Absolute Maximum Ratings (Ta = 25°C)


Item	Symbol	Rating	Unit	Measurement Conditions
Input	LED forward current	I_F	50	mA
	Repetitive peak LED forward current	I_{FP}	---	A
	LED forward current reduction rate	$\Delta I_F/^\circ\text{C}$	-0.5	mA/°C
	LED reverse voltage	V_R	5	V
	Connection temperature	T_j	125	°C
Output	Load voltage (AC peak/DC)	V_{OFF}	80	V
	Continuous load current	I_O	120	mA
	ON current reduction rate	$\Delta I_O/^\circ\text{C}$	-1.2	mA/°C
	Connection temperature	T_j	125	°C
Dielectric strength between input and output (See note 1.)		V_{I-O}	1,500	V_{rms}
Ambient operating temperature		T_a	-20 to +85	°C
Storage temperature		T_{slg}	-40 to +125	°C
Soldering temperature		---	260	°C

Note: 1. The dielectric strength between the input and output was checked by applying voltage between all pins as a group on the LED side and all pins as a group on the light-receiving side.

Electrical Characteristics (Ta = 25°C)

Item	Symbol	Minimum	Typical	Maximum	Unit	Measurement conditions
Input	LED forward voltage	V_F	1.0	1.15	1.3	V
	Reverse current	I_R	---	---	10	μA
	Capacity between terminals	C_T	---	15	---	pF
	Trigger LED forward current	I_{FT}	---	2	5	mA
Output	Maximum resistance with output ON	R_{ON}	---	7.5	12	Ω
	Current leakage when the relay is open	I_{LEAK}	---	100	200	pA
	Capacity between terminals	C_{OFF}	---	5	7	pF
Capacity between I/O terminals		C_{I-O}	---	0.8	---	pF
Insulation resistance between I/O terminals		R_{I-O}	1,000	---	---	M Ω
Turn-ON time		t_{ON}	---	0.1	0.25	ms
Turn-OFF time		t_{OFF}	---	0.15	0.2	ms

Note: 2. Turn-ON and Turn-OFF Times




Recommended Operating Conditions

Use the G3VM under the following conditions so that the Relay will operate properly.


Item	Symbol	Minimum	Typical	Maximum	Unit
Load voltage (AC peak/DC)	V_{DD}	---	---	64	V
Operating LED forward current	I_F	10	---	30	mA
Continuous load current (AC peak/DC)	I_O	---	---	120	mA
Operating temperature	T_a	25	---	60	°C

■ Engineering Data


**LED forward current vs.
Ambient temperature**
IF - Ta




**Continuous load current vs.
Ambient temperature**
IO - Ta




**LED forward current vs.
LED forward voltage**
IF - VF




**Continuous load current vs.
On-state voltage**
IO - VON




**On-state resistance vs.
Ambient temperature**
RON - Ta




**Trigger LED forward current vs.
Ambient temperature**
IFT - Ta




**Turn ON, Turn OFF time vs.
LED forward current**
ton, toff - IF




**Turn ON, Turn OFF time vs.
Ambient temperature**
ton, toff - Ta



**Current leakage vs.
Load voltage**
I LEAK - VOFF



**Output terminal capacitance
COFF/COFF(ov) vs. Load voltage**
COFF - VOFF



All sales are subject to Omron Electronic Components LLC standard terms and conditions of sale, which can be found at http://www.components.omron.com/components/web/webfiles.nsf/sales_terms.html

ALL DIMENSIONS SHOWN ARE IN MILLIMETERS.

To convert millimeters into inches, multiply by 0.03937. To convert grams into ounces, multiply by 0.03527.

OMRON[®]

**OMRON ELECTRONIC
COMPONENTS LLC**

55 E. Commerce Drive, Suite B
Schaumburg, IL 60173

847-882-2288

OMRON ON-LINE

Global - <http://www.omron.com>

USA - <http://www.components.omron.com>

Cat. No. X302-E-1

12/10

Specifications subject to change without notice

Printed in USA