

MPF102

Preferred Devices

JFET VHF Amplifier

N-Channel – Depletion

Features

- Pb-Free Package is Available*




ON Semiconductor®

<http://onsemi.com>

MAXIMUM RATINGS


Rating	Symbol	Value	Unit
Drain – Source Voltage	V_{DS}	25	Vdc
Drain – Gate Voltage	V_{DG}	25	Vdc
Gate – Source Voltage	V_{GS}	-25	Vdc
Gate Current	I_G	10	mAdc
Total Device Dissipation @ $T_A = 25^\circ\text{C}$ Derate above 25°C	P_D	350 2.8	mW mW/ $^\circ\text{C}$
Junction Temperature Range	T_J	125	$^\circ\text{C}$
Storage Temperature Range	T_{stg}	-65 to +150	$^\circ\text{C}$

Maximum ratings are those values beyond which device damage can occur. Maximum ratings applied to the device are individual stress limit values (not normal operating conditions) and are not valid simultaneously. If these limits are exceeded, device functional operation is not implied, damage may occur and reliability may be affected.



TO-92 (TO-226AA)
CASE 29-11
STYLE 5

MARKING DIAGRAM



MPF102 = Device Code
A = Assembly Location
Y = Year
WW = Work Week
■ = Pb-Free Package

(Note: Microdot may be in either location)

ORDERING INFORMATION

Device	Package	Shipping
MPF102	TO-92	1000 Units/Bulk
MPF102G	TO-92 (Pb-Free)	1000 Units/Bulk

Preferred devices are recommended choices for future use and best overall value.

*For additional information on our Pb-Free strategy and soldering details, please download the ON Semiconductor Soldering and Mounting Techniques Reference Manual, SOLDERRM/D.

MPF102

ELECTRICAL CHARACTERISTICS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

Characteristic	Symbol	Min	Max	Unit
----------------	--------	-----	-----	------

OFF CHARACTERISTICS

Gate – Source Breakdown Voltage ($I_G = -10\ \mu\text{Adc}$, $V_{DS} = 0$)	$V_{(BR)GSS}$	-25	–	Vdc
Gate Reverse Current ($V_{GS} = -15\ \text{Vdc}$, $V_{DS} = 0$) ($V_{GS} = -15\ \text{Vdc}$, $V_{DS} = 0$, $T_A = 100^\circ\text{C}$)	I_{GSS}	– –	–2.0 –2.0	nAdc μAdc
Gate – Source Cutoff Voltage ($V_{DS} = 15\ \text{Vdc}$, $I_D = 2.0\ \text{nAdc}$)	$V_{GS(off)}$	–	–8.0	Vdc
Gate – Source Voltage ($V_{DS} = 15\ \text{Vdc}$, $I_D = 0.2\ \text{mAdc}$)	V_{GS}	–0.5	–7.5	Vdc

ON CHARACTERISTICS

Zero – Gate – Voltage Drain Current (Note 1) ($V_{DS} = 15\ \text{Vdc}$, $V_{GS} = 0\ \text{Vdc}$)	I_{DSS}	2.0	20	mAdc
--	-----------	-----	----	------





SMALL – SIGNAL CHARACTERISTICS

Forward Transfer Admittance (Note 1) ($V_{DS} = 15\ \text{Vdc}$, $V_{GS} = 0$, $f = 1.0\ \text{kHz}$) ($V_{DS} = 15\ \text{Vdc}$, $V_{GS} = 0$, $f = 100\ \text{MHz}$)	$ y_{fs} $	2000 1600	7500 –	μmhos
Input Admittance ($V_{DS} = 15\ \text{Vdc}$, $V_{GS} = 0$, $f = 100\ \text{MHz}$)	$\text{Re}(y_{is})$	–	800	μmhos
Output Conductance ($V_{DS} = 15\ \text{Vdc}$, $V_{GS} = 0$, $f = 100\ \text{MHz}$)	$\text{Re}(y_{os})$	–	200	μmhos
Input Capacitance ($V_{DS} = 15\ \text{Vdc}$, $V_{GS} = 0$, $f = 1.0\ \text{MHz}$)	C_{iss}	–	7.0	pF
Reverse Transfer Capacitance ($V_{DS} = 15\ \text{Vdc}$, $V_{GS} = 0$, $f = 1.0\ \text{MHz}$)	C_{rss}	–	3.0	pF

1. Pulse Test; Pulse Width $\leq 630\ \text{ms}$, Duty Cycle $\leq 10\%$.

COMMON SOURCE CHARACTERISTICS

ADMITTANCE PARAMETERS

 $(V_{DS} = 15 \text{ Vdc}, T_{\text{channel}} = 25^\circ\text{C})$ Figure 1. Input Admittance (y_{is})Figure 2. Reverse Transfer Admittance (y_{rs})Figure 3. Forward Transfer Admittance (y_{fs})Figure 4. Output Admittance (y_{os})

COMMON SOURCE CHARACTERISTICS

S-PARAMETERS

($V_{DS} = 15\text{ Vdc}$, $T_{channel} = 25^\circ\text{C}$, Data Points in MHz)




Figure 5. S_{11s}




Figure 6. S_{12s}




Figure 7. S_{21s}








Figure 8. S_{22s}

COMMON GATE CHARACTERISTICS

ADMITTANCE PARAMETERS

(V_{DG} = 15 Vdc, T_{channel} = 25°C)Figure 9. Input Admittance (Y_{ig})Figure 10. Reverse Transfer Admittance (Y_{rg})Figure 11. Forward Transfer Admittance (Y_{fg})Figure 12. Output Admittance (Y_{og})

COMMON GATE CHARACTERISTICS

S-PARAMETERS

($V_{DS} = 15\text{ Vdc}$, $T_{channel} = 25^\circ\text{C}$, Data Points in MHz)




Figure 13. S_{11g}




Figure 14. S_{12g}




Figure 15. S_{21a}






Figure 16. S_{22a}

MPF102

PACKAGE DIMENSIONS

TO-92 (TO-226)
CASE 29-11
ISSUE AL



NOTES:

1. DIMENSIONING AND TOLERANCING PER ANSI Y14.5M, 1982.
2. CONTROLLING DIMENSION: INCH.
3. CONTOUR OF PACKAGE BEYOND DIMENSION R IS UNCONTROLLED.
4. LEAD DIMENSION IS UNCONTROLLED IN P AND BEYOND DIMENSION K MINIMUM.

DIM	INCHES		MILLIMETERS	
	MIN	MAX	MIN	MAX
A	0.175	0.205	4.45	5.20
B	0.170	0.210	4.32	5.33
C	0.125	0.165	3.18	4.19
D	0.016	0.021	0.407	0.533
E	0.045	0.055	1.15	1.39
F	0.095	0.105	2.42	2.66
G	0.015	0.020	0.39	0.50
H	0.500	---	12.70	---
I	0.250	---	6.35	---
J	0.080	0.105	2.04	2.66
K	---	0.100	---	2.54
L	0.115	---	2.93	---
M	0.135	---	3.43	---

STYLE 5:

1. DRAIN
2. SOURCE
3. GATE

ON Semiconductor and  are registered trademarks of Semiconductor Components Industries, LLC (SCILLC). SCILLC reserves the right to make changes without further notice to any products herein. SCILLC makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does SCILLC assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. "Typical" parameters which may be provided in SCILLC data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. SCILLC does not convey any license under its patent rights nor the rights of others. SCILLC products are not designed, intended, or authorized for use as components in systems intended for surgical implant into the body, or other applications intended to support or sustain life, or for any other application in which the failure of the SCILLC product could create a situation where personal injury or death may occur. Should Buyer purchase or use SCILLC products for any such unintended or unauthorized application, Buyer shall indemnify and hold SCILLC and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that SCILLC was negligent regarding the design or manufacture of the part. SCILLC is an Equal Opportunity/Affirmative Action Employer. This literature is subject to all applicable copyright laws and is not for resale in any manner.

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor
P.O. Box 61312, Phoenix, Arizona 85062-1312 USA
Phone: 480-829-7710 or 800-344-3860 Toll Free USA/Canada
Fax: 480-829-7709 or 800-344-3867 Toll Free USA/Canada
Email: orderlit@onsemi.com

N. American Technical Support: 800-282-9855 Toll Free
USA/Canada

Japan: ON Semiconductor, Japan Customer Focus Center
2-9-1 Kamimeguro, Meguro-ku, Tokyo, Japan 153-0051
Phone: 81-3-5773-3850

ON Semiconductor Website: <http://onsemi.com>

Order Literature: <http://www.onsemi.com/litorder>

For additional information, please contact your
local Sales Representative.