

G4ODC5R



G4 Reed Relay Output, 5 VDC logic, normally open

\$15.50 USD

Price in USA and Canada Only

Availability: In Stock

Add to Cart

Data Sheet



Description Specifications Documents Downloads Accessories

The G4ODC5R is a reed relay, low-contact-resistance DC output. It is a single-pole, single-throw, normally open mechanical relay (Form A, SPST-NO). It was designed for a low-voltage DC load that is purely resistive (no inrush current).

Typical applications for these modules include analog signal and communication line multiplexing. Because of their low 10 VA rating, these modules cannot be used with inductive or capacitive loads (even very small loads) nor 120 VAC.

If you need a Factory Mutual approved version of this module, see the G4ODC5RFM.

My.Opto22

Log In

My.Opto22 Home

My OptoProducts

My Cart

All Opto22

Contact Opto 22

Most Popular

Recently Viewed

MADE IN THE USA



Subscribe to OptoNews

Our OptoNews brings fresh product news, tech tips, and more to your inbox every other week.

my.Opto22

Create or log in to your personal Opto 22 account to manage subscriptions, check orders, and save your favorites.

Get Information

Get free product information, a demonstration, or help from our Pre-sales Engineers.

Products

SNAP PAC System
IO4AB
OptoEMU System
PC-Based I/O
Solid State Relays
All Products

Learn About PACs

About IO4AB
Flash
White Papers
Case Studies
Glossary
Training

Support

OptoKnowledgeBase
Downloads
Documents
Training
Onsite Support
Agency Approvals
Warranties

How to Buy

Find a Distributor
Shop Online
Buy by Phone
International
Pre-sales Engineering

About Opto 22

History
Pressroom
Directions
Sustainability
OptoNews
Corporate Contacts
Careers
Events

Popular Links

OptoForums
Parts List
Product Updates
Blogs & Feeds
Topic Pages