


Manganese Lithium Coin Batteries (ML series): Individual Specifications

ML920S


■ Dimensions(mm)




■ Specification

Nominal voltage (V)	3
Nominal capacity (mAh)	11.0
Continuous standard load (mA)	0.03
Operating temperature (C)	-20 ~ +60

■ Discharge characteristics




■ Consumption current vs. Duration time



ML1220


■ Dimensions(mm)



■ Specification

Nominal voltage (V)	3
Nominal capacity (mAh)	17.0
Continuous standard load (mA)	0.03
Operating temperature (C)	-20 ~ +60

■ Discharge characteristics



■ Consumption current vs. Duration time

