

## Label, can be removed - EML-RM (8X8)R - 0830528

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid  
(<http://download.phoenixcontact.com>)



Label, can be removed, Roll, white, Unlabeled, Can be labeled with: Thermomark R, Thermomark X, Thermomark S, Mounting type: Adhesive, Lettering field: 8 x 8 mm

### Product Features

- ☒ Stick-on device marking, removable
- ☒ Particularly suitable for temporary marking
- ☒ The labels cannot be reused following removal

### Key commercial data

|                      |                                                                                                         |
|----------------------|---------------------------------------------------------------------------------------------------------|
| Packing unit         | 1 PCE                                                                                                   |
| GTIN                 | <br>4 046356 719995 |
| Custom tariff number | 39199000                                                                                                |
| Country of origin    | GERMANY                                                                                                 |

### Technical data

#### General

|                                     |                                |
|-------------------------------------|--------------------------------|
| Length (b)                          | 8 mm                           |
| Width (a)                           | 8 mm                           |
| Color                               | white                          |
| Wipe resistance                     | DIN EN 61010-1 (VDE 0411-1)    |
| Ambient temperature (operation)     | -40 °C ... 120 °C              |
| Ambient temperature (assembly)      | 15 °C                          |
| Components                          | free from silicone and halogen |
| Material                            | Polyester                      |
| Number of individual labels         | 4000                           |
| Number of individual labels per row | 4                              |
| Adhesive                            | Acrylic                        |
| Printability                        | Thermal transfer               |

## Label, can be removed - EML-RM (8X8)R - 0830528

### Technical data

#### General

|                                                              |                                           |
|--------------------------------------------------------------|-------------------------------------------|
| Device                                                       | 5146477 THERMOMARK ROLL                   |
| Device                                                       | 5146723 THERMOMARK ROLL X1                |
| Device                                                       | 5145274 THERMOMARK X1.1                   |
| Device                                                       | 5146231 THERMOMARK X1.2                   |
| Device                                                       | 5146257 THERMOMARK S1.1                   |
| Ink ribbon                                                   | 5145384 THERMOMARK-RIBBON 110             |
| Test specification weathering-resistance                     | Following ISO 4892-2:2006-02 + A1:2009-07 |
| Test duration                                                | 96 h                                      |
| Wipe resistance test result                                  | Test passed                               |
| Salt spray test specification                                | DIN EN ISO 9227:2012-09                   |
| Test duration                                                | 96 h                                      |
| Salt spray testing result                                    | Test passed                               |
| Alternating condensation climate with SO2 test specification | DIN 50018:1997-06                         |
| Climate level                                                | KFW 1.0 S                                 |
| Cycles                                                       | 2                                         |
| Condensation test result                                     | Test passed                               |
| Wipe resistance of test specification inscriptions           | IEC 61010-1:2010-06                       |
| Result                                                       | Test passed                               |

### Classifications

#### ETIM

|          |          |
|----------|----------|
| ETIM 3.0 | EC000761 |
| ETIM 4.0 | EC000761 |
| ETIM 5.0 | EC000761 |

#### UNSPSC

|               |          |
|---------------|----------|
| UNSPSC 11     | 39121410 |
| UNSPSC 12.01  | 39121410 |
| UNSPSC 13.2   | 39121410 |
| UNSPSC 6.01   | 30211811 |
| UNSPSC 7.0901 | 39121410 |

#### eCl@ss

|            |          |
|------------|----------|
| eCl@ss 4.0 | 24190208 |
| eCl@ss 4.1 | 24190208 |
| eCl@ss 5.0 | 27149103 |
| eCl@ss 5.1 | 27141137 |

## Label, can be removed - EML-RM (8X8)R - 0830528

### Classifications

eCl@ss

|            |          |
|------------|----------|
| eCl@ss 6.0 | 27141137 |
| eCl@ss 7.0 | 27141137 |

### Accessories

#### Accessories

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black