

16-bit buffer/line driver; 3-state

74ALVC16244

FEATURES

- Wide supply voltage range of 1.2 V to 3.6 V
- In accordance with JEDEC standard no.8-1A
- CMOS low power consumption
- Multibyte™ flow-through standard pin-out architecture
- Low inductance multiple power and ground pins for minimum noise and ground bounce
- Direct interface with TTL levels
- All data inputs have bushold
- Output drive capability 50 Ω transmission lines @ 85 °C

DESCRIPTION

The 74ALVC16244 is a high-performance, low-power, low-voltage, Si-gate CMOS device and superior to most advanced CMOS compatible TTL families.

The 74ALVC16244 is a 16-bit non-inverting buffer/line driver with 3-state outputs. The 3-state outputs are controlled by the output enable inputs 1OE and 2OE. A HIGH on nOE causes the outputs to assume a high impedance OFF-state. The "16244" is identical to the "16240" but has non-inverting outputs.

FUNCTION TABLE

INPUTS		OUTPUT
nOE	nAn	nYn
L	L	L
L	H	H
H	X	Z

H = HIGH voltage level  
 L = LOW voltage level  
 X = don't care  
 Z = high impedance OFF-state

QUICK REFERENCE DATA

GND = 0 V; T<sub>amb</sub> = 25 °C; t<sub>r</sub> = t<sub>f</sub> = 2.5 ns

SYMBOL	PARAMETER	CONDITIONS	TYPICAL	UNIT
t <sub>PHL</sub> /t <sub>PLH</sub>	propagation delay 1A <sub>n</sub> to 1Y <sub>n</sub> ; 2A <sub>n</sub> to 2Y <sub>n</sub>	C <sub>L</sub> = 15 pF V <sub>CC</sub> = 3.3 V	2.1	ns
C <sub>I</sub>	input capacitance		3.0	pF
C <sub>PD</sub>	power dissipation capacitance per buffer	notes 1 and 2	30	pF

Notes to the quick reference data

1. C<sub>PD</sub> is used to determine the dynamic power dissipation (P<sub>D</sub> in μW)  
 $P_D = C_{PD} \times V_{CC}^2 \times f_i + \sum (C_L \times V_{CC}^2 \times f_o)$  where:  
 f<sub>i</sub> = input frequency in MHz; C<sub>L</sub> = output load capacity in pF;  
 f<sub>o</sub> = output frequency in MHz; V<sub>CC</sub> = supply voltage in V;  
 Σ (C<sub>L</sub> × V<sub>CC</sub><sup>2</sup> × f<sub>o</sub>) = sum of the outputs.
2. The condition is V<sub>i</sub> = GND to V<sub>CC</sub>

ORDERING INFORMATION

TYPE NUMBER	PACKAGES			
	PINS	PACKAGE	MATERIAL	CODE
74ALVC16244DL	48	SSOP48	plastic	SSOP48/SOT370
74ALVC16244DGG	48	TSSOP48	plastic	TSSOP48/SOT362

PINNING

PIN NO.	SYMBOL	NAME AND FUNCTION
1	1OE	'1' output enable input (active LOW)
2, 3, 5, 6	1Y <sub>0</sub> to 1Y <sub>3</sub>	'1Y' data outputs
4, 10, 15, 21, 28, 34, 39, 45	GND	ground (0 V)
7, 18, 31, 42	V <sub>CC</sub>	positive supply voltage
8, 9, 11, 12	2Y <sub>0</sub> to 2Y <sub>3</sub>	'2Y' data outputs
13, 14, 16, 17	3Y <sub>0</sub> to 3Y <sub>3</sub>	'3Y' data outputs
19, 20, 22, 23	4Y <sub>0</sub> to 4Y <sub>3</sub>	'4Y' data outputs
24	4OE	'4' output enable input (active LOW)
25	3OE	'3' output enable input (active LOW)
30, 29, 27, 26	4A <sub>0</sub> to 4A <sub>3</sub>	'4A' data inputs
36, 35, 33, 32	3A <sub>0</sub> to 3A <sub>3</sub>	'3A' data inputs
41, 40, 38, 37	2A <sub>0</sub> to 2A <sub>3</sub>	'2A' data inputs
47, 46, 44, 43	1A <sub>0</sub> to 1A <sub>3</sub>	'1A' data inputs
48	2OE	'2' output enable input (active LOW)



## 16-bit buffer/line driver; 3-state

74ALVC16244

**DC CHARACTERISTICS FOR 74ALVC244**




For the DC characteristics see chapter "ALVC family characteristics", section "Family specifications".

**AC CHARACTERISTICS FOR 74ALVC244**GND = 0 V;  $t_r = t_f = 2.5$  ns;  $C_L = 50$  pF

SYMBOL	PARAMETER	$T_{amb}$ (°C)			UNIT	TEST CONDITIONS	
		MIN.	TYP.	MAX.		$V_{CC}$ (V)	WAVEFORMS
$t_{PHL}/t_{PLH}$	propagation delay	-	-	-	ns	1.2	Fig. 5
	1A <sub>n</sub> to 1Y <sub>n</sub> ;	-	-	4.0		2.7	
	2A <sub>n</sub> to 2Y <sub>n</sub>	-	2.3*	3.6		3.0 to 3.6	
$t_{PZH}/t_{PZL}$	3-state output enable time	-	-	-	ns	1.2	Figs 6
	1 $\overline{OE}$ to 1Y <sub>n</sub> ;	-	-	5.5		2.7	
	2 $\overline{OE}$ to 2Y <sub>n</sub>	-	-	4.7		3.0 to 3.6	
$t_{PHZ}/t_{PLZ}$	3-state output disable time	-	-	-	ns	1.2	Figs 6
	1 $\overline{OE}$ to 1Y <sub>n</sub> ;	-	-	6.0		2.7	
	2 $\overline{OE}$ to 2Y <sub>n</sub>	-	-	5.0		3.0 to 3.6	

**Notes:** All typical values are measured at  $T_{amb} = 25$  °C.  
 \* Typical values are measured at  $V_{CC} = 3.3$  V.

AC WAVEFORMS



- Notes:
- (1)  $V_M = 0.5 \cdot V_{CC}$  at  $V_{CC} < 2.7$  V  
 $V_M = 1.5$  V at  $V_{CC} \geq 2.7$  V
  - (2)  $V_X = V_{OL} + 0.3$  V at  $V_{CC} \geq 2.7$  V  
 $V_X = V_{OL} + 0.1 \cdot V_{CC}$  at  $V_{CC} < 2.7$  V
  - (3)  $V_Y = V_{OH} - 0.3$  V at  $V_{CC} \geq 2.7$  V  
 $V_Y = V_{OH} - 0.1 \cdot V_{CC}$  at  $V_{CC} < 2.7$  V
  - (4)  $V_{OL}$  and  $V_{OH}$  are the typical output voltage drop that occur with the output load.