

Label for rough plastic surfaces - EML-HA (70X32)R - 0830607

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://download.phoenixcontact.com>)



Label for rough plastic surfaces, Roll, white, Unlabeled, Can be labeled with: Thermomark R, Thermomark X, Thermomark S, Mounting type: Adhesive, Lettering field: 70 x 32 mm

The figure shows a version of the article

Key commercial data

Packing unit	1 PCE
GTIN	 4 046356 719612
Custom tariff number	39199000
Country of origin	GERMANY

Technical data

General

Length (b)	70 mm
Width (a)	32 mm
Color	white
Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
Ambient temperature (operation)	-40 °C ... 150 °C
Ambient temperature (assembly)	5 °C
Components	free from silicone and halogen
Material	Polyester
Number of individual labels	1000
Number of individual labels per row	1
RoHS compliant	Yes
Halogen-free	Yes
Silicone-free	Yes
Cadmium-free	Yes
Adhesive	Acrylic

Label for rough plastic surfaces - EML-HA (70X32)R - 0830607

Technical data

General

Printability	Thermal transfer
Device	5146477 THERMOMARK ROLL
Device	5146723 THERMOMARK ROLL X1
Device	5145274 THERMOMARK X1.1
Device	5146231 THERMOMARK X1.2
Device	5146257 THERMOMARK S1.1
Ink ribbon	5145384 THERMOMARK-RIBBON 110
Ink ribbon	0829544 THERMOMARK-RIBBON 110 BU
Ink ribbon	0829542 THERMOMARK-RIBBON 110 GN
Ink ribbon	0829543 THERMOMARK-RIBBON 110 RD
Test specification weathering-resistance	Following ISO 4892-2:2006-02 + A1:2009-07
Test duration	96 h
Wipe resistance test result	Test passed
Salt spray test specification	DIN EN ISO 9227:2012-09
Test duration	96 h
Salt spray testing result	Test passed
Alternating condensation climate with SO2 test specification	DIN 50018:1997-06
Climate level	KFW 1.0 S
Cycles	2
Condensation test result	Test passed
Wipe resistance of test specification inscriptions	IEC 61010-1:2010-06
Result	Test passed
Foil strength	50 µm
Adhesive strength	45 µm

Classifications

ETIM

ETIM 3.0	EC000761
ETIM 4.0	EC000761
ETIM 5.0	EC000761

UNSPSC

UNSPSC 11	39121410
UNSPSC 12.01	39121410
UNSPSC 13.2	39121410
UNSPSC 6.01	30211811

Label for rough plastic surfaces - EML-HA (70X32)R - 0830607

Classifications

UNSPSC

UNSPSC 7.0901	39121410
---------------	----------

eCl@ss

eCl@ss 4.0	24190219
eCl@ss 4.1	24190219
eCl@ss 5.0	27149103
eCl@ss 5.1	27141137
eCl@ss 6.0	27141137
eCl@ss 7.0	27141137

Accessories

Accessories

Ink ribbon - THERMOMARK-RIBBON 110 - 5145384



Ink ribbon, Length: 300000 mm, Width: 110 mm, Color: black