


## Model 4911A Retractable Sheath Banana Plug Each End Patch Cord



### MATERIALS:

Retractable Sheath Banana Plug:

Plug Body: Brass, Nickel Plated

Banana Spring: Beryllium Copper, Nickel Plated

Compression Spring: Stainless Steel

Tip: Nylon, Color Matches Color of Wire

Insulation: Nylon Molded to the Plug and Wire. Color Matches Color of Wire.

Wire: 18 AWG, Stranding 65 x 36 t.c., PVC Insulated, .144 (3,66mm) O.D.

Marking: "POMONA 4911A-XX-\*".

### RATINGS:

Operating Temperature: +55° C (+131° F) Max.

Operating Voltage: 1000 Volts AC/DC Max.

Current: 10 Amperes

### ORDERING INFORMATION: Model 4911A-XX-\*

XX = Wire Length, Standard Lengths: 4" (10,16cm), 8" (20,32cm), 12" (30,48cm), 24" (60,96cm), 36" (91,44cm), 48" (121,92cm) & 60" (152,4cm). Additional lengths can be quoted upon request.

\* = Color, -0 Black, -2 Red

Ordering Example: 4911A-12-2 Patch Cord is 12" (30,48cm), Color is Red.

All dimensions are in inches. Tolerances (except noted): .xx = ±.02" (.51 mm), .xxx = ±.005" (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA

# Pomona<sup>®</sup>

**Model 4911A**  
**Retractable Sheath Banana Plug**  
**Each End Patch Cord**

All dimensions are in inches. Tolerances (except noted): .xx =  $\pm .02$ " (.51 mm), .xxx =  $\pm .005$ " (.127 mm).  
All specifications are to the latest revisions. Specifications are subject to change without notice.  
Registered trademarks are the property of their respective companies. Made in USA

6/9/99  
SY/EH/LS

**Sales: 800-490-2361 Fax: 888-403-3360**  
**Technical Assistance: 800-241-2060**

C:\Laura Goldberg\FlukeDataSheet\4911A\_1\_01.doc

PomonaACCESS 90608 (800) 444-6785 or (425) 446-6010  
More drawings available at [www.pomonaelectronics.com](http://www.pomonaelectronics.com)

Page 2 of 2

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Pomona:

[4911A-36-0](#) [4911A-36-2](#) [4911A-60-0](#) [4911A-60-2](#) [4911A-24-0](#) [4911A-24-2](#) [4911A-12-2](#) [4911A-12-0](#) [4911A-48-0](#)  
[4911A-48-2](#)