

MATERIAL AND FINISH

Insulator: Polycarbonate, UL-94V-0 rated
Contacts: Brass, Nickel plated

ELECTRICAL SPECIFICATIONS:

Current rating: 16 A
Voltage rating: 250 VAC
Current rating: 20 A
Voltage rating: 250 VAC
Insulation resistance: 100 Mohm min. at 500 VDC
Dielectric withstanding voltage: 2000 VAC for one minute

ORDERING CODE:

42R07-3 1 2 3

1) COLOR




1 = BLACK
2 = GRAY

2) ELECTRICAL CIRCUIT CONFIGURATION

1 = 20A 250V 70°C 2+GROUND
2 = 20A 250V 155°C 2+GROUND
3 = 20A 250V 70°C 2 POLE

3) PANEL THICKNESS

REV	DATE	CHANGES	CHNG	CHK	APPR	PB	PB	PB
A	11/24/04	ADD 13.0, 9.7, 13.6, 5.0 DIM						



RECOMMENDED
PANEL CUTOUT

P/N	A	MAX. PANEL THICKNESS
42R07-3X2X-150	1.5	1.5
42R07-3X2X-200	2.0	2.0
42R07-3X2X-250	2.5	2.5

ADDITIONAL PANEL THICKNESS
AVAILABLE ON REQUEST

TOLERANCE UNLESS OTHERWISE SPECIFIED	
X ± 1	
X.X ± 0.4	
X.XX ± 0.20	

Power Dynamics, Inc.

Phone: 973 560-0019 Whippany, New Jersey Fax: 973 560-0076

PART: 16/20A IEC 60320 APPL. INLET; QC

TERMINALS: SNAP-IN, PANEL MOUNT

PART #:		42R07-3X2X-XXXD3		SHEET 1 of 1	
SIZE:		A		ALL DIMENSIONS FOR REFERENCE ONLY	
SCALE:		NTS		DIMENSIONS ARE IN MILLIMETERS	
				REV: C	

DRAWN BY	GQ	DATE:	08/24/01
CHECK BY	TD	DATE:	08/29/01
APPR BY	PB	DATE:	08/29/01

RoHS
COMPLIANT