



NPN General Purpose Amplifier

- ◇ Complementary PNP Type Available (MMBT3906)
- ◇ Epoxy Meets UL 94 V-0 Flammability Rating
- ◇ Surface Mount SOT-23 Package
- ◇ Rohs Compliant / Green EMC



Equivalent Circuit



Device Marking Code	
<b>MMBT3904</b>	<b>1AM●</b>

**Maximum Ratings (Ta=25°C Unless Otherwise Noted)**

Symbol	Parameter	Value	Unit
V <sub>CB0</sub>	Collector-Base Voltage	60	V
V <sub>CE0</sub>	Collector-Emitter Voltage	40	V
V <sub>EB0</sub>	Emitter-Base Voltage	6	V
I <sub>C</sub>	Collector Current	200	mA
P <sub>C</sub>	Collector Power Dissipation*	225	mW
R <sub>θJA</sub>	Thermal Resistance From Junction To Ambient	556	°C/W
T <sub>J</sub>	Junction Temperature	150	°C
T <sub>stg</sub>	Storage Temperature	-55~+150	°C

\*Device mounted on an FR4 PCB, single-sided copper, tin-plated and standard footprint.


**Electrical Characteristics @ 25°C Unless Otherwise Specified**

Symbol	Parameter	Test Conditions	Min	Max	Units
$V_{(BR)CEO}$	Collector–Emitter Breakdown Voltage	$I_C=1.0mA, I_B=0$	40		V
$V_{(BR)CBO}$	Collector–Base Breakdown Voltage	$I_C=10\mu A, I_E=0$	60		V
$V_{(BR)EBO}$	Emitter–Base Breakdown Voltage	$I_E=10\mu A, I_C=0$	6.0		V
$I_{CBO}$	Collector Cutoff Current	$V_{CB}=30V, I_E=0$		50	nA
$I_{CEX}$	Collector Cutoff Current	$V_{CE}=30V, V_{BE}=3.0V$		50	nA
$h_{FE}$	DC Current Gain	$I_C=0.1mA, V_{CE}=1.0V$	40		
		$I_C=1.0mA, V_{CE}=1.0V$	70		
		$I_C=10mA, V_{CE}=1.0V$	100	300	
		$I_C=50mA, V_{CE}=1.0V$	60		
		$I_C=100mA, V_{CE}=1.0V$	30		
$V_{CE(sat)}$	Collector–Emitter Saturation Voltage	$I_C=10mA, I_B=1.0mA$		0.2	V
		$I_C=50mA, I_B=5.0mA$		0.3	
$V_{BE(sat)}$	Base–Emitter Saturation Voltage	$I_C=10mA, I_B=1.0mA$	0.65	0.85	V
		$I_C=50mA, I_B=5.0mA$		0.95	
$f_T$	Transition Frequency	$I_C=10mA, V_{CE}=20V, f=100MHz$	300		MHZ
$C_{obo}$	Output Capacitance	$V_{CB}=5.0V, I_E=0, f=1.0MHz$		4.0	PF
$C_{ibo}$	Input Capacitance	$V_{BE}=0.5V, I_C=0, f=1.0MHz$		8.0	PF
NF	Noise Figure	$I_C=100\mu A, V_{CE}=5.0V, R_S=1.0k\Omega, f=10Hz$ to 15.7kHz		5.0	dB


**Switching Characteristics**

Symbol	Parameter	Test Conditions	Min	Max	Units
$t_d$	Delay Time	$V_{CC}=3.0V, V_{BE}=0.5V, I_C=10mA, I_{B1}=1.0mA$		35	ns
$t_r$	Rise Time			35	ns
$t_s$	Storage Time	$V_{CC}=3.0V, I_C=10mA, I_{B1}=I_{B2}=1.0mA$		200	ns
$t_f$	Fall Time			50	ns


# RATING AND CHARACTERISTICS CURVES (MMBT3904)




Static Characteristics




DC Current Gain Characteristics




Collector-Emitter Saturation Voltage Characteristics



Base-Emitter Saturation Voltage Characteristics



Base-Emitter Voltage Characteristics



Collector Power Derating Curve


# PACKAGING OF DIODE

REEL PACK

PACKAGE	PACKING CODE	REEL ( EA )	COMPONENT SPACE(mm)	TAPE SPACE (mm)	REEL DIA (mm)	CARTON SIZE (mm)	EA PER CARTON	GROSS WEIGHT(Kg)
SOT-23/-3L	-T	3,000	---	---	178	438*438*220	180,000	---


## Package Dimensions

Package outline : SOT23



Symbol	Dimensions in mm	
	Min.	Max.
A	2.800	3.040
B	2.100	2.640
C	1.200	1.400
D	0.890	1.030
E	1.780	2.050
F	0.450	0.600
G	0.013	0.100
H	0.900	1.110
J	0.085	0.180
K	0.370	0.510
L	0.300	0.500

### SOT23 Package Outline



### Land Pattern Recommendation

Notice:

1. Lead plating: Pb free solder
2. Lead thickness includes solder plating
3. Lead frame: CAC-5
4. Other Tolerance:  $\pm 0.05$

## DISCLAIMER NOTICE

Rectron Inc reserves the right to make changes without notice to any product specification herein, to make corrections, modifications, enhancements or other changes. Rectron Inc or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies. Data sheet specifications and its information contained are intended to provide a product description only. "Typical" parameters which may be included on RECTRON data sheets and/ or specifications can and do vary in different applications and actual performance may vary over time. Rectron Inc does not assume any liability arising out of the application or use of any product or circuit.

Rectron products are not designed, intended or authorized for use in medical, life-saving implant or other applications intended for life-sustaining or other related applications where a failure or malfunction of component or circuitry may directly or indirectly cause injury or threaten a life without expressed written approval of Rectron Inc. Customers using or selling Rectron components for use in such applications do so at their own risk and shall agree to fully indemnify Rectron Inc and its subsidiaries harmless against all claims, damages and expenditures.