

SPECIFICATION

- Supplier : Samsung electro-mechanics
- Product : Multi-layer Ceramic Capacitor
- Samsung P/N : **CL10B122KB8NNWC**
- Description : **CAP, 1.2nF, 50V, ±10%, X7R, 0603**

A. Samsung Part Number

CL 10 B 122 K B 8 N N W C
 ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪

① Series	Samsung Multi-layer Ceramic Capacitor									
② Size	0603 (inch code)		L: 1.6 ± 0.1 mm		W: 0.8 ± 0.1 mm					
③ Dielectric	X7R		⑧ Inner electrode		Ni					
④ Capacitance	1.2 nF		Termination		Cu					
⑤ Capacitance tolerance	±10 %		Plating		Sn 100% (Pb Free)					
⑥ Rated Voltage	50 V		⑨ Product		Normal					
⑦ Thickness	0.8 ± 0.1 mm		⑩ Special		Product for Network application					
			⑪ Packaging		Cardboard Type,7"reel(4,000ea)					

B. Samsung Reliability Test and Judgement condition

	Performance	Test condition
Capacitance	Within specified tolerance	1kHz±10% 1.0±0.2Vrms
Tan δ (DF)	0.025 max.	
Insulation Resistance	More than 500Mohm·μF	Rated Voltage 60~120 sec.
Appearance	No abnormal exterior appearance	Visual inspection
Withstanding Voltage	No dielectric breakdown or mechanical breakdown	250% of the rated voltage
Temperature Characteristics	X7R (From -55℃ to 125℃, Capacitance change should be within ±15%)	
Adhesive Strength of Termination	No peeling shall be occur on the terminal electrode	500g·F, for 10±1 sec.
Bending Strength	Capacitance change : within ±12.5%	Bending to the limit (1mm) with 1.0mm/sec.
Solderability	More than 75% of terminal surface is to be soldered newly	SnAg3.0Cu0.5 solder 245±5℃, 3±0.3sec. (preheating : 80~120℃ for 10~30sec.)
Resistance to Soldering heat	Capacitance change : within ±7.5% Tan δ, IR : initial spec.	Solder pot : 270±5℃, 10±1sec.

	Performance	Test condition
Vibration Test	Capacitance change : within $\pm 5\%$ Tan δ , IR : initial spec.	Amplitude : 1.5mm From 10Hz to 55Hz (return : 1min.) 2hours $\times$ 3 direction (x, y, z)
Moisture Resistance	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.05 max IR : More than $25M\Omega \cdot \mu F$	With rated voltage $40 \pm 2^{\circ}C$, 90~95%RH, 500+12/-0 hours.
High Temperature Resistance	Capacitance change : within $\pm 12.5\%$ Tan δ : 0.05 max IR : More than $50M\Omega \cdot \mu F$	With 200% of the rated voltage Max. operating temperature 1000+48/-0 hours.
Temperature Cycling	Capacitance change : within $\pm 7.5\%$ Tan δ , IR : initial spec.	1 cycle condition Min. operating temperature $\rightarrow 25^{\circ}C$ $\rightarrow$ Max. operating temperature $\rightarrow 25^{\circ}C$ 5 cycles test

C. Recommended Soldering method :

Reflow (Reflow Peak Temperature : $260 \pm 0/-5^{\circ}C$, 10sec. Max)

* For the more detail Specification, Please refer to the Samsung MLCC catalogue.