

Round dies M DIN EN 22568 HSS, ground (formerly DIN 223)

Type: Type B closed,
preslotted
Thread: metric, DIN ISO 13
Tolerance: ISO - 6g
Surface: bright
Right-hand cutting

For unalloyed or low-alloyed steels up to
800 N/mm² strength and non-ferrous metals.
The thread is cut in one operation.



1.6

Packing unit:
Individual plastic pack

Nominal thread size	Pitch mm	Outside Ø mm	Thickness mm	Article no.	Price / each €
M 1	0,25	16,0	5,0	237 010	
M 1,2	0,25	16,0	5,0	237 012	
M 1,4	0,30	16,0	5,0	237 014	
M 1,6	0,35	16,0	5,0	237 016	
M 1,7	0,35	16,0	5,0	237 017	
M 1,8	0,35	16,0	5,0	237 018	
M 2	0,40	16,0	5,0	237 020	
M 2,2	0,45	16,0	5,0	237 022	
M 2,3	0,40	16,0	5,0	237 023	
M 2,5	0,45	16,0	5,0	237 025	
M 2,6	0,45	16,0	5,0	237 026	
M 3	0,50	20,0	5,0	237 030	
M 3,5	0,60	20,0	5,0	237 035	
M 4	0,70	20,0	5,0	237 040	
M 4,5	0,75	20,0	7,0	237 045	
M 5	0,80	20,0	7,0	237 050	
M 6	1,00	20,0	7,0	237 060	
M 7	1,00	25,0	9,0	237 070	
M 8	1,25	25,0	9,0	237 080	
M 9	1,25	25,0	9,0	237 090	
M 10	1,50	30,0	11,0	237 100	
M 11	1,50	30,0	11,0	237 110	
M 12	1,75	38,0	14,0	237 120	
M 14	2,00	38,0	14,0	237 140	
M 16	2,00	45,0	18,0	237 160	
M 18	2,50	45,0	18,0	237 180	
M 20	2,50	45,0	18,0	237 200	
M 22	2,50	55,0	22,0	237 220	
M 24	3,00	55,0	22,0	237 240	
M 27	3,00	65,0	25,0	237 270	
M 30	3,50	65,0	25,0	237 300	
M 33	3,50	65,0	25,0	237 330	
M 36	4,00	65,0	25,0	237 360	
M 39	4,00	75,0	30,0	237 390	
M 42	4,50	75,0	30,0	237 420	
M 45	4,50	90,0	36,0	237 450	
M 48	5,00	90,0	36,0	237 480	
M 52	5,00	90,0	36,0	237 520	

Emphasised articles are new additions.