




(1.00 mm) .0394"


FTM-125-02-L-DV



FTMH-116-02-L-DV-P



FTMH-111-02-F-DV-ES-A



SMT MICRO TERMINAL STRIPS

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com?FTMH or www.samtec.com?FTM

Insulator Material:
Black Liquid Crystal Polymer

Terminal Material:
Phosphor Bronze

Current Rating (FTMH/CLM):
2.8 A per pin
(2 pins powered)

Operating Temp Range:
-55 °C to +125 °C

Plating:
Sn or Au over
50 μ" (1.27 μm) Ni
RoHS Compliant:
Yes

Mates with:
CLM, MLE

PROCESSING

Lead-Free Solderable:
Yes

-DV Lead Coplanarity:
(0.10 mm) .004" max
-DH Lead Coplanarity:
(0.10 mm) .004" max (05-25)
(0.15 mm) .006" max (26-50)*
*(.004" stencil solution
may be available; contact
IPG@samtec.com)

RECOGNITIONS


For complete scope of
recognitions see
www.samtec.com/quality



ALSO AVAILABLE (MOQ Required)

- End shrouds with board locks
- Molded end shrouds for 05 through 08 positions
- Other platings

Note:
Some sizes, styles and
options are non-standard,
non-returnable.



TYPE STRIP

1

NO. PINS PER ROW

LEAD STYLE

PLATING OPTION

FTMH
= SMT Micro

FTM
= Micro Low Profile

FTMH
= 05 thru 50

FTM
= 02 thru 50 (unshrouded)
= 05 thru 46 (shrouded)

-02

= (1.91 mm) .075" Post
(Mates with MLE)

-03




= (1.65 mm) .065" Post
(Mates with CLM)

-F

= Gold flash on post,
Matte Tin on tail


-L

= 10 μ" (0.25 μm)
Gold on post, Matte Tin on tail




FTMH	
OPTION	B
-ES	(1.57) .062
-EC	(4.06) .160
-EP	(5.49) .216


FTMH	
LEAD STYLE	A
-02	(1.91) .075
-03	(1.65) .065




-ES OPTION




-EC OPTION




-EP OPTION




-DV OPTION



-DH OPTION



-A OPTION



-P OPTION


Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM


All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.


FTMH-122-02-F-DV-EC




FTMH-120-02-L-DV




FTMH-135-02-F-DH





FTMH-125-02-L-DV



FTMH-128-03-L-DV-EP






FTMH, FTM SERIES

ROW
OPTION

-DV
= Dual Vertical

-DH
= Dual Horizontal
(FTMH only)



Shrouded options removed for clarity

FLEX SHROUD OPTIONS

(FTMH-DV only with
9 pins/row minimum)

-ES
= End Shroud

-EC
= End Shroud with Locking Clip
(Manual placement required)

-EP
= End Shroud with Guide Post
(Use only when mating with CLM)




FTMH	
OPTION	C
-S	(7.00) .276
-SA	(4.00) .157

(FTMH only)

-S
= End Shroud
(05 positions minimum).
Molded or press-fit shroud at
Samtec's discretion
(See assembly print at
www.samtec.com?FTM
for dimensions)

-SA
= End Shroud with Alignment Pins
(05 through 46 positions)

FTMH	
LEAD STYLE	D
-02	(1.91) .075
-03	(1.65) .065


OTHER
OPTIONS

-A
= Alignment Pin
(3 positions minimum)
Metal or plastic at Samtec discretion
(FTMH-DV only)

-K
= (2.50 mm) .098" DIA Polyimide
Film Pick & Place Pad
(FTMH-DH only)

-P
= Plastic Pick & Place Pad
(-DV only)
(6 positions minimum FTMH)
(7 positions minimum FTM)

-TR
= Tape & Reel



Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.
Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.