






TSW-109-10-F-D-RA



TSW-112-07-F-T



HTSW-120-13-T-D



TSW-114-16-G-S-RE

## TSW, HTSW SERIES

## LEAD STYLE

## PLATING OPTION

## ROW OPTION

## OTHER OPTIONS

## -F

= Gold flash on post, Matte Tin on tail

## -L

= 10 μ" (0.25 μm) Gold on post, Matte Tin on tail

## -G

= 10 μ" (0.25 μm) Gold on post, Gold flash on balance

## -T

= Matte Tin

## OTHER SOLUTIONS

- Elevated Right-angle option
- Shunts

## -S

= Single Row

## -D

= Double Row

## -T

= Triple Row

## -Q


= Double Row (5.08 mm) .200" row space

## -RA or -RE

= Right-angle

## -NA

= Right-angle (using straight body for coplanar mating with SSW-RA series)



## -LL


= Locking Lead



Two leads per strip crimped in opposite directions on or near centerline. See charts for available styles. N/A with single row 1 or 2 positions. Recommended hole size (1.02 mm ± 0.03 mm) .040" ± .001"

## -LC

= Locking Clip (Styles -08 thru -13 &amp; -22 only)



Requires 4 pin minimum (NA with -T, -Q, -RA or -RE)

## -LA

= -RA Option with -LL Option

## -"XXX"


= Polarized Position

## Straight Pin Versions

(Specify "LEAD STYLE" from chart)

| STYLE | A               | B                 | C               |
|-------|-----------------|-------------------|-----------------|
| * -05 | (3.30)<br>.130  | (8.51)<br>.335    | (2.67)<br>.105  |
| * -06 | (2.41)<br>.095  | (7.62)<br>.300    | (2.67)<br>.105  |
| * -07 | (2.54)<br>.100  | (10.92)<br>.430   |                 |
| * -08 | (5.08)<br>.200  | (13.46)<br>.530   |                 |
| * -09 | (10.16)<br>.400 | (18.54)<br>.730   | (5.84)<br>.230  |
| * -10 | (12.70)<br>.500 | (21.08)<br>.830   |                 |
| * -11 | (15.24)<br>.600 | (23.62)<br>.930   |                 |
| * -12 | (17.78)<br>.700 | (26.16)<br>.1.030 |                 |
| * -13 | (22.86)<br>.900 | (31.24)<br>.1.230 |                 |
| * -14 | (2.79)<br>.110  | (13.46)<br>.530   | (8.13)<br>.320  |
| * -15 | (7.87)<br>.310  | (18.54)<br>.730   | (13.21)<br>.520 |
| * -16 | (2.79)<br>.110  | (21.08)<br>.830   | (15.74)<br>.620 |

\* Available with -LL (Locking Lead) Option



Specify -07 for best mate with IDXX Series IDC Cable

| STYLE | A                 | B                 | C                 |
|-------|-------------------|-------------------|-------------------|
| * -18 |                   | (23.62)<br>.930   | (18.29)<br>.720   |
| * -19 | (2.79)<br>.110    | (26.16)<br>.1.030 | (20.83)<br>.820   |
| * -20 |                   | (31.24)<br>.1.230 | (25.91)<br>.1.020 |
| * -21 |                   | (36.32)<br>.1.430 | (30.99)<br>.1.220 |
| * -22 | (7.62)<br>.300    | (16.00)<br>.630   | (5.84)<br>.230    |
| * -23 | (2.92)<br>.115    | (11.30)<br>.445   | (6.73)<br>.265    |
| * -24 | (5.33)<br>.210    | (12.15)<br>.480   | (8.13)<br>.320    |
| * -25 | (3.20)<br>.126    | (11.58)<br>.456   |                   |
| * -26 | (25.40)<br>.1.000 | (33.78)<br>.1.330 | (5.84)<br>.230    |
| * -27 | (20.32)<br>.800   | (28.70)<br>.1.130 |                   |
| * -28 | (23.11)<br>.910   | (33.78)<br>.1.330 | (8.13)<br>.320    |
| * -29 | (18.03)<br>.710   | (28.70)<br>.1.130 |                   |
| * -30 | (0.89)<br>.035    | (9.27)<br>.365    | (5.84)<br>.230    |
| * -41 | (1.27)<br>.050    | (11.94)<br>.470   | (8.13)<br>.320    |

+ Style -41 &amp; -42 available with HTSW only.


▲ Except: Style -26 (0.46) .018 DIA Tail

## Right-Angle Versions

(Specify "LEAD STYLE" from chart and select -RA or -RE from other options)

| -RA LEAD STYLE | SINGLE (-S)     |                | DOUBLE (-D)     |                 | TRIPLE (-T & -Q) |  |
|----------------|-----------------|----------------|-----------------|-----------------|------------------|--|
|                | A               | C              | A               | A               | A                |  |
| * -08          | (2.29)<br>.090  |                | (2.29)<br>.090  | (2.29)<br>.090  |                  |  |
| * -09          | (7.37)<br>.290  |                | (7.37)<br>.290  | (7.37)<br>.290  |                  |  |
| * -10          | (9.91)<br>.390  | (5.84)<br>.230 | (9.91)<br>.390  | (9.91)<br>.390  |                  |  |
| * -11          | (12.45)<br>.490 |                | (12.45)<br>.490 | (12.45)<br>.490 |                  |  |
| * -12          | (14.99)<br>.590 |                | (14.99)<br>.590 | (14.99)<br>.590 |                  |  |
| * -13          | (20.07)<br>.790 |                | (20.07)<br>.790 | N/A             |                  |  |
| * -16          | (5.08)<br>.200  | (8.13)<br>.320 | (5.08)<br>.200  | (5.08)<br>.200  |                  |  |
| * -21          | (25.15)<br>.990 | (5.84)<br>.230 | N/A             | N/A             |                  |  |
| * -22          | (4.83)<br>.190  |                | (4.83)<br>.190  | (4.83)<br>.190  |                  |  |
| * -25          | (2.54)<br>.100  | (8.13)<br>.320 | (2.54)<br>.100  | (2.54)<br>.100  |                  |  |
| * -27          | (22.61)<br>.890 | (5.84)<br>.230 | N/A             |                 |                  |  |
| * -28          | (17.53)<br>.690 |                | (17.53)<br>.690 |                 |                  |  |
| * -29          | (20.32)<br>.800 | (8.13)<br>.320 | N/A             |                 |                  |  |
| * -30          | (15.24)<br>.600 |                | (15.24)<br>.600 |                 |                  |  |

\* Available with -LA (Locking Lead) Option



| LEAD STYLE | B              |
|------------|----------------|
| -RA        | (1.52)<br>.060 |
| -RE        | (4.06)<br>.160 |

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

All parts within this catalog are built to Samtec's specifications.

Customer specific requirements must be approved by Samtec and identified in a Samtec customer-specific drawing to apply.