

High-Voltage Rectifier Diodes

Parameter Type No.	Absolute Maximum Ratings					Electrical Characteristics (Ta = 25)						Others			
	V _{RM} (kV)	I _{R(AV)} (mA)	I _{FSM} (A) 50Hz Half-cycle Sinewave Single Shot	T _c ()	T _{stg} ()	V _F (V)		I _R (μ A)	I _{R(H)} (μ A)	t _{rr} (μ s)		Mass (g)	Fig.	Remarks	
						max	I _F (mA)			V _R = V _{RM} max	V _R = V _{RM} T _a = 100 max				I _F /I _{RP} (mA)
SHV-02	2	2.0 TV high voltage rectifier Capacitive load	0.3	100	- 40 to + 120	10	1	3	0.18	10/10	-	0.15	Ⓐ	For general FBT	
SHV-03S	3											16	0.16		Ⓑ
SHV-03	3											40	0.32		Ⓒ
SHV-10	10											45			
SHV-12	12											55			
SHV-14	14											60			
SHV-16	16		75	Ⓓ											
SHV-20	20		0.5	100	- 40 to + 120	10	1	3	0.18	10/10	-	0.2	Ⓒ	For layer- built FBT	
SHV-24	24											26	0.32		Ⓔ
SHV-06NK	6											36	0.2		Ⓒ
SHV-08NK	8											40			
SHV-10K	10											45			
SHV-12K	12											48	0.3		Ⓔ
SHV-06UNK	6		60												
SHV-08UNK	8		68												
SHV-10UK	10		90												
SHV-12UK	12	0.5	100	- 40 to + 120	10	1	3	0.15	10/10	0.30	0.2	Ⓒ	For high- frequency layer-built FBT		
SHV-16UK	16										30	0.3		Ⓔ	
SHV-08DN	8	0.5	100	- 40 to + 120	10	1	3	0.15	10/10	0.20	0.2	Ⓒ	For Ultra high-frequency layer-built FBT		
SHV-12DN	12										45	0.3		Ⓓ	
HVR-1X-40B	9	350	20	60	- 40 to + 130	9	350	10	V _Z = 9.5 to 15kV	-	-	3.67	Ⓒ	For Microwave Oven	
UX-C2B	8		15	(Ta)	- 30 to + 130	13.5		V _Z = 8.5kV min.	0.1	100/100	Ⓓ		For Inverter-type Microwave Oven		

Type No.	External Dimensions (Unit: mm)	Marking (Cathode Mark)	
		Pattern	Color
SHV-02	Fig. Ⓐ 		White
SHV-03S			Red
SHV-03	Fig. Ⓑ 		White
SHV-06NK	Fig. Ⓒ 		White
SHV-06UNK			Red
SHV-08NK			White
SHV-08UNK			Red
SHV-08DN		Red	
SHV-12DN	Fig. Ⓓ 		Red

Type No.	External Dimensions (Unit: mm)	Marking (Cathode Mark)	
		Pattern	Color
SHV-10	Fig.Ⓔ 		White
SHV-10K			
SHV-10UK			Red
SHV-12			
SHV-12K			
SHV-12UK			White
SHV-14			
SHV-16		Fig.Ⓕ 	
SHV-16UK			Red
SHV-20			White
SHV-24			

The SHV series of diodes have been miniaturized by resin on the assumption for remolding. Measures against creeping discharge and humidity stress must be taken when using these diodes.
 The taping specifications of the SHV series differ from ordinary diodes. (P.10)

SHV series





Fig.Ⓒ




Fig.Ⓓ

