


SANYO

Cadnica




Cell Type N-500A

Specifications


Nominal Capacity			500mAh				
Nominal Voltage			1.2V				
Charging Current		Standard	50mA				
		Quick	150mA				
		Fast	750mA				
Charging Time		Standard	14 to 16Hrs.				
		Quick	4 to 6Hrs.				
		Fast	about 1Hr.				
Ambient Temperature	Charge	Standard	0°C to +45°C [+32°F to 113°F]				
		Quick	10°C to +45°C [+50°F to 113°F]				
		Fast	0°C to +45°C [+32°F to 113°F]				
	Discharge		-20°C to +60°C [-4°F to 140°F]				
	Storage		-30°C to +50°C [-22°F to 122°F]				
Internal Impedance (Av.) (at. 50% discharge)			9.0mΩ (at 1000Hz)				
Weight			19g/0.67oz				
Dimensions(D)×(H) (with tube)			17.0	⁰ _{-0.5}	× 28.5	⁰ ₋₁	mm
			0.67	⁰ _{-0.02}	× 1.12	⁰ _{-0.04}	inch

Typical Characteristics


Charge




Discharge (at high rate)




Charge



Discharge (at high rate)



Discharge (at low rate)



Temperature (Charge & Discharge)

