

# RE11LAMW

on-delay timing relay - 1 s..100 h - 24..240 V  
AC/DC - solid state output

Product availability: Stock - Normally stocked in distribution facility

## Main

Commercial Status	Commercialised
Range of product	Zelio Time
Product or component type	Modular timing relay
Discrete output type	Solid state
Width pitch dimension	0.69 in (17.5 mm)
Component name	RE11L
Time delay type	A
Time delay range	0.1...1 s 1...10 h 1...10 min 1...10 s 10...100 h 6...60 min 6...60 s
[Us] rated supply voltage	24...240 V AC/DC 50/60 Hz

## Complementary

Control type	Selector switch on front panel
Voltage range	0.85...1.1 Us
Nominal output current	0.7 A
Connections - terminals	Screw terminals, clamping capacity: 2 x 2.5 mm <sup>2</sup> without cable end Screw terminals, clamping capacity: 2 x 1.5 mm <sup>2</sup> with cable end Screw terminals, clamping capacity: 1 x 4 mm <sup>2</sup> without cable end
Housing material	Self-extinguishing
Repeat accuracy	+/- 0.5 % conforming to IEC 61812-1
Temperature drift	+/- 0.05 %/°C
Voltage drift	+/- 0.2 %/V
Setting accuracy of time delay	+/- 10 % of full scale at 25 °C conforming to IEC 61812-1
Minimum pulse duration	0.05 s
Reset time	<= 350 ms on de-energisation
On-load factor	100 %
Power consumption in VA	<= 32 VA 240 V
Power consumption in W	<= 1.5 W 240 V <= 0.6 W 24 V
Breaking capacity	0.7 A AC/DC at 68 °F (20 °C) 0.5 A AC/DC conforming to UL
Maximum output current	20 A < 10 ms
Minimum switching current	10 mA
Leakage current	< 5 mA
Maximum switching voltage	250 V
Voltage drop	8 V 2-wire 4 V 3-wire
Electrical durability	100000000 cycles
Mechanical durability	100000000 cycles
Marking	CE
Creepage distance	4 kV/3 conforming to IEC 60664-1
Surge withstand	2 kV (common mode) conforming to IEC 61000-4-5 level 3 1 kV (differential mode) conforming to IEC 61000-4-5 level 3
Mounting support	35 mm symmetrical mounting rail conforming to EN 50022
Product weight	0.13 lb(US) (0.06 kg)

## Environment

Immunity to microbreaks	> 10 ms
Derating factor	5 mA/°C
Dielectric strength	2.5 V 1 mA/1 minute conforming to IEC 60664 2.5 V 1 mA/1 minute conforming to IEC 60255-5
Standards	73/23/EEC 89/336/EEC 93/68/EEC EN 50081-1/2 EN 50082-1/2 IEC 60669-2-3 IEC 61812-1
Product certifications	CSA CULus
Ambient air temperature for storage	-22...140 °F (-30...60 °C)
Ambient air temperature for operation	-4...140 °F (-20...60 °C)
IP degree of protection	IP50 (front panel) conforming to IEC 60529 IP40 (housing) conforming to IEC 60529 IP20 (terminal block) conforming to IEC 60529
Vibration resistance	0.35 mm (f = 10...55 Hz) conforming to IEC 60068-2-6
Relative humidity	93 % without condensation conforming to IEC 60068-2-3
Resistance to electrostatic discharge	8 kV (in contact) conforming to IEC 61000-4-2 level 3 6 kV (in air) conforming to IEC 61000-4-2 level 3
Resistance to electromagnetic fields	9.14 V/yd (10 V/m), 80 MHz to 1 GHz conforming to IEC 61000-4-3 level 3 9.14 V/yd (10 V/m), 80 MHz to 1 GHz conforming to ENV 50140/204 level 3
Resistance to fast transients	2 kV, direct conforming to IEC 61000-4-4 level 3 1 kV, capacitive connecting clip conforming to IEC 61000-4-4 level 3
Immunity to radioelectric fields	10 V (0.15...80 MHz) conforming to ENV 50141 (IEC 61000-4-6 level 3)
Immunity to voltage dips	95 %/5 s conforming to IEC 61000-4-11 60 %/100 ms conforming to IEC 61000-4-11 30 %/10 ms conforming to IEC 61000-4-11
Disturbance radiated/conducted	Class B conforming to EN 55022 (EN 55011 group 1)

## Ordering and shipping details

Category	22370 - RE, RM MISC TIMERS & COUNTERS
Discount Schedule	CP2
GTIN	00785901468943
Nbr. of units in pkg.	1
Package weight(Lbs)	0.14
Product availability	Stock - Normally stocked in distribution facility
Returnability	Y
Country of origin	FR

## Contractual warranty

Period	18 months
--------	-----------