


<b>Rating</b>
6A 125V AC 3A 250V AC
<b>Contact resistant</b>
50mΩ Max
<b>Insulation resistant</b>
DC 500V 100MΩ Min
<b>Dielectric strength</b>
AC 1000V 1 minute
<b>Cut-out</b>



**FEATURES**

- \* MATERIAL: Alkyd base (UL flame: 94V-0) for high insulation, Stainless steel cover for corrosion resistant.
- \* Contacts and Terminals are copper with silver alloy and silver plated.
- \* Epoxy sealed for dust and moisture resistant.
- \* Colorful handle covers and waterproof boot are optional for toggle type A.



TA1

FUNCTION		LEVER	TERMINAL
<p>0 1</p> <p>ON OFF 2P SPST</p>	<p>0 5</p> <p>ON OFF (ON) 3P SPDT</p>	<p>A Standard</p>	<p>1  SO</p> <p>2  PC</p> <p>3  PC Angle(2.54)</p> <p>5  PC Angle(3.8)</p>
<p>0 2</p> <p>ON ON 3P SPDT</p>	<p>0 6</p> <p>ON ON 3P SPDT</p>	<p>F Flat</p>	
<p>0 3</p> <p>ON OFF ON 3P SPDT</p>		<p>G Plastic</p>	
<p>0 4</p> <p>(ON) OFF (ON) 3P SPDT</p>			

