



SHOULDER ELECTRONICS LIMITED

SAW FILTER FOR TELECOMMUNICATION

Part Number	Center Frequency (MHz)	Passband width(MHz)	Insertion Loss(dB) Within Passband	Stopband Attenuation (dB)		I/O Impedance		SAMPLE DIMENSIONS TEST CIRCUIT
				Fo-100i× Fo-40.8	Fo+40.8i× Fo+100	A Type	B Type	
HDFiöiöiöA HDFiöiöiöB	402,406,410,414 418,422,426,430 434,438,442,446 450,454,458,462 465,470,474,478 482,486,490,494 498,502,506,510 514,518,522,526	FoiÀ2.0	4.5dB Max	55dB Min	55dB Min	50i, /0pF	150i, /0pF	

ii



[[Home](#) | [About SDE](#) | [Request Info](#) | [Saw Filter](#) | [Saw Resonator](#) | [Ceramic Resonator](#) | [Ceramic Discriminator](#) | [Ceramic Filter1](#) | [Ceramic Filter2](#) | [Ceramic Trap](#) | [Crystal Unit](#) | [Clock Oscillator](#) | [Dielectric Filter](#) | [Dielectric Resonator](#)]

Copyright 2001 by Shoulder Electronics Limited
 Contact Us: Tel: 86-755-2979884 Fax:86-755-2979885
 Questions or comments: info@china-shoulder.com