

SINGLE COLOR LED


2 x 3mm Semi-Round Shape

3363K / 3373K Series

STANDARD COLOR



Outline Dimensions



Absolute Maximum Ratings

(Ta=25°C)

Item	Symbol	Red			Orange	Yellow	Yellow Green	Green	Pure Green	Units
		BR	MPR	MVR	MAA	MAY	MPY	MPG	MBG	
Power Dissipation	Pd	100	75	75	70	85	85	70	70	mW
Forward Current	If	50	30	30	25	30	30	25	25	mA
Peak Forward Current	IfM	300	75	75	60	75	75	60	60	mA
Reverse Voltage	Vr	4	4	4	4	4	4	4	4	V
Operating Temperature	Topr	-30 to +85								°C
Storage Temperature	Tstg	-30 to +100								°C
Derating (DC)*	If	0.67	0.40		0.33	0.40		0.33		mA/°C

* Ta=25°C, IfM applies for the pulse width 1msec. and duty cycle 1/20
The current derating for operation applies when the temperature is above 25°C


Electro-Optical Characteristics

*3363K lens is clear and 3373K lens is diffused

**The viewing angle is an average and will vary by color (Ta=25°C)

Part No.	Material	Emitted Color	Lens Color*	Luminous Intensity Iv			Wavelength Spectral Line Half Width				Forward Voltage Vf			Reverse Current Ir		Viewing Angle** (2 1/2)	
				MIN.	TYP.	If	Peak p TYP.	Dominant d TYP.	TYP.	If	TYP.	MAX.	If	MAX.	Vr		
				mcd			mA			nm		mV		µA			V
BR3363K/3373K	GaAlAs	Red	Pastel Red	10/8	20/16	20	660	647	30	20	1.7	2.0	20	20	4	35/40°	
MPR3363K/3373K	GaP			2/1.5	4/3	10	700	635	100	10	2.1	2.8	10	20	4		
MVR3363K/3373K	GaAsP			8/6	16/12	20	630	624	30	20	2.0	2.8	20	20	4		
MAA3363K/3373K	GaAsP	Orange	Pastel Orange	20/10	40/20	20	605	606	30	20	2.2	2.8	20	20	4		
MAY3363K/3373K	GaAsP	Yellow	Pastel Yellow	20/10	40/20	20	580	590	30	20	2.2	2.8	20	20	4		
MPY3363K/3373K	GaP	Yellow Green		30/20	60/40	20	570	572	30	20	2.1	2.8	20	20	4		
MPG3363K/3373K	GaP	Green	Pastel Green	15/10	30/20	20	560	567	30	20	2.1	2.8	20	20	4		
MBG3363K/3373K	GaP	Pure Green		8/5	16/10	20	555	558	30	20	2.1	2.8	20	20	4		
Units				mcd			mA			nm		mV		µA		V	Deg.

Spatial Distribution (x)



Operation Current Derating Chart

