

RCA Audio Patch Cords

Shielded RCA Patch Cords
 Black 2.8mm OD PVC Jacket
 Fully Molded Construction
 Nickel or Gold-Plated High-Retention RCA Plugs
 Color-Coded Red-White/Red-White or Black-Black
 AWG26 Stranded Copper Center Conductor
 Low-Loss 95% Spiral-Wound Copper Shield
 99.99% Pure Oxygen-Free Copper Wire

- 255-100** 6' RCA Jack to RCA Plug
- 255-105** 10' RCA Jack to RCA Plug
- 255-110** 6' RCA Plug to RCA Plug
- 255-115** 10' RCA Plug to RCA Plug
- 255-117** 25' RCA Plug to RCA Plug
- 255-118** 25' RCA Plug to Plug – AWG24
- 255-120** 3' 2-RCA Plugs to 2-RCA Plugs
- 255-121** 3' 2-RCA Plug-Plug Gold Plated
- 255-125** 6' 2-RCA Plugs to 2-RCA Plugs
- 255-126** 6' 2-RCA Plug-Plug Gold Plated
- 255-127** 9' 2-RCA Plugs to 2-RCA Plugs
- 255-128** 9' 2-RCA Plug-Plug Gold Plated
- 255-130** 12' 2-RCA Plugs to 2-RCA Plugs
- 255-131** 12' 2-RCA Plug-Plug Gold Plated
- 255-132** 15' 2-RCA Plugs to 2-RCA Plugs
- 255-133** 15' 2-RCA Plug-Plug Gold Plated
- 255-134** 20' 2-RCA Plugs to 2-RCA Plugs
- 255-135** 25' 2-RCA Plugs to 2-RCA Plugs
- 255-136** 25' 2-RCA Plug-Plug Gold Plated
- 255-138** 50' 2-RCA Plug-Plug Nickel Plated **◀ NEW**
- 255-140** 6' 2-RCA Plugs – RCA Piggyback
- 255-145** 12' 2-RCA Plugs – RCA Piggyback
- 255-150** 6' 4-RCA Plug-Plug – Color Coded
- 255-175** 6' 2-RCA Jacks to 2-RCA Plugs
- 255-244** 3' 2-RCA Plugs to 2-RCA Angle Plugs
- 255-246** 6' 2-RCA Plugs to 2-RCA Angle Plugs

Black

255-100 6' Nickel
255-105 10' Nickel

Black

255-118 25' AWG24 Nickel

Red

White

Red

White

255-140 6' Nickel
255-145 12' Nickel

Red

White

Yellow

Black

Red

White

Yellow

Black

255-150 6' Nickel

Red

White

Red

White

255-175 6' Nickel

Black

255-110 6' Nickel
255-115 10' Nickel
255-117 25' Nickel



Red

White

Red

White

- 255-120** 3' Nickel
- 255-121** 3' Gold
- 255-125** 6' Nickel
- 255-126** 6' Gold
- 255-127** 9' Nickel
- 255-128** 9' Gold
- 255-130** 12' Nickel
- 255-131** 12' Gold
- 255-132** 15' Nickel
- 255-133** 15' Gold
- 255-134** 20' Nickel
- 255-135** 25' Nickel
- 255-136** 25' Gold
- 255-138** 50' Nickel

Red

White

Red

White

255-244 3' Nickel
255-246 6' Nickel