


P = GOLD FLASH OVERALL

(260°C FOR 10 SECS MAX.)

[illegible]

A diagram of a pin with a central shaft and a wider head. The head is divided into two sections: a top section labeled 'HEAD DIM.' and a bottom section labeled 'TAIL DIM.'. The dimensions are indicated by vertical arrows pointing to the respective sections.

ZA	0.120	3.05	0.120	3.05
ZB	0.120	3.05	0.095	2.41
ZC	0.120	3.05	0.260	6.60
ZD	0.120	3.05	0.610	15.49
ZI	0.520	13.21	0.110	2.79
ZJ	0.720	18.29	0.110	2.79
ZO	0.820	20.83	0.110	2.79
ZQ	1.020	25.91	0.110	2.79
ZR	1.220	30.99	0.110	2.79

UNLESS OTHERWISE SPECIFIED: DIMENSIONS ARE IN INCHES[MM] TOLERANCES: ANGULAR: $.XX = \pm .012 [.30]$ $.XXX = \pm .008 [.20]$ $.XXXX = \pm .0040 [.100]$ INTERPRET DIMENSIONS AND TOLERANCING PER: ASME Y14.5M-2009	DRAWN	DATE	NAME
		03/21/2011	LH
	THE INFORMATION HEREIN CONTAINS PROPRIETARY INFORMATION OF SULLINS ELECTRONICS AND IS NOT TO BE REPRODUCED, USED OR DISCLOSED TO OTHERS FOR ANY PURPOSE EXCEPT AS SPECIFICALLY AUTHORIZED IN WRITING BY AN OFFICER OF SULLINS ELECTRONICS.		
	