



# MBRF1035 THRU MBRF10100

## Isolation 10.0 AMPS. Schottky Barrier Rectifiers



Voltage Range  
35 to 100 Volts  
Current  
10.0 Amperes


### Features

- ✦ Plastic material used carries Underwriters Laboratory Classifications 94V-0
- ✦ Metal silicon junction, majority carrier conduction
- ✦ Low power loss, high efficiency
- ✦ High current capability, low forward voltage drop
- ✦ High surge capability
- ✦ For use in low voltage, high frequency inverters, free wheeling, and polarity protection applications
- ✦ Guardring for overvoltage protection
- ✦ High temperature soldering guaranteed:  
260°C/10 seconds, 0.25" (6.35mm) from case

### Mechanical Data

- ✦ Cases: ITO-220AC molded plastic body
- ✦ Terminals: Lead solderable per MIL-STD-750, Method 2026
- ✦ Polarity: As marked
- ✦ Mounting position: Any
- ✦ Mounting torque: 5 in. - lbs. max
- ✦ Weight: 0.08 ounce, 2.24 grams

### ITO-220AC



### Maximum Ratings and Electrical Characteristics

Rating at 25°C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, derate current by 20%

Type Number	Symbol	MBRF 1035	MBRF 1045	MBRF 1050	MBRF 1060	MBRF 1090	MBRF 10100	Units
Maximum Recurrent Peak Reverse Voltage	$V_{RRM}$	35	45	50	60	90	100	V
Maximum RMS Voltage	$V_{RMS}$	24	31	35	42	63	70	V
Maximum DC Blocking Voltage	$V_{DC}$	35	45	50	60	90	100	V
Maximum Average Forward Rectified Current See Fig. 1	$I_{(AV)}$	10						A
Peak Repetitive Forward Current (Square Wave, 20KHz) at $T_c=135^\circ\text{C}$	$I_{FRM}$	20.0						A
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	$I_{FSM}$	150						A
Peak Repetitive Reverse Surge Current (Note 1)	$I_{RRM}$	1.0			0.5			A
Voltage Rate of Change (Rated $V_R$ )	$dV/dt$	10,000						V/ $\mu\text{S}$
Maximum Instantaneous Forward Voltage at (Note 2) $I_F=10\text{A}, T_c=25^\circ\text{C}$ $I_F=10\text{A}, T_c=125^\circ\text{C}$ $I_F=20\text{A}, T_c=25^\circ\text{C}$ $I_F=20\text{A}, T_c=125^\circ\text{C}$	$V_F$	-		0.80		0.85		V
		0.57		0.70		0.71		
		0.84		0.95		-		
		0.72		0.85		-		
Maximum Instantaneous Reverse Current @ $T_c=25^\circ\text{C}$ at Rated DC Blocking Voltage (Note 2) @ $T_c=125^\circ\text{C}$	$I_R$	0.1			0.1			mA
		15.0			6.0			mA
Typical Junction Capacitance	$C_j$	390		300		220		pF
Maximum Thermal Resistance, Junction to Case	$R_{\theta_{JC}}$	4.0						$^\circ\text{C}/\text{W}$
Operating Junction Temperature Range	$T_J$	-65 to +150						$^\circ\text{C}$
Storage Temperature Range	$T_{STG}$	-65 to +175						$^\circ\text{C}$

- Notes: 1. 2.0us Pulse Width,  $f=1.0$  KHz  
 2. Pulse Test: 300us Pulse Width, 1% Duty Cycle  
 3. Mounted on Heatsink Size of 2 in x 3 in x 0.25 in Al-Plate.

## RATINGS AND CHARACTERISTIC CURVES (MBRF1035 THRU MBRF10100)

FIG.1- FORWARD CURRENT DERATING CURVE




FIG.2- MAXIMUM NON-REPETITIVE FORWARD SURGE CURRENT




FIG.3- TYPICAL INSTANTANEOUS FORWARD CHARACTERISTICS




FIG.4- TYPICAL REVERSE CHARACTERISTICS




FIG.5- TYPICAL JUNCTION CAPACITANCE




FIG.6- TYPICAL TRANSIENT THERMAL CHARACTERISTICS

