

POWER RELAY

1 POLE—1, 3, 5, 10 A (MEDIUM LOAD CONTROL)

LZ SERIES

■ FEATURES

- UL, CSA
- 4 kinds of contact ratings
—Low level to 10 amps switching
- Standard and high sensitivity types available
- High surge strength version available
- UL class B (130°C) insulation type available (only plastic sealed type)
- Printed circuit terminals—fits grid with 0.1 inch
- Plastic sealed type backfilled with nitrogen available



■ ORDERING INFORMATION

[Example] LZ – B 12 H M S E – K HV – UC
 (a) (b) (c) (d) (e) (f) (g) (h) (i) (j)

(a)	Series Name	LZ : LZ Series
(b)	Coil Heat Proof Class	Nil : Standard type B : UL class B insulation type (130°C)
(c)	Nominal Voltage	Refer to the COIL DATA CHART
(d)	Contact Rating	Nil : 3 A H : 5 A V : 10 A W : 1 A (bifurcated)
(e)	Contact Arrangement	Nil : 1 form C (SPDT) M : 1 form A (SPST-NO)
(f)	Coil Type	Nil : Standard type S : High sensitive type
(g)	Contact Material (Rating)	Nil : Gold overlay silver-palladium (only LZ-W) Nil : Gold overlay silver-nickel (3 A, 5 A) Nil : Silver alloy (10 A) (only LZ-V) E : Silver-nickel (3 A, 5 A)
(h)	Enclosure	Nil : Flux free type K : Plastic sealed type (recommended for new designs) C : Plastic sealed type (with tape)
(i)	Surge Strength	Nil : Standard type (4,000 V) HV : High dielectric strength type (6,000 V)
(j)	Standard	UC: UL, CSA approved type

■ SAFETY STANDARD AND FILE NUMBERS

UL508 (File No. E56140, E45026)

C22.2 No. 0, No. 14 (File No. LR35579)

Please note that UL/CSA ratings may differ from the standard ratings.

Please request when the approval markings are required on the cover and/or relay recognized by SEV is required.

Type	Nominal voltage	Contact rating
LZ- ()W LZ- ()WS	1.5 to 48 VDC 1.5 to 24 VDC	0.8 A 240 VAC resistive 1 A 30 VDC/120 VAC resistive
LZ- () LZ- ()S	1.5 to 48 VDC 1.5 to 24 VDC	1/10 HP 120 VAC/240 VAC 2.5 A 240 VAC resistive 3 A 30 VDC/120 VAC resistive Pilot duty D 150
LZ- ()H LZ- ()HS	1.5 to 48 VDC 1.5 to 24 VDC	1/8 HP 120 VAC/240 VAC 4 A 240 VAC resistive 5 A 30 VDC/120 VAC resistive Pilot duty C 150
LZ- ()VM	1.5 to 48 VDC	1/4 HP 120 VAC/240 VAC 7 A 240 VAC resistive 10 A 24 VDC/120 VAC resistive Pilot duty C 150

■ SPECIFICATIONS

LZ-()Type (Standard Type)

Item			10 A Type	5 A Type	3 A Type	1 A Type
			LZ-()VM	LZ-()H, LZ-()HE	LZ(), LZ-()E	LZ-()W
Contact	Arrangement		1 form A (SPST-NO) or 1 form C (SPDT)			
	Material		Silver alloy	Gold overlay silver alloy Silver alloy (LZ-HE, E)		Gold overlay silver-palladium
	Style		Single			Bifurcated
	Resistance (initial) (at 1 A 6 VDC)		Maximum 100 mΩ	Maximum 70 mΩ (LZ-H,LZ) Maximum 100 mΩ (LZ-HE, E)		Maximum 50 mΩ
	Rating (resistive)		10 A 120 VAC/24 VDC 1/4 H 120 VAC	5 A 120 VAC/24 VDC 1/8 H 120 VAC	3 A 120 VAC/30 VDC 1/10 H 120 VAC	1 A 120 VAC/30 VDC
	Maximum Carrying Current		10 A	5 A		1 A
	Maximum Switching Power		1,680 VA, 240 W	960 VA, 120 W	600 VA, 90 W	190 VA, 30 W
	Maximum Switching Voltage		250 VAC, 150 VDC			
	Maximum Switching Current		10 A	5 A	3 A	1 A
	Minimum Switching Load*1		100 mA 5 VDC	10 mA 5 VDC (LZ-H) 100 mA 5 VDC (LZ-HE)	10 mA 5 VDC (LZ-)	0.1 mA 100 VDC 100 mA 5 VDC (LZ-E)
Coil	Nominal Power (at 20°C)		0.45 to 0.60 W			
	Operate Power (at 20°C)		0.17 to 0.22 W			
	Operating Temperature		-30°C to +70°C (no frost) (refer to the CHARATERISTIC DATA)			
Time Value	Operate (at nominal voltage)		Maximum 7 ms			
	Release (at nominal voltage)		Maximum 4 ms			
Insulation	Resistance (at 500 VDC)		Minimum 250 MΩ			
	Dielectric Strength	between open contacts	750 VAC 1 minute			
		between coil and contacts	2,000 VAC 1 minute			
	Surge Strength		Standard type: 4,000 V (at 1.2×50 μs) High dielectric strength Type: 6,000 V (at 1.2×50 μs)			
Life	Mechanical		2 × 10 ⁷ operations minimum			
	Electrical		1 × 10 ⁵ operations minimum (contact rating)			
Other	Vibration Resistance	Misoperation	10 to 55 Hz (double amplitude of 3.3 mm)			
		Endurance	10 to 55 Hz (double amplitude of 3.3 mm)			
	Shock Resistance	Misoperation	100 m/s ² (11 ±1 ms)			
		Endurance	1,000 m/s ² (6 ±1 ms)			
	Weight		Approximately 7.7 g			

*1 Minimum switching loads mentioned above are reference values. Please perform the confirmation test with the actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

■ SPECIFICATIONS

LZ-() S Type (High Sensitive Type)

Item			5 A Type	3 A Type	1 A Type
			LZ-()HS, LZ()HSE	LZ-()S, LZ-()SE	LZ-()WS
Contact	Arrangement		1 form A (SPST-NO) or 1 form C (SPDT)		
	Material		Gold overlay silver alloy (single type)		Gold overlay silver-palladium (bifurcated type)
	Resistance (initial) (at 1 A 6 VDC)		Maximum 70 mΩ (LZ-HS, S) Maximum 100 mΩ (LZ-HSE, SE)		Maximum 50 mΩ
	Rating	Resistive	5 A 120 VAC/24 VDC	3 A 120 VAC/24 VDC	1 A 120 VAC/24 VDC
		Motor Load	1/8 H 120 VAC	1/10 H 120 VAC	
	Maximum Carrying Current		5 A		1 A
	Maximum Switching Power		960 VA, 120 W	600 VA, 90 W	190 VA, 30 W
	Maximum Switching Voltage		250 VAC, 150 VDC		
	Maximum Switching Current		5 A	3 A	1 A
	Minimum Switching Load*1		10 mA 5 VDC (LZ-HS, S) 100 mA 5 VDC (LZ-HSE, SE)		0.1 mA 100 mVDC
Coil	Nominal Power (at 20°C)		0.33 W		
	Operate Power (at 20°C)		0.14 W		
	Operating Temperature		-30°C to +80°C (no frost) (refer to the CHARACTERISTIC DATA)		
Time Value	Operate (at nominal voltage)		Maximum 7 ms		
	Release (at nominal voltage)		Maximum 4 ms		
Insulation	Resistance		Minimum 250 MΩ		
	Dielectric Strength	between open contacts	750 VAC 1 minute		
		between coil and contacts	2,000 VAC 1 minute		
	Surge Strength		Standard type : 4,000 V (at 1.2 × 50μs) High dielectric strength type: 6,000 V (at 1.2 × 50μs)		
Life	Mechanical		2 × 10 ⁷ operations minimum		
	Electrical		1 × 10 ⁵ operations minimum (rated load)		
Other	Vibration	Misoperation	10 to 55 Hz (double amplitude of 3.3 mm)		
	Resistance	Endurance	10 to 55 Hz (double amplitude of 3.3 mm)		
	Shock	Misoperation	100 m/s ² (11 ±1 ms)		
	Resistance	Endurance	1,000 m/s ² (6 ±1 ms)		
	Weight		Approximately 7.7 g		













*1 Minimum switching loads mentioned above are reference values. Please perform the confirmation test with the actual load before production since reference values may vary according to switching frequencies, environmental conditions and expected reliability levels.

■ COIL DATA CHART










	MODEL				Nominal voltage	Coil resistance (±10%)	Must operate voltage	Must release voltage	Nominal power
	Single			Bifurcated					
	10 A Type	5 A Type	3 A Type	1 A Type					
Standard Type	LZ-(B) 1.5 VM	LZ-(B) 1.5 H (M) (E)	LZ-(B) 1.5 (M) (E)	LZ-(B) 1.5 W (M)	1.5 VDC	5 Ω	0.97 VDC	0.08 VDC	450 mW
	LZ-(B) 3 VM	LZ-(B) 3 H (M) (E)	LZ-(B) 3 (M) (E)	LZ-(B) 3 W (M)	3 VDC	20 Ω	1.95 VDC	0.15 VDC	450 mW
	LZ-(B) 5 VM	LZ-(B) 5 H (M) (E)	LZ-(B) 5 (M) (E)	LZ-(B) 5 W (M)	5 VDC	56 Ω	3.25 VDC	0.25 VDC	450 mW
	LZ-(B) 6 VM	LZ-(B) 6 H (M) (E)	LZ-(B) 6 (M) (E)	LZ-(B) 6 W (M)	6 VDC	80 Ω	3.9 VDC	0.3 VDC	450 mW
	LZ-(B) 9 VM	LZ-(B) 9 H (M) (E)	LZ-(B) 9 (M) (E)	LZ-(B) 9 W (M)	9 VDC	180 Ω	5.85 VDC	0.45 VDC	450 mW
	LZ-(B) 12 VM	LZ-(B) 12 H (M) (E)	LZ-(B) 12 (M) (E)	LZ-(B) 12 W (M)	12 VDC	320 Ω	7.8 VDC	0.6 VDC	450 mW
	LZ-(B) 18 VM	LZ-(B) 18 H (M) (E)	LZ-(B) 18 (M) (E)	LZ-(B) 18 W (M)	18 VDC	720 Ω	11.7 VDC	0.9 VDC	450 mW
	LZ-(B) 24 VM	LZ-(B) 24 H (M) (E)	LZ-(B) 24 (M) (E)	LZ-(B) 24 W (M)	24 VDC	1,280 Ω	15.6 VDC	1.2 VDC	450 mW
	LZ-(B) 48 VM	LZ-(B) 48 H (M) (E)	LZ-(B) 48 (M) (E)	LZ-(B) 48 W (M)	48 VDC	3,800 Ω	28.8 VDC	2.4 VDC	600 mW
	LZ-(B) 100 VM	LZ-(B) 100 H (M) (E)	LZ-(B) 100 (M) (E)	LZ-(B) 100 W (M)	100 VDC	22,200 Ω	65.0 VDC	5.0 VDC	450 mW
High Sensitive Type		LZ-(B)1.5 H (M)S (E)	LZ-(B)1.5 (M)S (E)	LZ-(B) 1.5 W (M) S	1.5 VDC	6.8 Ω	0.97 VDC	0.08 VDC	330 mW
		LZ-(B) 3 H (M)S (E)	LZ-(B) 3 (M)S (E)	LZ-(B) 3 W (M) S	3 VDC	27 Ω	1.95 VDC	0.15 VDC	330 mW
		LZ-(B) 5 H (M)S (E)	LZ-(B) 5 (M)S (E)	LZ-(B) 5 W (M) S	5 VDC	80 Ω	3.25 VDC	0.25 VDC	330 mW
		LZ-(B) 6 H (M)S (E)	LZ-(B) 6 (M)S (E)	LZ-(B) 6 W (M) S	6 VDC	110 Ω	3.9 VDC	0.3 VDC	330 mW
		LZ-(B) 9 H (M)S (E)	LZ-(B) 9 (M)S (E)	LZ-(B) 9 W (M) S	9 VDC	250 Ω	5.85 VDC	0.45 VDC	330 mW
		LZ-(B) 12 H (M)S (E)	LZ-(B) 12 (M)S (E)	LZ-(B) 12 W (M) S	12 VDC	440 Ω	7.8 VDC	0.6 VDC	330 mW
		LZ-(B) 18 H (M)S (E)	LZ-(B) 18 (M)S (E)	LZ-(B) 18 W (M) S	18 VDC	990 Ω	11.7 VDC	0.9 VDC	330 mW
		LZ-(B) 24 H (M)S (E)	LZ-(B) 24 (M)S (E)	LZ-(B) 24 W (M) S	24 VDC	1,780 Ω	15.6 VDC	1.2 VDC	330 mW

Note : All values in the table are measured at 20°C.

CHARACTERISTIC DATA




REFERENCE DATA



DIMENSIONS


Dimensions

LZ-M type




Schematics

(BOTTOM VIEW)



PC board mounting

hole layout
(BOTTOM VIEW)




LZ SERIES

■ DIMENSIONS


● Dimensions

LZ-M-K, LZ-M-C type (Plastic sealed type)




Dotted line: Seal tape [LZ-M-C Type]


LZ type




● Schematics (BOTTOM VIEW)





● PC board mounting hole layout (BOTTOM VIEW)



LZ-K, LZ-C type (Plastic sealed type)



Dotted line: Seal tape [LZ-C Type]



Unit: mm

**Fujitsu Takamisawa
International
Headquarter
Offices**

www.fujitsu.takamisawa.com

Japan

Fujitsu Takamisawa Component Limited
Global Marketing and Sales
Gotanda-Chuo Building
3-5, Higashigotanda 2-chome, Shinagawa-ku
Tokyo 141, Japan
Tel: (81-3) 5449-7010
Fax: (81-3) 5449-2626

North and South America

Fujitsu Takamisawa America, Inc.
250 E. Caribbean Drive
Sunnyvale, CA 94089 U.S.A.
Tel: (1-408) 745-4900
Fax: (1-408) 745-4970

Europe

Fujitsu Takamisawa Europe B.V.
Diamantlaan 25
2132 WV Hoofddorp
Netherlands
Tel: (31-23) 5560910
Fax: (31-23) 5560950

Asia Pacific

Fujitsu Takamisawa Asia Pacific Pte. Ltd.
102E Pasir Panjang Road
#04-01 Citilink Warehouse Complex
Singapore 118529
Tel: (65) 375-8560
Fax: (65) 273-3021