

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					C	ECR-13-014508	13OCT2015	UKo	Ak
					C1	ECR-14-007162	21SET2017	AP	AK
					C2	ECR-18-017686 (Add prod. site; PN list update)	07MAY2019	HC	LS
					C3	ECR-24-204093 (Add prod. site CZ)	27MAR2024	Stei	Ried

Order Number - ABCCCC

made in Austria:

A : Line (1...Line1)

B : Day (1-7, Mon=1, Tue=2.)

C : Time(hhmm)

made in Czech Rep.:

A : Packing day (1-7, Sun=1)

B : Shift (1=day, 2=night)

C : Lot number (sequential)

made in Portugal:

A : Packing day (1-7, Sat=1)

B : Shift (1=day, 2=night)

C : Lot number (sequential)

AT : made in Austria

CZ : made in Czech Rep.

historic:

H : made in Switzerland (until 2013)

PT : made in Portugal (until 2023)

Q : made in China (until 2016)

C : made in China (until 2012)

Date code (YYWW)

Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM00..	00	1.5	3-1462037-7		3-1462037-5	
IM00NS	00N	1.5				1-1462038-0*
IM01..	01	3	1462037-1	4-1462037-0	1462037-4	
IM01B..	01B	3	4-1462039-5			
IM01C..	01C	3	1462038-4			
IM01NS	01N	3				1-1462038-1
IM01N..L	01N	3				4-1462039-3
IM01P	01P	3	9-1462037-3			
IM02..	02	4.5	1462037-9	1-1462037-1	1-1462037-3	6-1462039-4
IM02..	02	4.5	8-1462039-1			
IM02..L	02	4.5	2-1462039-3			
IM02C..	02C	4.5	1462038-1			
IM02D..	02D	4.5	9-1462038-8			
IM02H..	02H	4.5	1-1462039-1			
IM02I..	02I	4.5	1462047-9	1462047-8		
IM02NS	02N	4.5				1-1462038-2

© COPYRIGHT 2000

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

*obsolete

DRAWING ALIAS: IM0C-DOK17

DIMENSIONS:		DWN	21FEB2003	MATERIAL	FINISH
mm		HD 9121		-	-
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK HD 9121	21FEB2003	TE Connectivity	
		APVD HD 9121	21FEB2003		
		PRODUCT SPEC			
		APPLICATION SPEC			
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-				NAME IM-Relay Marking SIZE A 4 CAGE CODE 00779 DRAWING NO C- 1462037-1 RESTRICTED TO -	
		WEIGHT -		CUSTOMER DRAWING SCALE 10:1 SHEET 1 OF 6 REV C3	

2000

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
IM02NS..L	02N	4.5				2-1462039-4			
IM02PNS	02P	4.5				5-1462039-8			
IM03..	03	5	1-1462037-4	1-1462037-6	1-1462037-8				
IM03..L	03	5	2-1462039-5						
IM03..X	03	5	8-1462039-6						
IM03C..	03C	5	1462038-2		4-1462039-7				
IM03D..	03D	5	9-1462038-9	3-1462039-3	8-1462039-3				
IM03I..	03I	5		1472047-6					
IM03NS	03N	5				1-1462038-3			
IM03P..	03P	5	5-1462039-5						
IM03PNS	03P	5				5-1462039-9			
IM04..	04	6	4-1462037-2	4-1462037-4	4-1462037-1				
IM04B..	04B	6	6-1462039-5						
IM04NS	04N	6				1-1462038-4			
IM05..	05	9	3-1462037-4	4-1462037-5	2-1462037-2				
IM05B..	05B	9	5-1462039-3						
IM05C..	05C	9	1462038-3						
IM05D..	05D	9	1-1462039-7						
IM05NS	05N	9				1-1462038-5			
IM06..	06	12	2-1462037-3	4-1462037-6	2-1462037-7				
IM06C..	06C	12	9-1462037-9	3-1462039-4	4-1462037-9				
IM06D..	06D	12	1-1462039-8	7-1462039-0	3-1462039-8				
IM06NS	06N	12				1-1462038-6			
IM06P..	06P	12	5-1462039-6						
IM06PNS	06P	12				6-1462039-0			
IM07..	07	24	4-1462037-7	4-1462037-8	3-1462037-0				
*obsolete									
DIMENSIONS: mm				DWN HD 9121 21FEB2003 CHK HD 9121 21FEB2003 APVD HD 9121 21FEB2003 PRODUCT SPEC - APPLICATION SPEC - WEIGHT -		MATERIAL - FINISH -		DRAWING ALIAS: IM0C-DOK17	
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m 0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-				NAME IM-Relay Marking		SIZE A 4 CAGE CODE 00779 DRAWING NO C-1462037-1 RESTRICTED TO -		CUSTOMER DRAWING	
SCALE 10:1				SHEET 2 OF 6		REV C3			


2000

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2000



LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
IM07C..	07C	24	1462039-2		1462039-1				
IM07D..	07D	24		7-1462039-4	7-1462039-2				
IM07NS	07N	24				1-1462038-7			
IM08I..	08I	2.4			1462047-3				
IM11..	11	3	9-1462038-5						
IM12..	12	4.5	1462039-3						
IM13..	13	5	1462039-4						
IM15..	15	9	8-1462039-5						
IM16..	16	12	1462039-5						
IM17..	17	24	1462039-6		4-1462039-6				
IM21..	21	3	2-1462039-6		1-1462039-5				
IM22..	22	4.5	2-1462039-7		2-1462039-8	8-1462039-9			
IM23..	23	5	2-1462039-9		3-1462039-0	6-1462039-7			
IM25..	25	9	3-1462039-5						
IM26..	26	12	3-1462039-1		3-1462039-2				
IM40..	40	1.5	5-1462037-1						
IM40D..	40D	1.5	8-1462039-4						
IM40NS	40N	1.5				1-1462038-8			
IM41..	41	3	5-1462037-4	5-1462037-5	5-1462037-3				
IM41C..	41C	3	4-1462039-2						
IM41D..	41D	3	6-1462039-8						
IM41NS	41N	3				1-1462038-9			
IM42..	42	4.5	3-1462037-1	5-1462037-7	5-1462037-6				
IM42C..	42C	4.5	4-1462039-1						
IM42D..	42D	4.5	1-1462039-9						
*obsolete									
DIMENSIONS:		DWN	21FEB2003	MATERIAL		DRAWING ALIAS:			
mm		HD 9121		-		IM0C-DOK17			
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK	21FEB2003			FINISH			
		HD 9121				-			
		APVD	21FEB2003						
		HD 9121							
		PRODUCT SPEC							
		-							
		APPLICATION SPEC							
		-							
		WEIGHT							
		-							
		CUSTOMER DRAWING							
		SCALE	10:1						
		SHEET	3						
		OF	6						
		REV	C3						

2000

RELEASED FOR PUBLICATION


ALL RIGHTS RESERVED.

THIS DRAWING IS UNPUBLISHED.

COPYRIGHT 2000



0 PLC ±-
1 PLC ±-
2 PLC ±-
3 PLC ±-
4 PLC ±-
ANGLES ±-



TE Connectivity

IM-Relay
Marking


SIZE A 4 CAGE CODE 00779 DRAWING NO C-1462037-1 RESTRICTED TO -

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
HJ	-						
			-	SEE SHEET 1	-	-	-

Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)
IM42DNS	42D	4.5				1-1462039-6
IM42NS	42N	4.5				2-1462038-0
IM42P..	42P	4.5	5-1462039-7			
IM42PNS	42P	4.5				7-1462039-8
IM43..	43	5	5-1462037-9	6-1462037-0	5-1462037-8	
IM43C..	43C	5	9-1462038-7			
IM43NS	43N	5				2-1462038-1
IM44..	44	6	6-1462037-2	6-1462037-3	6-1462037-1	
IM44NS	44N	6				2-1462038-2
IM45..	45	9	6-1462037-4	6-1462037-5	3-1462037-2	
IM45I..	45I	9	1462047-5			
IM45NS	45	9				2-1462038-3
IM46..	46	12	6-1462037-7	6-1462037-8	6-1462037-6	
IM46C..	46C	12	8-1462039-0			
IM46NS	46N	12				2-1462038-4
IM46PNS	46P	12				6-1462039-1
IM47..	47	24	7-1462037-0		6-1462037-9	
IM47D..	47D	24		7-1462039-5		
IM47NS	47N	24				2-1462038-5
IM48..	48	2.4	1462039-8			
IM48D..	48D	2.4	1462039-9			
IM48C..	48C	2.4	9-1462039-0			
IM48I..	48I	2.4	1462047-1			
IM49I..	49I	2	1462047-4			

*obsolete

DRAWING ALIAS: IMOC-DOK17

DIMENSIONS:		DWN	HD 9121	21FEB2003	MATERIAL		-	FINISH		-		
mm		CHK	HD 9121	21FEB2003	TE Connectivity							
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		APVD	HD 9121	21FEB2003								
		PRODUCT SPEC		NAME IM-Relay Marking								
		APPLICATION SPEC										
		WEIGHT					SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
0 PLC ±- 1 PLC ±- 2 PLC ±- 3 PLC ±- 4 PLC ±- ANGLES ±-		-		A 4	00779	G- 1462037-1		-				
		CUSTOMER DRAWING			SCALE	10:1	SHEET	4	OF	6	REV	3

COPYRIGHT 2000

LOC		DIST		REVISIONS					
HJ		-		P	LTR	DESCRIPTION	DATE	DWN	APVD
					-	SEE SHEET 1	-	-	-
Relay-Typ	Mark 1)	Mark 2)	PN (GR)	PN (JR)	PN (TS)	PN (KS/NS)			
IMC01..	C01	3	1462042-1		1462042-4				
IMC02..	C02	4.5	1462042-2		1462042-5				
IMC03..	C03	5	1462042-8		1462042-7				
IMC06..	C06	12	1462042-3		1462042-6				
IMC07..	C07	24	1-1462042-1		1-1462042-2				
IMC02C..	C02C	4.5	1-1462042-0						
IMC03C..	C03C	5	1-1462042-5						
IMC06C..	C06C	12	1462042-9		1-1462042-4				
IMC41C..	C41C	3			1-1462042-3				
IME01..	E01	3	1462043-1		1462043-5				
IME02..	E02	4.5	1462043-2		1462043-6				
IME03..	E03	5	1462043-3		1462043-7				
IME06..	E06	12	1462043-4		1462043-8				
IMF61..	F61	3	1462048-3						
IMF68..	F68	2.4	1-1462048-0						
*obsolete									
DIMENSIONS:		DWN		21FEB2003		MATERIAL		DRAWING ALIAS:	
mm		HD 9121				-		IM0C-DOK17	
TOLERANCES UNLESS OTHERWISE SPECIFIED: DIN 7168-m		CHK		21FEB2003				FINISH	
		HD 9121						-	
		APVD		21FEB2003					
		HD 9121							
		PRODUCT SPEC							
		-							
		APPLICATION SPEC							
		-							
		WEIGHT							
		-							
		CUSTOMER DRAWING							
		SCALE		10:1		SHEET		6 OF 6	
		REV		C3					

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

	TE Connectivity
NAME	
IM-Relay Marking	
SIZE	CAGE CODE
A 4	00779
DRAWING NO	
C- 1462037-1	
RESTRICTED TO	
-	

2000

RELEASED FOR PUBLICATION

THIS DRAWING IS UNPUBLISHED.

ALL RIGHTS RESERVED.

COPYRIGHT 2000