





LOC		DIST		REVISONS				
GP	00	P	LTR	DESCRIPTION		DATE	DWN	APVD
			D1	REVISED PER ECR-18-005503		30MAY2018	BDA	SG




ISOMETRIC REAR VIEW
(12 POSITION SHOWN)




ISOMETRIC MATING FACE VIEW
(12 POSITION SHOWN)




CIRCUIT #1



FRONT VIEW
(2 POSITION SHOWN)



FRONT VIEW
(3 POSITION SHOWN)



FRONT VIEW
(4 POSITION SHOWN)

1 MATERIAL: NYLON, UL94V-0 FLAME RETARDENT, COLOR: NATURAL



2 HOUSINGS TO USE "RETAINER":

"BREAKAWAY RETAINER" P/N: 1-2132782-2 (12 POSITION),
12 POSITION PART TO BE SEPERATED AT APPROPRIATE NOTCHES TO FIT
2 POSITION THRU 11 POSITION HOUSINGS

"NORMAL RETAINER" P/N: X-1744544-X
WHERE XX IS THE NUMBER OF POSITIONS.

3 MEETS UL 61800-5-1

Flam	RTIle deg C	HWI	HA1	CTI
V0	130	PLC3	PLC1	PLC0_UL746



CIRCUIT #1

45.68	12.42	48.08	12	1-2132781-2
41.72	8.46	44.12	11	1-2132781-1
37.76	12.42	40.16	10	1-2132781-0
33.80	8.46	36.20	9	2132781-9
29.84	12.42	32.24	8	2132781-8
25.88	8.46	28.28	7	2132781-7
21.92	12.42	24.32	6	2132781-6
17.96	8.46	20.36	5	2132781-5
14.36	12.42	16.40	4	2132781-4
10.40	8.46	12.44	3	2132781-3
6.44	4.50	8.48	2	2132781-2
DIM H	DIM F	DIM A	NO. OF POSI.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN G. PETERS	09FEB2010	 TE Connectivity				
DIMENSIONS:				CHK E. HOWARD	09FEB2010					
mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:			APVD S. FLICKINGER	09FEB2010	NAME RECEPTACLE HOUSING, ECONOMY POWER II, 3.96 CENTERLINE W/ RETAINING FEATURES			
		0. PLC 1. PLC 2. PLC 3. PLC 4. PLC	± ±0.5 ±0.30 ± ±	PRODUCT SPEC			RESTRICTED TO			
		APPLICATION SPEC								
		FINISH			WEIGHT			SIZE CAGE CODE DRAWING NO		
MATERIAL 					-			A100779C=2132781		
Customer Drawing							SCALE 3:1 SHEET 1 OF 1 REV D1			