




1. MAXIMUM INSERTION LOSS IS 0.5dB PLUS CABLE ATTENUATION @ 1300nm. SEE TABLE
2. PRODUCT AND PROCESSING MUST MEET REQUIREMENTS OF THE TYCO ELECTRONICS STANDARD 230-702

0.65	100.0±1.0 [3937.0±39.4]	1-6278789-7
0.50	4.00±0.08 [157.5±3.0]	1-6278789-6
3.5	2000.0±20.0 [78740.0±787.0]	1-6278789-5
0.95	304.8±3.0 [12000.0±120.0]	1-6278789-4
0.50	0.75±0.03 [29.5±1]	1-6278789-3
0.50	0.65±0.03 [25.6±1]	1-6278789-2
0.54	30±0.30 [1181±12]	1-6278789-1
0.53	25±0.30 [984±12]	1-6278789-0
0.53	20±0.3 [787±12]	6278789-9
0.52	15±0.15 [591±6]	6278789-8
0.51	10±0.15 [394±6]	6278789-7
0.51	8±0.15 [315±6]	6278789-6
0.51	6±0.08 [236±3]	6278789-5
0.50	5±0.08 [197±3]	6278789-4
0.50	3±0.05 [118±2]	6278789-3
0.50	2±0.05 [79±2]	6278789-2
0.50	1±0.05 [39±2]	6278789-1
	L METERS [INCHES]	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN C.S.VASU 03 FEB 06		 Tyco Electronics Corporation Harrisburg, Pa 17105-3608	
DIMENSIONS: METERS [INCHES]		CHK J.DUNCAN 03 FEB 06			
		APVD J.DUNCAN 03 FEB 06		NAME CABLE ASSEMBLY, FIBER OPTIC, 62.5/125µm LDS, OVERMOLDED CERAMIC BAYONET, OPTIMATE	
		PRODUCT SPEC —			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC —		SIZE	
0 PLC ± —		WEIGHT —		CAGE CODE	
1 PLC ± —		CUSTOMER DRAWING		DRAWING NO	
2 PLC ± —				RESTRICTED TO	
3 PLC ± —		A2		00779	
4 PLC ± —		C=6278789		SCALE	
ANGLES ± —		N/A		SHEET	
MATERIAL		FINISH		1 OF 1	
—		—		REV	
				A1	

6278789

1

 A