



Not EU RoHS or ELV Compliant

- CNS Series
- Time Delay Relay
- Input Voltage = 120 VAC
- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Contact Rating = 10A @ 30 VDC or 277 VAC

[View all Features](#) | [Find Similar Products](#)

- ▶ [Check Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)
- ▶ [Request Samples](#)

NEW!

- None Available

- [CNS Multifunction Time Delay Relay \(PDF, English\)](#)

- None Available

- None Available

- None Available

- None Available

- Product Line Information

- Schematic
- Wiring Diagram

- Tooling

List all Documents

- Product Type = Time Delay Relay
- Termination Type = 8-Pin Octal Style Plug

- Input Voltage (VAC) = 120
- Contact Rating = 10A @ 30 VDC or 277 VAC

- Series = CNS

- Mounting Options = Socket
- Mode of Operation = Programmable - 4 Timing Functions
- Delay Time = 0.1 seconds to 100 minutes
- Type of Control = Knob
- Repeatability, Max. = $\pm 2\%$
- Approved Standards = CSA Certified, UL Recognized
- Contact Material = Silver Cadmium Oxide
- Approx. Dimensions (L x W x H) (mm [in]) = 47.80 x 47.80 x 71.90 [1.883 x 1.883 x 2.832]
- Enclosure = Beige Plastic 1/16 DIN Case

- Contact Arrangement = 2 Form C, DPDT, 2 C/O
- Multiple Timing Ranges = Without

- RoHS/ELV Compliance = Not ELV/RoHS compliant
- Lead Free Solder Processes = Not relevant for lead free process

- Temperature Range ($^{\circ}\text{C}$) = $-10 - +55$

- Brand = Potter & Brumfield