






1. REFERENCE APPLICATION SPEC 114-13059 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESSES.
2. MATERIAL:
CONTACT & SHIELD - PHOSPHOR BRONZE
HOUSING & CHICKLET - GLASS FILLED POLYESTER
3. FINISH:
CONTACT & SHIELD - 0.76µm MIN GOLD OVER
1.27µm MIN NICKEL IN MATING AREA, 0.5µm MIN TIN
OVER 1.27µm MIN NICKEL IN COMPLIANT PIN AREA.
4. CONNECTOR MARKED WITH PART NUMBER AND
DATE CODE IN APPROXIMATE AREA SHOWN
5. DIMENSION APPLIES TO CENTERLINE OF THRU HOLE
6. DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER
7. CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT.
TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995



THIS DRAWING IS A CONTROLLED DOCUMENT.						DWN C.D. HUMBERT		24NOV2010				TE Connectivity	
DIMENSIONS:						TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK N. LEHMAN		24NOV2010			
mm						FRACTIONAL		NAME		HEADER ASSEMBLY, SELECTIVELY LOADED, RIGHT ANGLE, 3 PAIR, HMZd			
						0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± ANGLES ±		PRODUCT SPEC					
MATERIAL						FINISH		APPLICATION SPEC					
								WEIGHT		SIZE CAGE CODE		DRAWING NO	RESTRICTED TO
										A100779		C=I645595	-
CUSTOMER DRAWING								SCALE		6:1		SHEET	OF
													REV 0