




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION AUG ,2006.
 © COPYRIGHT 2009 BY TYCO ELECTRONICS CORPORATION. ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS			
DW	—	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E	REVISED (ECR-09-022119)	09OCT09	SC	WK






SECTION C-C




NOTE:

- MATERIAL:
 HOUSING: LCP WITH 30% GF, UL 94V-0, BLACK COLOR.
 OR
 PA6T WITH 30% GF, 33% REGRIND, UL 94V-0, BLUE OR WHITE COLOR.
 CONTACTS: BRASS.
 BOARDLOCKS: BRASS.
- FINISH:
 CONTACTS: (SEE TABLE) GOLD PLATED ON CONTACT AREA, 2.54µm [100µ"] MIN. MATTE-TIN ON SOLDER TAIL, WITH ENTIRE CONTACT UNDERPLATED 1.27µm [50µ"] MIN. NICKEL.
 BOARDLOCKS: 1.27µm [50µ"] MIN. NICKEL OVER 2.54µm [100µ"] MIN. TIN PLATED.
- WAVE SOLDER CAPABLE TO 265°C PER TEST SPEC. 109-202, CONDITION B.



SECTION B-B



DIMENSIONS	A	B	HOUSING COLOR	MIN. GOLD THICKNESS	PART NUMBER	STATUS
3.37	3.3	BLUE (293C)	0.381µm [15µ"]	1-1734699-5	AVAILABLE	
		BLACK		1-1734699-4		
3.37	3	BLUE (293C)	0.381µm [15µ"]	1-1734699-3	AVAILABLE	
		BLACK		1-1734699-2		
2.57	2.05	WHITE	0.762µm [30µ"]	1734699-9	OBSOLETE	
			0.381µm [15µ"]	1734699-8		
			GOLD FLASH	1734699-7	AVAILABLE	
		BLUE (293C)	0.762µm [30µ"]	1734699-6	OBSOLETE	
			0.381µm [15µ"]	1734699-5		
			GOLD FLASH	1734699-4	AVAILABLE	
BLACK	0.762µm [30µ"]	1734699-3				
	0.381µm [15µ"]	1734699-2	AVAILABLE			
	GOLD FLASH	1734699-1				

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. WU 06JUN2008	Tyco Electronics Corporation Taipei, Taiwan			
DIMENSIONS: MM		CHK S. HOU 06JUN2008	NAME			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD W. KODAMA 06JUN2008	PRODUCT SPEC			
0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.25 3 PLC ± - 4 PLC ± - ANGLES ± 3°		QUALIFICATION SPEC		RESTRICTED TO		
MATERIAL SEE NOTE		FINISH SEE NOTE		SERIAL ATA, 7 POS., PLUG, VERTICAL, A TYPE, DIP.		
		108-57469 501-57539		SIZE A3	CAGE CODE 00779	
		WEIGHT 0.48 GRAMS		DRAWING NO C=1734699		
		CUSTOMER DRAWING		SCALE	SHEET 1 OF 2	
				REV E		

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

AUG ,2006.

© COPYRIGHT 2009

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

LOC
DWDIST
/

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1.			

SHIPPING BOX
INNER CARTON
SHEAF
TUBE

NOTE:

- DIMENSION:
TUBE: L= 340, W= 12.65, H= 5.8
INNER CARTON: L= 140, W= 77, H= 355
SHIPPING BOX: L= 372, W= 293, H= 172
- QUANTITY:
20 PCS/TUBE
50 TUBES/SHEAF
2 SHEAFS/INNER CARTON
4 INNER CARTONS/SHIPPING BOX
8000 PCS/SHIPPING BOX
- WEIGHT:
NET WEIGHT: 7.5 KG
GROSS WEIGHT: 8.5 KG

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:

MM

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	± -
1 PLC	± -
2 PLC	± -
3 PLC	± -
4 PLC	± -
ANGLES	± -
FINISH	-

MATERIAL

FINISH

DWN

CHK

APVD

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

-

CUSTOMER DRAWING

Tyco Electronics Corporation
Taipei, Taiwan

NAME

SERIAL ATA, 7 POS., PLUG,
VERTICAL, A TYPE, DIP.

SIZE

CAGE CODE

DRAWING NO

RESTRICTED TO

A300779

C=1734699

SCALE

-

SHEET

2 OF 2

REV

E

AMP 1470-19 REV 31MAR2000