








SEZ. (SECT.) A-A


SEZ. (SECT.) B-B



SEZ. (SECT.) C-C



SEZ. (SECT.) D-D



SEZ. (SECT.) E-E

NOTE (NOTES)

1. MATERIALE (MATL.): BRONZO FOSFOROSO (PHOSPHOR BRONZE).
2. FINITURA (FINISH): STAGNATO 0.8µm ECCEPTE LE ZONE TRANCIAE. CTIN PLATED 0.8µm ALL OVER EXCEPT FOR CUTTING EDGES).
3. PER MINI-APPLICATORE (FOR MINI-APPLICATOR) P/N 781119-2.
4. PER APPLICATORE STD. (FOR STD. APPLICATOR).
5. PER UTENSILE A MANO (FOR HANDTOOL) P/N 782116.

NOTE (NOTES)

182207-2

280709-1

280709-2

MATERIALE E FINITURA. (MATL. & FINISH)	LOOSE-PIECE PART NUMBER: (MATL. & FINISH)	STRIP PART NUMBER: (GR. TO L.3) (NOTA QUOTED 4)	STRIP PART NUMBER: (GR. TO R.3) (NOTA QUOTED 3)
1 & 2			

CUSTOMER DWG.
FOR REFERENCE ONLY

DISEGNO PER CLIENTE
SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED
BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS
RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING
TOLERANCES, SEE NON
DIVERGENTE SPECIFICATO
TOLERANCES, UNLESS
OTHERWISE SPECIFIED

± 0.3

AMP

AMP ITALIA S.p.A.
Corso F.lli Cervi, 15
COLLENO (TORINO)

DESCRIZIONE
AMP MODU II REC. CONTACT,
HIGH PRESSURE, C.O.S.I.

REV.	REVISIONI (REVISIONS)	DIS. DATA (DATE)	APP. (APP.)	LOC. SIZE (CODE NO)	REV.	FOR 10 (COVERED BY)
P	PRIMO SMOSSO E C.C. 1/1/89 AGGIUNTI MARCHIO C.T.R.A.D. 1/1/89 C.T.R.A.D. 1/1/89	DIS. G. CAMPA 29 JUNE 89	APP. 2	I A3C	280709	1