



LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
—	—		A1	REV LC CONN PROTECTIVE CAP	17APR15	KG	KG

1. MAXIMUM CONNECTOR INSERTION LOSS: 1.5 dB PRO BEAM JR. (1550nm)
0.5 dB LC (1550nm)
2. MINIMUM CONNECTOR RETURN LOSS: 34 dB PRO BEAM JR. (1550nm)
55 dB LC (1550nm)

3 SEE TRACE LABEL DETAIL.



LC CONNECTOR
4X



VIEW A-A
(NOT TO SCALE)

LC LABEL	PRO BEAM JR. POSITION
B1	A1
A1	B1
B2	A2
A2	B2

FIBER PATH CHART

TE CONNECTIVITY
BAR CODE



XXXXXXXXXXXXXXXXXX
 MADE IN XXXX 1938500-X

TE CONNECTIVITY
TRACE NO.

TE CONNECTIVITY
PART NO.

TRACE LABEL DETAIL 3

30.5+1.0/−0	1938500−2
15.000±0.150	1938500−1
L	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN K.GLATFELTER 22MAR2010	 TE Connectivity			
DIMENSIONS: METERS		CHK J.BARRY 22MAR2010				
		APVD J.BARRY 22MAR2010	NAME			
		PRODUCT SPEC	CABLE ASSEMBLY, FIBER OPTIC, 4 FIBER, SINGLEMODE, PRO BEAM JR., PLUG (NIALBRZ) TO (4) LC, 4 x 1550nm			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE A2	CAGE CODE 00779	DRAWING NO C=1938500	RESTRICTED TO —
MATERIAL —		WEIGHT —	CUSTOMER DRAWING		SCALE NTS	SHEET 1 OF 1
FINISH —		REVISIONS	REV A1			