




- 1

CONNECTOR SHALL BE MARKED IN ACCORDANCE WITH METHOD I OF MIL-STD-1285. MARKING SHALL CONTAIN THE MILITARY PIN, CAGE CODE (OR TE), AND DATE CODE. EXAMPLE: M83513/03-XXXX TE YYWW (WHERE XXXX IS PART OF THE PIN SHOWN IN THE "MIL-DTL-83513" COLUMN OF THE PART NUMBER TABLE, AND YYWW IS THE DATE CODE). FOR THE SIZE 15 PLUG, THE MARKING MUST BE PRINTED ON BOTH SIDES OF THE FLANGE. TEXT HEIGHT SHALL BE .035 INCH MINIMUM.
- 2

POSITION 1 SHALL BE INDICATED BY AN IDENTIFIABLE MARK, LOCATED APPROXIMATELY AS SHOWN ON THE POSITION 1 SIDE OF THE CONNECTOR FLANGE. THIS MARK SHALL BE INCLUDED AS PART OF THE PART MARKING INFORMATION.
- 3

LENGTH IS SHOWN IN THE "L DIM" COLUMN OF THE PART NUMBER TABLE. LENGTH TOLERANCE IS +1.0/-0.0 FOR INSULATED WIRE TERMINATIONS, AND +0.20/-0.00 FOR UNINSULATED WIRE TERMINATIONS
- 4


INSULATED WIRE IS SHOWN FOR REFERENCE ONLY. PART MAY BE TERMINATED WITH INSULATED OR UNINSULATED WIRE ACCORDING TO THE PART NUMBER TABLE.
- 5

EPOXY ENCAPSULATION. EPOXY MAY WICK .125 INCH MAX FOR INSULATED WIRE, AND .050 INCH MAX FOR UNINSULATED WIRE.
- 6

ALL DIMENSIONS AND REQUIREMENTS ARE PER MIL-DTL-83513/3

| LOC<br>— | DIST<br>— | REVISIONS |     |             |      |     |      |
|----------|-----------|-----------|-----|-------------|------|-----|------|
|          |           | P         | LTR | DESCRIPTION | DATE | DWN | APVD |
|          |           |           | —   | SEE SHEET 1 | —    | —   | —    |

| TE<br>PART NUMBER | <div>3</div> | <div>1</div>      |               |                       |
|-------------------|--------------|-------------------|---------------|-----------------------|
|                   | L DIM        | MIL-DTL-83513 PIN | MICRODOT P/N  | MCKS DESCRIPTION      |
| 1532180-1         | 18           | M83513/03-B01N    | 094-6225-0001 | MCKS-N1-B-15P6G1-18.0 |
| 1532180-2         | 36           | M83513/03-B02N    | 094-6225-0002 | MCKS-N1-B-15P6G1-36.0 |
| 1532180-3         | 18           | M83513/03-B03N    | 094-6225-0003 | MCKS-N1-B-15P6G9-18.0 |
| 1532180-4         | 36           | M83513/03-B04N    | 094-6225-0004 | MCKS-N1-B-15P6G9-36.0 |
| 1532180-5         | 18           | M83513/03-B09N    | 094-6225-0009 | MCKS-N1-B-15P6Q1-18.0 |
| 1532180-6         | 36           | M83513/03-B10N    | 094-6225-0010 | MCKS-N1-B-15P6Q1-36.0 |
| 1532180-7         | 18           | M83513/03-B11N    | 094-6225-0011 | MCKS-N1-B-15P6Q9-18.0 |
| 1532180-8         | 36           | M83513/03-B12N    | 094-6225-0012 | MCKS-N1-B-15P6Q9-36.0 |
| 1532180-9         | 72           | M83513/03-B13N    | 094-6225-0013 | MCKS-N1-B-15P6G1-72.0 |
| 1-1532180-0       | 72           | M83513/03-B14N    | 094-6225-0014 | MCKS-N1-B-15P6G9-72.0 |
| 1-1532180-1       | 72           | M83513/03-B15N    | 094-6225-0015 | MCKS-N1-B-15P6Q1-72.0 |
| 1-1532180-2       | 72           | M83513/03-B16N    | 094-6225-0016 | MCKS-N1-B-15P6Q9-72.0 |
| 1-1532180-3       | 0.5          | M83513/03-B05N    | 094-6225-0005 | MCKS-N1-B-15P5L4-0.5  |
| 1-1532180-4       | 1.0          | M83513/03-B06N    | 094-6225-0006 | MCKS-N1-B-15P5L4-1.0  |
| 1-1532180-5       | 0.5          | M83513/03-B07N    | 094-6225-0007 | MCKS-N1-B-15P5L5-0.5  |
| 1-1532180-6       | 1.0          | M83513/03-B08N    | 094-6225-0008 | MCKS-N1-B-15P5L5-1.0  |
| 1-1532180-7       | 18           | M83513/03-B01C    | 094-6235-0001 | MCKS-C2-B-15P6G1-18.0 |
| 1-1532180-8       | 36           | M83513/03-B02C    | 094-6235-0002 | MCKS-C2-B-15P6G1-36.0 |
| 1-1532180-9       | 18           | M83513/03-B03C    | 094-6235-0003 | MCKS-C2-B-15P6G9-18.0 |
| 2-1532180-0       | 36           | M83513/03-B04C    | 094-6235-0004 | MCKS-C2-B-15P6G9-36.0 |
| 2-1532180-1       | 0.5          | M83513/03-B05C    | 094-6235-0005 | MCKS-C2-B-15P5L4-0.5  |
| 2-1532180-2       | 1.0          | M83513/03-B06C    | 094-6235-0006 | MCKS-C2-B-15P5L4-1.0  |
| 2-1532180-3       | 0.5          | M83513/03-B07C    | 094-6235-0007 | MCKS-C2-B-15P5L5-0.5  |
| 2-1532180-4       | 1.0          | M83513/03-B08C    | 094-6235-0008 | MCKS-C2-B-15P5L5-1.0  |
| 2-1532180-5       | 18           | M83513/03-B09C    | 094-6235-0009 | MCKS-C2-B-15P6Q1-18.0 |
| 2-1532180-6       | 36           | M83513/03-B10C    | 094-6235-0010 | MCKS-C2-B-15P6Q1-36.0 |
| 2-1532180-7       | 18           | M83513/03-B11C    | 094-6235-0011 | MCKS-C2-B-15P6Q9-18.0 |
| 2-1532180-8       | 36           | M83513/03-B12C    | 094-6235-0012 | MCKS-C2-B-15P6Q9-36.0 |
| 2-1532180-9       | 72           | M83513/03-B13C    | 094-6235-0013 | MCKS-C2-B-15P6G1-72.0 |
| 3-1532180-0       | 72           | M83513/03-B14C    | 094-6235-0014 | MCKS-C2-B-15P6G9-72.0 |
| 3-1532180-1       | 72           | M83513/03-B15C    | 094-6235-0015 | MCKS-C2-B-15P6Q1-72.0 |
| 3-1532180-2       | 72           | M83513/03-B16C    | 094-6235-0016 | MCKS-C2-B-15P6Q9-72.0 |

|                                                                                       |                                                                                                                                   |                     |              |                                                                                                                                                 |                         |
|---------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------|---------------------|--------------|-------------------------------------------------------------------------------------------------------------------------------------------------|-------------------------|
| THIS DRAWING IS A CONTROLLED DOCUMENT.                                                |                                                                                                                                   | DWN<br>B. ROMANCHUK | 03 SEP 08    |  Tyco Electronics Corporation<br>Harrisburg, PA 17105-3608 |                         |
| DIMENSIONS:<br>INCHES                                                                 |                                                                                                                                   | CHK<br>—            | —            | NAME                                                                                                                                            |                         |
|  |                                                                                                                                   | APVD<br>M. STORRY   | 03 SEP 08    | PRODUCT SPEC                                                                                                                                    |                         |
|                                                                                       |                                                                                                                                   | APPLICATION SPEC    |              | RESTRICTED TO                                                                                                                                   |                         |
|                                                                                       |                                                                                                                                   | —                   |              | —                                                                                                                                               |                         |
| MATERIAL<br>—                                                                         | TOLERANCES UNLESS OTHERWISE SPECIFIED:<br>0 PLC ± -<br>1 PLC ± -<br>2 PLC ± -<br>3 PLC ± -<br>4 PLC ± -<br>ANGLES ± -<br>FINISH — | WEIGHT<br>—         | SIZE<br>A2   | CAGE CODE<br>98278                                                                                                                              | DRAWING NO<br>C=1532180 |
| CUSTOMER DRAWING                                                                      |                                                                                                                                   |                     | SCALE<br>4:1 | SHEET<br>2 OF 2                                                                                                                                 | REV<br>A                |