






REVISIONS						
P	LYR	DESCRIPTION	DATE	DWN	APVD	
	F	REVISED PER ECR-20-100915	28APR2021	JP	VS	
	G	REVISED PER ECR-22-130081	12OCT2022	SKR	DS	
	H	REVISED PER ECR-22-146226	09NOV2022	RS	DS	
	HI	REVISED PER ECR-22-158310	16NOV2022	RS	DS	



POS.	DIM. A
2*6	39.70
2*5	33.70
2*4	27.70
2*3	21.70



SIDE RAIL DESIGN FOR LEVEL 2 RESIN

△ MATERIAL:
LEVEL 1: PBT, STANDARD TEMPERATURE 105°C
KEY A: NATURAL; KEY B: PURPLE; KEY C: BLUE; KEY D: YELLOW


LEVEL 2: PA66, HIGH TEMPERATURE 150°C
KEY A: LIGHT GREY; KEY B: RED; KEY C: BLACK; KEY D: NATURAL

△ MATERIAL MARK:
LEVEL 1:PBT,LEVEL 2:HDT

3. APPLICABLE CONTACT P/N
RECEPTACLE CONTACT: 1971237/1971779/81/83/85/87-*, 2238066-*


4. MATING CONN, P/N
CAP HSG: *-1971774/5-*
TPA (LOCKING PLATE): *-1971778-*

△ GLOW WIRE COMPLIANT IN ACCORDANCE WITH IEC 60335-1. THIS IS BASED ON THE PRODUCT MEETING A GWEPT 850° C TEST AND RESIN GWIT GREATER THAN OR EQUAL TO 775° C.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 09JUL2012 COMMY WU		 TE Connectivity	
DIMENSIONS:		CHK 09JUL2012 HAPYE WU			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 09JUL2012 YIHONG MAO		NAME	
mm		PRODUCT SPEC 108-106118		PLUG HOUSING, DOUBLE ROW POWER TRIPLE LOCK	
		APPLICATION SPEC 114-106118		SIZE CAGE CODE DRAWING NO	
0 PLC ±. 1 PLC ±.35 2 PLC ±.0.25 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		WEIGHT -		RESTRICTED TO -	
MATERIAL		Customer Drawing		A1 00779 C-1971776	
		SCALE 4:1		SHEET 1 OF 2 REV H1	


LOC		DIST		REVISIONS			
P	LTR	DESCRIPTION		DATE	DWN	APVD	
-	-	SEE SHEET 1		-	-	-	




2*5 POSITIONS




KEYING FOR 2*5 POS.




2*4 POSITIONS



KEYING FOR 2*4 POS.




2*3 POSITIONS




KEYING FOR 2*3 POS.

2*6	LEVEL 1	KEY A	1-1971776-6
		KEY B	2-1971776-6
		KEY C	3-1971776-6
		KEY D	4-1971776-6
	LEVEL 2	KEY A	5-1971776-6
		KEY B	6-1971776-6
		KEY C	7-1971776-6
		KEY D	8-1971776-6
2*5	LEVEL 1	KEY A	1-1971776-5
		KEY B	2-1971776-5
		KEY C	3-1971776-5
		KEY D	4-1971776-5
	LEVEL 2	KEY A	5-1971776-5
		KEY B	6-1971776-5
		KEY C	7-1971776-5
		KEY D	8-1971776-5
POS.	MATERIAL	KEY	P/N

2*4	LEVEL 1	KEY A	1-1971776-4
		KEY B	2-1971776-4
		KEY C	3-1971776-4
		KEY D	4-1971776-4
	LEVEL 2	KEY A	5-1971776-4
		KEY B	6-1971776-4
		KEY C	7-1971776-4
		KEY D	8-1971776-4
2*3	LEVEL 1	KEY A	1-1971776-3
		KEY B	2-1971776-3
		KEY C	3-1971776-3
		KEY D	4-1971776-3
	LEVEL 2	KEY A	5-1971776-3
		KEY B	6-1971776-3
		KEY C	7-1971776-3
		KEY D	8-1971776-3
POS.	MATERIAL	KEY	P/N



2*6 POSITIONS



KEYING FOR 2*6 POS.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TOMMY WU	09JUL2012	 TE Connectivity	NAME PLUG HOUSING, DOUBLE ROW POWER TRIPLE LOCK - - - Customer Drawing	
		CHK HAPYE WU	09JUL2012			
		APVD YUZHONG MAO	09JUL2012			
		PRODUCT SPEC				
DIMENSIONS:		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC		
mm		0 PLC ± 1 PLC ±0.35 2 PLC ±0.25 3 PLC ± 4 PLC ± ANGLES ±		108-106118		
				114-106118		
MATERIAL		FINISH		WEIGHT		
-		-		-		
				A1 00779 ©=1971776		
				SCALE 5:1 SHEET 2 OF 2 REV H1		