



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECO-16-002001	25MAY2016	LN	RS




$\phi 0.79 \pm 0.13$
[.031 ± .005]
3 HOLES 120° APART



THREADS, SEE TABLE

VIEW X



THREADS, SEE TABLE

VIEW Y
SAME AS VIEW X EXCEPT AS SHOWN

- 1

SILVER PLATE PER QQ-S-365, 5.08μm[.000200] MIN THK
- 2

GOLD PLATE PER MIL-G-45204, 1.27μm[.000050] MIN THK
- 3

NICKEL PLATE PER QQ-N-290, 2.54μm[.000100] MIN THK
- 4

PASSIVATE PER QQ-P-35
- 5

5/8-24 UNEF-2B
- 6

7/16-28 UNEF-2B
- 7

1/4-36 UNS-2B

	X	5	3.18 [.125]	19.05±0.38[.750±.015]	1	BRASS PER QQ-B-626	9-332004-1
	Y	5	3.18 [.125]	19.05±0.38[.750±.015]	1	BRASS PER QQ-B-626	9-332004-0
	X	5	3.18 [.125]	19.05±0.38[.750±.015]	3	BRASS PER QQ-B-626	2-332004-3
	Y	7	1.57 [.062]	7.92±0.38[.312±.015]	3	BRASS PER QQ-B-626	2-332004-2
	Y	7	1.57 [.062]	7.92±0.38[.312±.015]	4	SST PER ASTM-A-582	2-332004-0
OBSOLETE	X	5	3.18 [.125]	19.05±0.38[.750±.015]	1	BRASS PER QQ-B-626	1-332004-9
	Y	5	3.18 [.125]	19.05±0.38[.750±.015]	3	BRASS PER QQ-B-626	1-332004-7
	Y	7	1.57 [.062]	7.92±0.38[.312±.015]	2	SST PER ASTM-A-582	1-332004-5
	Y	7	1.57 [.062]	7.92±0.38[.312±.015]	-	SST PER ASTM-A-582	1-332004-4
OBSOLETE	Y	5	3.18 [.125]	19.05±0.38[.750±.015]	1	BRASS PER QQ-B-626	1-332004-0
	VIEW	THREADS	B	A	FINISH	MATERIAL	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm [INCHES]

MATERIAL
SEE TABLE

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± 0.20[.008]

3 PLC ± -

4 PLC ± -

ANGLES ± -

FINISH
SEE TABLE

DWN
M. SNEED
5-18-93

CHK
J. DUNBAR
5-18-93

APVD
M. SNEED
5-18-93

PRODUCT SPEC
-

APPLICATION SPEC
-

WEIGHT
0.000000

CUSTOMER DRAWING

TE Connectivity

NAME
JAM NUT
-

SIZE
A2

CAGE CODE
00779

DRAWING NO
C-332004

RESTRICTED TO
-

SCALE
4:1

SHEET
1 OF 1

REV
D1