


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	REMOVED CORNER HOLE	01SEP2016	VL	SS
	A	DRAWING RELEASED	21APR2017	VL	SS
	A1	REVISED PER ECO-17-007644	26MAY2017	VL	SS
	A2	REVISED PER ECO-17-013857	20SEP2017	SS	HL



SCALE 3:1

NOTES:

- 1 MATERIAL: 0.20mm CRS. 1,25 - 3.00µm MATTE TIN FINISH.
- 2 MATERIAL: 0.20mm AL. 1.20 - 2.00µm MATTE TIN FINISH OVER NICKEL FLASH.
- 3 STAMPING BURR OUTSIDE OF PART, MAX 0.05mm.
- 4 PARTS TO BE FREE OF OIL AND CONTAMINENTS.
- 5 PART IS RoHS COMPLIANT PER TE CONNECTIVITY STANDARD TEC-138-702.
- 6 REFER TO 3D MODEL FOR UNSPECIFIED DIMENSIONS.
- 7 PACKAGING: TAPE AND REEL

7	2	2118707-4
7	1	2118707-2
PACKAGING	MATERIAL	PART NUMBER




TE Connectivity

NAME
1 PIECE STANDARD SHIELD


SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	©-2118707	-

DWN	V. LAC	07APR2016
CHK	S. SU	21APR2017
APVD	V. LAC	21APR2017
PRODUCT SPEC		
108-115119		
APPLICATION SPEC		
114-115013		
WEIGHT		
-		
CUSTOMER DRAWING		

THIS DRAWING IS A CONTROLLED DOCUMENT.		
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	
	0 PLC	±0.20
	1 PLC	±0.15
	2 PLC	±0.10
	3 PLC	±-
	4 PLC	±-
	ANGLES	±2
MATERIAL SEE TABLE	FINISH	SEE TABLE
-	-	-




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



NOTES:

8. STENCIL THICKNESS: 0.10mm MIN.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN V. LAC 07APR2016		TE Connectivity							
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		CHK S. SU 21APR2017		NAME 1 PIECE STANDARD SHIELD					
		0 PLC ±0.20 1 PLC ±0.15 2 PLC ±0.10 3 PLC ± 4 PLC ± ANGLES ±2		APVD V. LAC 21APR2017							
				PRODUCT SPEC 108-115119							
				APPLICATION SPEC 114-115013							
MATERIAL SEE TABLE -		FINISH SEE TABLE -		SIZE A3		CAGE CODE -		DRAWING NO C-2118707		RESTRICTED TO -	
CUSTOMER DRAWING				SCALE 5:1		SHEET 2 OF 3		REV A2			

