



MOD	LOC	DIST	P	F	ZONE	LTR	DESCRIPTION	DATE	APPD
4	BD	39				T	ADDED -9 PER NPR 4680 AND REDRAWN ON CAD	04/07/93	-
						T1	REVISED PER ECO-09-020935	08SEP09	KK AEG



TAPE MTG DETAIL
SCALE 2:1

- 1 0.76µm [.000030] MIN GOLD OVER 1.27µm [.000050] MIN NICKEL.
- 2 2.54µm [.000100] MIN GOLD OVER 1.27µm [.000050] MIN NICKEL.
- 3 WHEN ORDERING CONTACT ASSEMBLY ON TAPE, ORDER BY THE TAPE NUMBER PLUS THE PACKAGING CODE AS FOLLOWS:
- 1. FOR USE WITH AMP TAPETRONIC, PNEUMATIC TOOL—
A. 1000 PARTS TO A BOX ADD PACKAGING CODE: 1MBOX
 - 2. FOR USE WITH 4/8 INDENT STRIPPER CRIMPER—
A. 1000 PARTS TO A REEL ADD PACKAGING CODE: 1MREEL
B. 5000 PARTS TO A REEL ADD PACKAGING CODE: 5MREEL
- 4 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

4 OBSOLETE	SMALL PACK	1	-201580-9-
	TAPE MTG (SEE DETAIL) 3	2	-201580-7-
	TAPE MTG (SEE DETAIL) 3	1	-201580-4-
	STANDARD	2	201580-3
	STANDARD	1	201580-1

	PACKAGING TYPE	SOCKET BODY FINISH	PART NO
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON :	DR 04/07/93 D.GELTZ	AMP AMP Incorporated Harrisburg, PA 17105-3608	
2 PLC DEC ± -	CHK 4-26-93 R.STONE		
3 PLC DEC ± -	APPD 4-29-93 R.S.KLINE		
ANGLES ± -	APPD -		
MATERIAL	PRODUCT SPEC	CONTACT ASSEMBLY, SOCKET, #16, 20-24 AWG, TYPE II	
SOCKET BODY: COPPER ALLOY	-		
SPRING: STAINLESS STEEL	APPLICATION SPEC	SIZE C	CAGE CODE 00779
FINISH	-	DRAWING NO C-201580	
SOCKET BODY: SEE TABLE	WEIGHT -	SCALE 10:1	SHEET 1 OF 1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.