





LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	DWN
		B		REV PER ECO 12-010940	7-31-12	CT
		C		REVISED PER ECO-14-017030	24NOV14	MGM



- △ MATERIAL:
CONTACT AND SHIELD: COPPER ALLOY
HOUSING AND CHICKLET: LCP, COLOR: BLACK
- △ FINISH:
CONTACT: MATING AREA: 1.27µm MIN GOLD OVER
1.27µm MIN NICKEL
- △ FINISH:
COMPLIANT PIN AREA: 0.38µm MIN BRIGHT TIN LEAD OVER
1.27µm MIN NICKEL
- △ FINISH:
COMPLIANT PIN AREA: 0.38µm MIN MATTE TIN OVER
1.27µm MIN NICKEL
- △ --
- △ DIMENSION APPLIES TO CENTERLINE OF THRU HOLE.
- △ DATUMS AND BASIC DIMENSIONS ESTABLISHED BY CUSTOMER.
- △ REFERENCE APPLICATION SPEC 114-13267 FOR RECOMMENDED PLATED THRU HOLE DIAMETER AND PLATING THICKNESS.



△ △	2102315-2
△ △	2102315-1
FINISH	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. BELACK 24JUN2009	TE Connectivity	
DIMENSIONS:		CHK A. TSANG 6-24-2009	NAME Fortis Zd, 3-PAIR, 10-COLUMN, R/A, CENTER MODULE ASSEMBLY, SINGLE ENDED	
mm		APVD W. McALONIS 6-24-2009	SIZE CAGE CODE DRAWING NO	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	RESTRICTED TO	
0 PLC ±0.13		APPLICATION SPEC	A100779C=2102315	
1 PLC ±0.05		WEIGHT	SCALE	
2 PLC ±0.05		~11.16g	5:1	
3 PLC ±0.05		CUSTOMER DRAWING	SHEET 1 OF 1	
4 PLC ±0.05			REV C	
ANGLES FINISH				
MATERIAL				