

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

MAY ,2011.

© COPYRIGHT 2011 By Tyco Electronics Japan G.K.

ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE
J			B	REVISED	16SEP2015

1.材料 ハウジング、スライダ：熱可塑性樹脂 UL 94-V 色：黒

コンタクト：銅合金

シェル：銅合金

コイル：SWP

カムロッド：SUS

フックスプリング：SUS

2 仕上げ コンタクト：Ni下地めっき

接点部：金めっき

シェル：Ni下地めっき

金めっき

③ 非累積公差

4. コプラナリティは 0.1mm以下

⑤ スイッチ回路図

⑥ デートコードマーキングすること。吸着エリアφ4にはマーキングしないこと。

⑦ バージョンマーキングすること。吸着エリアφ4にはマーキングしないこと。

⑧ 生産場所コード：“G”：GUANGDONG，“Q”：QINGDAO.

1.MATERIAL HOUSING,SLIDER : THERMOPLASTIC RESIN

UL94V-0, COLOR;BLACK

CONTACT : COPPER ALLOY

SHELL : COPPER ALLOY

COIL : SWP

CAM ROD : SUS

HOOK SPRING : SUS

2 FINISH CONTACT : Ni UNDER PL

Au PL AT CONTACT AREA

SHELL : Ni UNDER PL

Au PL

③ NON-CUMULATIVE TOLERANCE



4. COPLANARITY IS 0.1MAX.


⑤ CIRCUIT DRAWING OF SWITCH.

⑥ MARK DATE CODE. MUST NOT MARK AT VACUUM AREA φ4.

YEAR XXXX WEEK
DAY SHIFT LINE
MARK VERSION. MUST NOT MARK AT VACUUM AREA φ4.
(MASS PRO) AX (PROTO) P1→P2→PX

⑧ PRODUCTION LOCATION CODE: "G" FOR GUANGDONG, "Q" FOR QINGDAO.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN Y.KUDO	21MAY2012	 TE Connectivity		
		CHK K.KOBAYASHI	21MAY2012			
DIMENSIONS: 単位： 耗 MM	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	APVD T.KUSUHARA	21MAY2012	NAME 名称		
	0 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES	PRODUCT SPEC 製品規格 108-78951	MICRO SD PUSH PUSH LOW PROFILE TYPE			
	± 0.3 ± 0.3 ± 0.3 ± 0.3 ± 0.3 ± 1°	APPLICATION SPEC 取付適用規格				
MATERIAL 材料	FINISH 仕上	WEIGHT 0.45g	SIZE A3	CAGE CODE 00779	DRAWING NO 番号 C-2201778	RESTRICTED —
CUSTOMER DRAWING			SCALE 尺度 5:1	SHEET 1 OF 4	REV B	

