





LOC	DIST	REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD	
	CI	REVISED PER ECO-12-007964	02MAY2012	KH	MS	




282824-3 AS SHOWN



- 1 MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
TERMINAL: COPPER ALLOY, TIN PLATED.
- 2 SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3 END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.
- 4 RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC. FILE N° E60677.
- 5 IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
- 6 NOT CUMULATIVE TOLERANCE.

RECOMMENDED PC BOARD LAYOUT



20.32	4	282824-4
15.24	3	282824-3
10.16	2	282824-2
DIM. A	N° OF POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN E. ZANOLINI 30 JUL 2001	 TE Connectivity		
DIMENSIONS: mm		CHK D. BIEVENOUR 30 JUL 2001			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. BIEVENOUR 30 JUL 2001	NAME TERMINAL BLOCK HEADER ASSEMBLY 180 DEGREE STACKING W/INTERLOCK 5.08mm PITCH		
0 PLC $\pm .3$ 1 PLC $\pm .3$ 2 PLC $\pm .25$ 3 PLC $\pm .$ 4 PLC $\pm .$ ANGLES ± 2		PRODUCT SPEC 108-20166			
MATERIAL		APPLICATION SPEC 114-20079	SIZE A300779		
FINISH		WEIGHT -			
CUSTOMER DRAWING		DRAWING NO C-282824		RESTRICTED TO -	
SCALE 3:1		SHEET 1 OF 1		REV C	