





P	LTR	DESCRIPTION	DATE	DWN	APVD
	E5	REVISED PER ECO-20-006341	16JUL2021	GMN	PS

POLARIZATION KEY SLOT




284512-3 AS SHOWN



- 1 MATERIALS AND FINISH
HOUSING : PA 6.6, UL 94-V0, COLOR GREEN
TERMINAL : PHOSPHOR BRONZE, PLATING: SEE TABLE.


2. SUITABLE FOR 1.6-2.4 mm. PC BOARD THICKNESS

- 3 NOT CUMULATIVE TOLERANCE
- 4 PRELIMINARY - NOT FOR PRODUCTION.
- 5 SPECIAL CODING LOCATED AT POSITION 2.
PART TO BE MATED WITH 2-284506-9.
- 6 SPECIAL CODING LOCATED AT POSITION 1 AND 2.
PART TO BE MATED WITH 3-284506-0.



RECOMMENDED PC BOARD LAYOUT

OBSOLETE	4	6	TIN	12.8	11.5	3	3-284512-9
	4	5	TIN	12.8	11.5	3	3-284512-8
	4		GOLD FLASH	26.8	25.5	7	3-284512-6
			0.2 MICRON GOLD	44.3	43.0	12	3-284512-5
			TIN	16.3	15.0	4	3-284512-4
			TIN	12.8	11.5	3	3-284512-3
			TIN	89.8	88.5	25	2-284512-5
			TIN	86.3	85.0	24	2-284512-4
			TIN	82.8	81.5	23	2-284512-3
			TIN	79.3	78.0	22	2-284512-2
			TIN	75.8	74.5	21	2-284512-1
			TIN	72.3	71.0	20	2-284512-0
			TIN	68.8	67.5	19	1-284512-9
			TIN	65.3	64.0	18	1-284512-8
			TIN	61.8	60.5	17	1-284512-7
			TIN	58.3	57.0	16	1-284512-6
			TIN	54.8	53.5	15	1-284512-5
			TIN	51.3	50.0	14	1-284512-4
			TIN	47.8	46.5	13	1-284512-3
			TIN	44.3	43.0	12	1-284512-2
			TIN	40.8	39.5	11	1-284512-1
			TIN	37.3	36.0	10	1-284512-0
			TIN	33.8	32.5	9	284512-9
			TIN	30.3	29.0	8	284512-8
			TIN	26.8	25.5	7	284512-7
			TIN	23.3	22.0	6	284512-6
			TIN	19.8	18.5	5	284512-5
			TIN	16.3	15.0	4	284512-4
			TIN	12.8	11.5	3	284512-3
			TIN	9.3	8.0	2	284512-2
			TERMINAL PLATING	B	A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 06FEB2002 E. ZANOLINI	 TE Connectivity	
		CHK 06FEB2002 E. ZANOLINI		
DIMENSIONS: mm		APVD 06FEB2002 D. BIEVENOUR	NAME TERMINAL BLOCK, HEADER ASSEMBLY 90 DEGREE, CLOSED ENDS 3.5mm PITCH	
		PRODUCT SPEC 108-20166	SIZE A300779	
		APPLICATION SPEC 114-20079		
MATERIAL		WEIGHT -	DRAWING NO C-284512	
FINISH		RESTRICTED TO		
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 OF 1
		REV E5		