






NOTES:

- ① MATERIAL CONTACTS; PHOSPHORBRONZE
MATERIAL HOUSING; GLASSFILLED POLYESTER (GRAY)
- ② GENERAL PLATING SPECIFICATION: UNDERPLATING (ENTIRE CONTACT):
1,27µm NICKEL MIN. AND ACTION PIN: 0,5µm TIN-LEAD MIN.
FOR PLATING OF MATING SURFACES SEE APPLICABLE SPECIFICATION
REFERENCE FOR EACH DASH NUMBER.
- ③ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 2.
- ④ CONFORMS TO ALL TESTING ACCORDING IEC 61076-4-101
PERFORMANCE LEVEL 1.
- ⑤ CONNECTOR TESTED AND QUALIFIED AGAINST TELCORDIA
GR-1217-CORE QUALITY LEVEL III, CENTRAL OFFICE APPLICATIONS.
- ⑥ CONNECTOR LUBRICATED WITH TELCORDIA GR-1217-CORE
APPROVED LUBRICANT.
- ⑧ ASSEMBLY PRINTED WITH P/N AND DATECODE
THE MARKING CAN APPEAR ON THE FRONT SIDE OR BACK SIDE.
- ⑨ HOLE PATTERN FOR FEMALE CONNECTOR TYPE A
110 PLATED-THROUGH HOLES AT 2x2mm SQUARE GRID
- ⑩ ROW "f" 13 PLATED THROUGH HOLES FOR UPPERSHIELD
- ⑪ SHIELD MOUNTED ON CONNECTOR WITH DOUBLE SIDED
ADHESIVE TAPE OR ADHESIVE
- ⑫ AREA RESERVED FOR KEYING PART (BASIC P.N. 100526)
13 BASIC P.N. LOWERSHIELD: 338108
- REF. ⑭ 0.76µm MIN GOLD PLATING AT MATING SURFACES.



COMPONENT SIDE AS SHOWN
RECOMMENDED PCB-HOLE LAY-OUT
SCALE 2,5:1



	  		3-352068-0
OBSOLETE	  		— 352068-9 —
OBSOLETE	 		— 352068-4 —
	 		352068-1
	FINISH	MATERIAL	PARTNUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. TRURIN	20JAN97	 TE Connectivity		
DIMENSIONS: mm		CHK —	—			
	TOLERANCES UNLESS OTHERWISE SPECIFIED: ±0.2		Z-PACK 2MM HM TYPE A – 25 COLUMNS PRE-SHIELDED RECEPTACLE			
	APVD —					NAME
	PRODUCT SPEC 108-19082					
	APPLICATION SPEC 114-19029					
MATERIAL —	FINISH —	WEIGHT 0.000000	A2	00779	C-352068	RESTRICTED TO —
CUSTOMER DRAWING			SCALE NTS	SHEET 1 of 1	REV N	