

OBSOLETE

SUPERSEDED

SUPERSEDED

SUPERSEDED

SUPERSEDED



SUPERSEDED

SUPERSEDED

SUPERSEDED

SUPERSEDED

SUPERSEDED



MATERIAL: CONNECTOR - NYLON UL94V-2 (BLUE).
CONTACTS - 0.30[.012] THICK COPPER ALLOY
BRIGHT TIN-LEAD .00203[.000080] MIN THICKNESS
FOR 640622-2 THRU 2-640622-8.
MATTE WHISKER MITIGATED TIN .00203[.000080] MIN THICKNESS
OVER NICKEL UNDERPLATE FOR 3-640622-2 THRU 5-640622-8.

2 CONTACTS ACCEPT 26 AWG WIRE WITH 1.52[.060] MAX
INSULATION DIAMETER.

3 CONTACTS MUST ACCEPT 0.64 ± 0.03 [.025 $\pm$.001] SQUARE
POST AND REMAIN LOCKED IN POSITION.

4 IDENTIFICATION NUMBER FOR LAST CIRCUIT MAY NOT APPEAR ON ALL ASSEMBLIES.

5 DIMENSIONS IN BRACKETS ARE IN INCHES.

6 HOUSING FEATURES ARE: FEED THRU WITH LOCKING
RAMP.

△ OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER
D.RENAUD/D.SINISI

8 OBSOLETE PARTS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. CARPENTER 08AUG2003		 TE Connectivity	
		CHK D. BOSSI 08AUG2003			
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME MTA-100 CONNECTOR ASSEMBLY, 26 AWG, STANDARD	
		APVD D. BOSSI 08AUG2003			
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 0.13 [005] 4 PLC ± ANGLES ±		PRODUCT SPEC 108-1050			
MATERIAL		APPLICATION SPEC 114-1019			
		FINISH		SIZE A2	
		WEIGHT		CAGE CODE 00779	
CUSTOMER DRAWING				DRAWING NO C-640622	
				RESTRICTED TO —	
				SCALE 5:1	
				SHEET 1 of 1	
				REV Y1	

A